

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unavteries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or i, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor and is officers, employees, uniotificated use, even if such claim any manner.



N-Channel PowerTrench[®] MOSFET 30 V, 3.8 m Ω

Features

- Max $r_{DS(on)}$ = 3.8 m Ω at V_{GS} = 10 V, I_D = 21 A
- Max $r_{DS(on)} = 5.0 \text{ m}\Omega$ at $V_{GS} = 4.5 \text{ V}$, $I_D = 17 \text{ A}$
- Advanced Package and Silicon design for low r_{DS(on)} and high efficiency
- Next generation enhanced body diode technology, engineered for soft recovery. Provides Schottky-like performance with minimum EMI in sync buck converter applications
- MSL1 robust package design
- 100% UIL tested
- RoHS Compliant




General Description

This N-Channel MOSFET has been designed specifically to improve the overall efficiency and to minimize switch node ringing of DC/DC converters using either synchronous or conventional switching PWM controllers. It has been optimized for low gate charge, low $r_{DS(on)}$, fast switching speed and body diode reverse recovery performance.

Applications

- IMVP Vcore Switching for Notebook
- VRM Vcore Switching for Desktop and Server
- OringFET / Load Switch
- DC-DC Conversion



MOSFET Maximum Ratings T_A = 25 °C unless otherwise noted

Symbol	Parameter			Ratings	Units	
V _{DS}	Drain to Source Voltage			30	V	
V _{GS}	Gate to Source Voltage		(Note 4)	±20	V	
ID	Drain Current -Continuous (Package limited)	T _C = 25 °C		42		
	-Continuous (Silicon limited)	T _C = 25 °C		105		
	-Continuous	T _A = 25 °C	(Note 1a)	21	Α	
	-Pulsed			150		
E _{AS}	Single Pulse Avalanche Energy		(Note 3)	144	mJ	
P _D	Power Dissipation	T _C = 25 °C		62	W	
	Power Dissipation	T _A = 25 °C	(Note 1a)	2.5		
T _J , T _{STG}	Operating and Storage Junction Temperature Range			-55 to +150	°C	

Thermal Characteristics

R_{\thetaJC}	Thermal Resistance, Junction to Case	2.0	°C/W
$R_{ ext{ heta}JA}$	Thermal Resistance, Junction to Ambient (Note	1a) 50	0/10

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDMS7670	FDMS7670	Power 56	13 "	12 mm	3000 units


G

S

s

S

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
Off Chara	cteristics					
BV _{DSS}	Drain to Source Breakdown Voltage	I _D = 250 μA, V _{GS} = 0 V				V
$\frac{\Delta BV_{DSS}}{\Delta T_{I}}$	Breakdown Voltage Temperature Coefficient	$I_D = 250 \ \mu\text{A}, \ V_{GS} = 0 \ V \ 30$ $I_D = 250 \ \mu\text{A}, \ referenced to 25 \ ^{\circ}\text{C}$		15		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 24 V, V _{GS} = 0 V			1	μA
I _{GSS}	Gate to Source Leakage Current, Forward	$V_{GS} = 20 \text{ V}, \text{ V}_{DS} = 0 \text{ V}$			100	nA
	cteristics					
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_{D} = 250 \ \mu A$	1.25	1.9	3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_{.1}}$	Gate to Source Threshold Voltage Temperature Coefficient	$I_D = 250 \ \mu\text{A}$, referenced to 25 °C	1.20	-7	0.0	mV/°C
j	Static Drain to Source On Resistance	V _{GS} = 10 V, I _D = 21 A		2.9	3.8	
r _{DS(on)}		$V_{GS} = 4.5 \text{ V}, I_D = 17 \text{ A}$		4.1	5.0	mΩ
		$V_{GS} = 10 \text{ V}, \text{ I}_{D} = 21 \text{ A}, \text{ T}_{J} = 125 \text{ °C}$				1
9fs	Forward Transconductance	V _{DS} = 5 V, I _D = 21 A		136		S
Dvnamic	Characteristics					
C _{iss}	Input Capacitance			3085	4105	pF
C _{oss}	Output Capacitance	$V_{DS} = 15 \text{ V}, \text{ V}_{GS} = 0 \text{ V},$		990	1315	pF
C _{rss}	Reverse Transfer Capacitance	_f = 1 MHz		75	115	pF
R _q	Gate Resistance			1.2	2.5	Ω
Switching	J Characteristics			15	26	ns
t _r	Rise Time	V _{DD} = 15 V, I _D = 21 A,		6	12	ns
t _{d(off)}	Turn-Off Delay Time	$V_{GS} = 10 \text{ V}, \text{ R}_{GEN} = 6 \Omega$		31	50	ns
t _f	Fall Time	-		5	10	ns
Q _g	Total Gate Charge	V _{GS} = 0 V to 10 V		40	56	nC
Q _g	Total Gate Charge	$V_{GS} = 0 \text{ V to } 4.5 \text{ V}$ $V_{DD} = 15 \text{ V},$ $I_D = 21 \text{ A}$		17	24	nC
Q _{gs}	Gate to Source Charge			9.8		nC
Q _{gd}	Gate to Drain "Miller" Charge	-		4.4		nC
*	urce Diode Characteristics	1		I		
	$V_{CS} = 0 V_{LS} = 2.1 A$			0.7	0.95	V
V _{SD}	Source to Drain Diode Forward Voltage	$V_{GS} = 0 V, I_S = 21 A$ (Note 2)		0.8	1.1	v
t _{rr}	Reverse Recovery Time			38	61	ns
Q _{rr}	Reverse Recovery Charge			19	34	nC
t _a	Reverse Recovery Fall Time	I _F = 21 A, di/dt = 100 A/μs		14		ns
t _b	Reverse Recovery Rise Time			24		ns
S	Softness (t _b /t _a)			1.7		
t _{rr}	Reverse Recovery Time	I _F = 21 A, di/dt = 300 A/μs		32	51	ns
Q _{rr}	Reverse Recovery Charge			34	54	nC
Notes : 1. R _{θJA} is determ the user's boa	ined with the device mounted on a 1in ² pad 2 oz copper pad rd design.	on a 1.5 x 1.5 in. board of FR-4 material. $R_{\theta JC}$ is	guaranteed	by design wh	ile R _{0CA} is de	etermined I




2. Pulse Test: Pulse Width < 300 $\mu s,$ Duty cycle < 2.0%.

3. E_{AS} of 144 mJ is based on starting T_J = 25 °C, L = 1 mH, I_{AS} = 17 A, V_{DD} = 27 V, V_{GS} = 10 V. 100% test at L = 0.3 mH, I_{AS} = 22 A.

4. As an N-ch device, the negative Vgs rating is for low duty cycle pulse occurrence only. No continuous rating is implied. ©2012 Fairchild Semiconductor Corporation 2 FDMS7670 Rev. D3

00000

FDMS7670 N-Channel PowerTrench[®] MOSFET



©2012 Fairchild Semiconductor Corporation FDMS7670 Rev. D3



- C_{iss}

Coss

Crss

10

100

125

SINGLE PULSE

R_{0JA} = 125 °C/W

100

= 25 °C


Т۸


10

1

150

30





1

V_{DS}, DRAIN to SOURCE VOLTAGE (V)

10

100

4

0.1

0.5

10⁻⁴

10


10

Figure 12. Single Pulse Maximum Power Dissipation

t, PULSE WIDTH (sec)

10⁻²

1000





ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC