

Is Now Part of




ON Semiconductor®


To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unavteries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or i, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor and is officers, employees, uniotificated use, even if such claim any manner.



■ High End Server/Workstation Vcore Low Side



MOSFET Maximum Ratings $T_A = 25^{\circ}C$ unless otherwise noted

Symbol	Parameter			Ratings	Units	
V _{DS}	Drain to Source Voltage		25	V		
V _{GS}	Gate to Source Voltage			12	V	
	Drain Current -Continuous (Package limited)	T _C = 25 °C		70		
I _D	-Continuous	T _A = 25 °C	(Note 1a)	30	Α	
	-Pulsed			150		
E _{AS}	Single Pulse Avalanche Energy		(Note 3)	79	mJ	
D	Power Dissipation	T _C = 25 °C		65	14/	
PD	Power Dissipation	T _A = 25 °C	(Note 1a)	2.5	W	
T _J , T _{STG}	Operating and Storage Junction Temperature Range			-55 to +150	°C	

Thermal Characteristics

Features

$R_{ ext{ heta}JC}$	Thermal Resistance, Junction to Case	T _C = 25 °C		1.9	°C/W
R_{\thetaJA}	Thermal Resistance, Junction to Ambient	T _A = 25 °C	(Note 1a)	50	0/11

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
05OD	FDMS8560S	Power 56	13"	12 mm	3000 units

November 2014

process.


Symbol	Parameter	Test Conditions	Min	Тур	Max	Units	
Off Chara	octeristics						
BV _{DSS}	Drain to Source Breakdown Voltage	I _D = 1 mA, V _{GS} = 0 V	25			V	
ΔBV _{DSS} 	Breakdown Voltage Temperature Coefficient	$I_D = 10$ mA, referenced to 25 °C		20		mV/°C	
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 20 V, V _{GS} = 0 V			500	μΑ	
I _{GSS}	Gate to Source Leakage Current	V_{GS} = +12 V/-8 V, V_{DS} = 0 V			±100	nA	
On Chara	cteristics						
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 1 \text{ mA}$	1.1	1.4	2.2	V	
$\Delta V_{GS(th)}$ ΔT_J	Gate to Source Threshold Voltage Temperature Coefficient	I _D = 10 mA, referenced to 25 °C		-3		mV/°C	
	Static Drain to Source On Resistance	V _{GS} = 10 V, I _D = 30 A		1.4	1.8	mΩ	
r _{DS(on)}		$V_{GS} = 4.5 \text{ V}, \text{ I}_{D} = 28 \text{ A}$		1.6	2.1		
		V_{GS} = 10 V, I_{D} = 30 A, T_{J} = 125 °C		2.1	2.8		
9 _{FS}	Forward Transconductance	V _{DS} = 5 V, I _D = 30 A		304		S	
C _{iss}	Characteristics Input Capacitance	V _{DS} = 13 V, V _{GS} = 0 V,		4350		pF	
C _{oss}	Output Capacitance	$v_{DS} = 13 v, v_{GS} = 0 v,$ 		1270		pF	
C _{rss}	Reverse Transfer Capacitance			138		pF	
R _g	Gate Resistance			0.8		Ω	
Switching	g Characteristics						
Switching t _{d(on)}	Turn-On Delay Time			13		ns	
		V _{DD} = 13 V, I _D = 30 A,		13 6		ns ns	
t _{d(on)}	Turn-On Delay Time	V _{DD} = 13 V, I _D = 30 A, V _{GS} = 10 V, R _{GEN} = 6 Ω					
t _{d(on)} t _r	Turn-On Delay Time Rise Time			6		ns	
t _{d(on)} t _r t _{d(off)}	Turn-On Delay Time Rise Time Turn-Off Delay Time	$V_{GS} = 10 \text{ V}, \text{ R}_{GEN} = 6 \Omega$ $V_{GS} = 0 \text{ V to } 10 \text{ V}$		6 45		ns ns	
t _{d(on)} t _r t _{d(off)} t _f	Turn-On Delay Time Rise Time Turn-Off Delay Time Fall Time	$V_{GS} = 10 \text{ V}, \text{ R}_{GEN} = 6 \Omega$ $V_{GS} = 0 \text{ V to } 10 \text{ V}$ $V_{GS} = 0 \text{ V to } 4.5 \text{ V} \text{ V}_{DD} = 13 \text{ V},$		6 45 5		ns ns ns	
t _{d(on)} t _r t _{d(off)} t _f Q _g	Turn-On Delay Time Rise Time Turn-Off Delay Time Fall Time Total Gate Charge	$V_{GS} = 10 \text{ V}, \text{ R}_{GEN} = 6 \Omega$		6 45 5 68		ns ns ns nC	
t _{d(on)} t _r t _{d(off)} t _f Q _g Q _g Q _{gs}	Turn-On Delay Time Rise Time Turn-Off Delay Time Fall Time Total Gate Charge Total Gate Charge	$V_{GS} = 10 \text{ V}, \text{ R}_{GEN} = 6 \Omega$ $V_{GS} = 0 \text{ V to } 10 \text{ V}$ $V_{GS} = 0 \text{ V to } 4.5 \text{ V} \text{ V}_{DD} = 13 \text{ V},$		6 45 5 68 32		ns ns ns nC nC	
t _{d(on)} t _r t _{d(off)} t _f Q _g Q _g Q _{gs} Q _{gd}	Turn-On Delay Time Rise Time Turn-Off Delay Time Fall Time Total Gate Charge Total Gate Charge Gate to Source Gate Charge	$V_{GS} = 10 \text{ V}, \text{ R}_{GEN} = 6 \Omega$ $V_{GS} = 0 \text{ V to } 10 \text{ V}$ $V_{GS} = 0 \text{ V to } 4.5 \text{ V} \text{ V}_{DD} = 13 \text{ V},$		6 45 5 68 32 8.2		ns ns nC nC nC	
t _{d(on)} t _r t _{d(off)} t _f Q _g Q _g Q _{gs} Q _{gd}	Turn-On Delay Time Rise Time Turn-Off Delay Time Fall Time Total Gate Charge Total Gate Charge Gate to Source Gate Charge Gate to Drain "Miller" Charge	$V_{GS} = 10 \text{ V}, \text{ R}_{GEN} = 6 \Omega$ $V_{GS} = 0 \text{ V to } 10 \text{ V}$ $V_{GS} = 0 \text{ V to } 4.5 \text{ V} \text{ V}_{DD} = 13 \text{ V},$		6 45 5 68 32 8.2	0.8	ns ns nC nC nC	


ain-Source Diode Characteristics							
SD	Source to Drain Diode Forward Voltage	$V_{GS} = 0 V, I_S = 2 A$ (Note 2)	0.6	0.8	V		
		$V_{GS} = 0 V, I_S = 30 A$ (Note 2)	0.8	1.2			
	Reverse Recovery Time	I _E = 30 A, di/dt = 300 A/μs	32		ns		
r	Reverse Recovery Charge	$F = 30 \text{ A}, \text{ u/ul} = 300 \text{ A/} \mu \text{s}$	41		nC		

Q_{rr} NOTES:

t_{rr}

1. R_{0JA} is determined with the device mounted on a FR-4 board using a specified pad of 2 oz copper as shown below. R_{0JC} is guaranteed by design while R_{0CA} is determined by the user's board design.








b 125 °C/W when mounted on a minimum pad of 2 oz copper.

3. E_{AS} of 79 mJ is based on starting T_J = 25 °C, L = 2.5 mH, I_{AS} = 8 A, V_{DD} = 23 V, V_{GS} = 10 V. 100% test at L = 0.1 mH, I_{AS} = 33.7 A.


©2012 Fairchild Semiconductor Corporation FDMS8560S Rev.D2

FDMS8560S N-Channel PowerTrench[®] SyncFETTM


FDMS8560S N-Channel PowerTrench[®] SyncFETTM



©2012 Fairchild Semiconductor Corporation FDMS8560S Rev.D2 www.fairchildsemi.com



FDMS8560S N-Channel PowerTrench[®] SyncFETTM



FDMS8560S N-Channel PowerTrench[®] SyncFETTM

Typical Characteristics (continued)

SyncFET[™] Schottky body diode Characteristics

Fairchild's SyncFETTM process embeds a Schottky diode in parallel with PowerTrench MOSFET. This diode exhibits similar characteristics to a discrete external Schottky diode in parallel with a MOSFET. Figure 14 shows the reverse recovery characteristic of the FDMS8560S.

Schottky barrier diodes exhibit significant leakage at high temperature and high reverse voltage. This will increase the power in the device.

T_{.1} = 125 °C

T_J = 100 °C

T_J = 25 °C

15

20

25

10⁻²

10⁻³

10⁻⁴

10⁻⁵

10⁻⁶

0




Figure 14. FDMS8560S SyncFETTM body diode reverse recovery characteristic

Figure 15. SyncFET[™] body diode reverse

V_{DS}, REVERSE VOLTAGE (V)

10

5

leakage versus drain-source voltage



ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC