

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild guestions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



May 2014

FDMA7670

Single N-Channel PowerTrench® MOSFET

30 V, 11 A, 15 mΩ

Features

- Max $r_{DS(on)} = 15 \text{ m}\Omega$ at $V_{GS} = 10 \text{ V}$, $I_D = 11 \text{ A}$
- \blacksquare Max $r_{DS(on)}$ = 22 m Ω at V_{GS} = 4.5 V, I_D = 9 A
- Low Profile 0.8 mm maximum in the new package MicroFET 2x2 mm
- Free from halogenated compounds and antimony oxides
- RoHS compliant





General Description

This device has been designed to provide maximum efficiency and thermal performance for synchronous buck converters. The low $r_{\text{DS(on)}}$ and gate charge provide excellent switching performance.

Application

■ DC - DC Buck Converters





MOSFET Maximum Ratings $T_A = 25$ °C unless otherwise noted

Symbol		Parameter		Ratings	Units
V_{DSS}	Drain to Source Voltage			30	V
V_{GSS}	Gate to Source Voltage			±20	V
1	Drain Current -Continuous	T _A = 25 °C	(Note 1a)	11	۸
'D	-Pulsed			24	_ A
P _D	Power Dissipation	T _A = 25 °C	(Note 1a)	2.4	w
	Power Dissipation	T _A = 25 °C	(Note 1b)	0.9	VV
T _J , T _{STG}	Operating and Storage Junction To	emperature Range		-55 to +150	°C

Thermal Characteristics

$R_{\theta JC}$	Thermal Resistance, Junction to Case	6.9	
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1a)	52	°C/W
R_{\thetaJA}	Thermal Resistance, Junction to Ambient (Note 1b)	145	

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
670	FDMA7670	MicroFET 2x2	7 "	12 mm	3000 units

Electrical Characteristics T_J = 25 °C unless otherwise noted

Symbol	Parameter Test Conditions		Min	Тур	Max	Units
Off Chara	octeristics					
BV _{DSS}	Drain to Source Breakdown Voltage	$I_D = 250 \mu A, V_{GS} = 0 V$	30			V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	I _D = 250 μA, referenced to 25 °C	15			mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 24 V, V _{GS} = 0 V			1	μА
I _{GSS}	Gate to Source Leakage Current	V _{GS} = 20 V, V _{DS} = 0 V			100	nA

On Characteristics

V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 250 \mu A$	1.0	2.0	3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I_D = 250 μ A, referenced to 25 °C		-6		mV/°C
		V _{GS} = 10 V, I _D = 11 A		10	15	
r _{DS(on)}	Static Drain to Source On Resistance	$V_{GS} = 4.5 \text{ V}, I_D = 9 \text{ A}$		14	22	mΩ
		V _{GS} = 10 V, I _D = 11 A, T _J = 125 °C		14	21	
9 _{FS}	Forward Transconductance	V _{DS} = 5 V, I _D = 11 A		36		S

Dynamic Characteristics

C _{iss}	Input Capacitance	V 45 V V 0 V	1020	1360	pF
Coss	Output Capacitance	V _{DS} = 15 V, V _{GS} = 0 V — f = 1.0 MHz	315	415	pF
C _{rss}	Reverse Transfer Capacitance	1 = 1.0 101112	35	55	pF
R_{q}	Gate Resistance		1.7		Ω

Switching Characteristics

t _{d(on)}	Turn-On Delay Time				8	15	ns
t _r	Rise Time		V _{DD} = 15 V, I _D = 11 A		3	10	ns
t _{d(off)}	Turn-Off Delay Time	V _{GS} = 10 V, R _{GEN} =	$V_{GS} = 10 \text{ V}, R_{GEN} = 6 \Omega$		19	34	ns
t _f	Fall Time				3	10	ns
Q _q	Total Gate Charge	V _{GS} = 0 V to 10 V			16	22	nC
Q_q	Total Gate Charge	V _{GS} = 0 V to 4.5 V	V _{DD} = 15 V,		8	10	nC
Q _{gs}	Gate to Source Gate Charge		I _D = 11 A		3.0		nC
Q_{qd}	Gate to Drain "Miller" Charge				2.2		nC

Drain-Source Diode Characteristics

I _S	Maximum Continuous Drain-Source Diode Forward Current				2	Α
V_{SD}	Source to Drain Diode Forward Voltage	$V_{GS} = 0 \text{ V}, I_{S} = 2 \text{ A}$	(Note 2)	0.8	1.2	V
t _{rr}	Reverse Recovery Time	L = 11 Λ di/dt = 100 Λ/μς		21	33	ns
Q _{rr}	Reverse Recovery Charge	$I_F = 11 \text{ A, di/dt} = 100 \text{ A/}\mu\text{s}$		6	12	nC

NOTES

1. R_{0JA} is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. R_{0JC} is guaranteed by design while R_{0CA} is determined by the user's board design.



a. 52 °C/W when mounted on a 1 in² pad of 2 oz copper.



 b. 145 °C/W when mounted on a minimum pad of 2 oz copper.

^{2.} Pulse Test: Pulse Width < 300 μ s, Duty cycle < 2.0%.

Typical Characteristics T_{.I} = 25°C unless otherwise noted




Figure 1. On-Region Characteristics




Figure 3. Normalized On-Resistance vs Junction Temperature




Figure 5. Transfer Characteristics




Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage




Figure 4. On-Resistance vs Gate to Source Voltage




Figure 6. Source to Drain Diode Forward Voltage vs Source Current

Typical Characteristics T_J = 25°C unless otherwise noted




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs Drain to Source Voltage




Figure 9. Forward Bias Safe Operating Area




Figure 10. Single Pulse Maximum Power Dissipation







Figure 11. Transient Thermal Response Curve









NOTES:

- A. PACKAGE DOES NOT FULLY CONFORM TO JEDEC MO-229 REGISTRATION
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 2009.
- D. LAND PATTERN RECOMMENDATION IS EXISTING INDUSTRY LAND PATTERN.
- E. DRAWING FILENAME: MKT-MLP06Lrev4.







ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdt/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and exp

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative