onsemi

<u>MOSFET</u> – Power, N-Channel, UltraFET

55 V, 15 A, 90 m Ω

FDMC15N06

Description

These N-Channel power MOSFETs are manufactured using the innovative UltraFET process. This advanced process technology achieves the lowest possible on-resistance per silicon area, resulting in outstanding performance.

This device is capable of withstanding high energy in the avalanche mode and the diode exhibits very low reverse recovery time and stored charge. It was designed for use in applications where power efficiency is important, such as switching regulators, switching converters, motor drivers, relay drivers, low voltage bus switches, and power management in portable and battery-operated products.

Features

- $R_{DS(on)} = 75 \text{ m}\Omega \text{ (Typ.)} @ V_{GS} = 10 \text{ V}, I_D = 15 \text{ A}$
- 100% Avalanche Tested
- These Device is Pb-Free and RoHS Compliant



WDFN8 3.3X3.3, 0.65P CASE 511DQ



MARKING DIAGRAM



Z = Assembly Plant Code

XY = Date Code (Year & Week)

KK = Lot Traceability Code 15N06 = Specific Device Code

ORDERING INFORMATION

Device	Package	Shipping [†]
FDMC15N06	WDFN8 (Pb-Free)	3000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, <u>BRD8011/D</u>.

Symbol	Parameter	Ratings	Unit
V _{DSS}	Drain to Source Voltage	55	V
V _{GSS}	Gate to Source Voltage	±20	V
Ι _D	Drain Current -Continuous (T_C = 25°C) -Continuous (T_C = 100°C) -Continuous (T_A = 25°C) (Note 3)	15 9 2.4	A
I _{DM}	Drain Current -Pulsed (Note 4)	60	A
E _{AS}	Single Pulse Avalanche Energy (Note 5)	36	mJ
I _{AR}	Avalanche Energy	15	А
E _{AR}	Repetitive Avalanche Energy	3.5	mJ
P _D	Power Dissipation $(T_C = 25^{\circ}C)$ $(T_A = 25^{\circ}C)$	35 2.3	W
T _J , T _{STG}	Operating and Storage Temperature Range	–55 to +150	°C
TL	Maximum Lead Temperature for Soldering, 1/8" from Case for 5 Seconds	300	°C

MOSFET MAXIMUM RATINGS $T_C = 25^{\circ}C$ unless otherwise noted

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case, Max	3.5	°C/W
R _{θJA}	Thermal Resistance, Junction to Ambient, Max (Note 3)	53	

ELECTRICAL CHARACTERISTICS Tc = 25 °C unless otherwise noted.

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit	
Off Characteristics							
BV _{DSS}	Drain to Source Breakdown Voltage	I_D = 250 $\mu A,V_{GS}$ = 0 V, T_C = 25 $^\circ C$	55	-	-	V	
$\frac{\Delta \text{BV}_{\text{DSS}}}{\Delta \text{T}_{\text{J}}}$	Breakdown Voltage Temperature Coefficient	I_D = 250 µA, Referenced to 25°C	-	70	-	V/°C	
I _{DSS}	Zero Gate Voltage Drain Current	V_{DS} = 50 V, V_{GS} = 0 V V_{DS} = 45 V, T_{C} = 150 °C	-	-	1 250	μΑ	
I _{GSS}	Gate to Body Leakage Current $V_{GS} = \pm 20 \text{ V}, \text{ V}_{DS} = 0 \text{ V}$		-	-	±100	nA	
On Characteri	On Characteristics						
V _{GS(th)}	Gate to Source Threshold Voltage	V_{GS} = V_{DS} , I_D = 250 μ A	2.0	-	4.0	V	
R _{DS(on)}	Static Drain to Source On Resistance	V _{GS} = 10 V, I _D = 15 A	-	0.075	0.090	Ω	
9fs	Forward Transconductance $V_{DS} = 20 \text{ V}, I_D = 15 \text{ A}$		-	5	-	S	
Dynamic Char	Dynamic Characteristics						
C _{iss}	Input Capacitance	V_{DS} = 25 V, V_{GS} = 0 V, f = 1 MHz	-	265	350	pF	
C _{oss}	Output Capacitance		-	97	130	pF	
C _{rss}	Reverse Transfer Capacitance		_	28	42	pF	
Q _{g(tot)}	Total Gate Charge at 10 V	V _{DS} = 30 V, I _D = 15 A,	-	8.8	11.5	nC	
Q _{gs}	Gate to Source Gate Charge	V _{GS} = 10 V (Note 4)	-	1.7	-	nC	
Q _{gd}	Gate to Drain "Miller" Charge		_	3.6	-	nC	

ELECTRICAL CHARACTERISTICS Tc = 25 °C unless otherwise noted.(continued)

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
Switching Cha	Switching Characteristics					
t _{d(on)}	Turn-On Delay Time	$V_{DD} = 30 \text{ V}, \text{ I}_{D} = 15 \text{ A}, V_{GS} = 10 \text{ V}, \text{ R}_{G} = 25 \Omega \text{ (Note 6)}$	-	9.5	29	ns
t _r	Turn–On Rise Time		-	36.5	83	ns
t _{d(off)}	Turn-Off Delay Time		-	22.5	55	ns
t _f	Turn-Off Fall Time		-	22	54	ns

Drain-Source Diode Characteristics

۱ _S	I _S Maximum Continuous Drain to Source Diode Forward Current		-	-	15	А
			-	-	60	А
I _{SM}	Maximum Pulsed Drain to Source Diode Forward Current		-	-	1.25	V
V_{SD}	Drain to Source Diode Forward Voltage	V _{GS} = 0 V, I _{SD} = 15 A				
t _{rr}	Reverse Recovery Time	$V_{GS} = 0 V, I_{SD} = 15 A,$	-	30	-	ns
Q _{rr}	Reverse Recovery Charge	$d_{F}/dt = 100 A_{\mu}s$ (Note 7)	_	35	-	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 3. $R_{\theta JA}$ is determined with the device mounted on a 1 in² oz. copper pad on a 1.5 x 1.5 in. board of FR-4 material $R_{\theta JC}$ is guaranteed by design

while $R_{\theta CA}$ is determined by the user's board design.



a. 53 °C/W when mounted on a 1 in² pad of 2 oz copper

b.125 °C/W when mounted on a minimum pad of 2 oz copper



TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS (CONTINUED)





Figure 14. Unclamped Inductive Switching Test Circuit & Waveforms







© Semiconductor Components Industries, LLC, 2019

WDFN8 3.3x3.3, 0.65P CASE 511DQ ISSUE 0

DATE 31 OCT 2016



- A. PACKAGE DOES NOT FULLY CONFORM TO
- JEDEC REGISTRATION MO-240.
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 2009.
- D. LAND PATTERN RECOMMENDATION IS EXISTING INDUSTRY LAND PATTERN
- E. DIMENSIONS DO NOT INCLUDE BURRS OR MOLD FLASH. BURRS OR MOLD FLASH SHALL NOT EXCEED 0.10MM.

DOCUMENT NUMBER:	98AON13648G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	WDFN8 3.3X3.3, 0.65P		PAGE 2 OF 2	

ON Semiconductor and una are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the right of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>