

ON Semiconductor

Is Now

onsemi™

To learn more about onsemi™, please visit our website at
www.onsemi.com

onsemi and **onsemi** and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi** product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner. Other names and brands may be claimed as the property of others.

MOSFET - Dual N-Channel, Asymmetric, POWERTRENCH[®] Power Clip 25 V

FDPC8016S

General Description

This device includes two specialized N-Channel MOSFETs in a dual package. The switch node has been internally connected to enable easy placement and routing of synchronous buck converters. The control MOSFET (Q1) and synchronous SyncFET™ (Q2) have been designed to provide optimal power efficiency.

Features

Q1: N-Channel

- Max $R_{DS(on)}$ = 3.8 mΩ at $V_{GS} = 10\text{ V}$, $I_D = 20\text{ A}$
- Max $R_{DS(on)}$ = 4.7 mΩ at $V_{GS} = 4.5\text{ V}$, $I_D = 18\text{ A}$

Q2: N-Channel

- Max $R_{DS(on)}$ = 1.4 mΩ at $V_{GS} = 10\text{ V}$, $I_D = 35\text{ A}$
- Max $R_{DS(on)}$ = 1.7 mΩ at $V_{GS} = 4.5\text{ V}$, $I_D = 32\text{ A}$
- Low Inductance Packaging Shortens Rise/Fall Times, Resulting in Lower Switching Losses
- MOSFET Integration Enables Optimum Layout for Lower Circuit Inductance and Reduced Switch Node Ringing
- These Devices are Pb-Free and are RoHS Compliant

Applications


- Computing
- Communications
- General Purpose Point of Load




ON Semiconductor[®]

www.onsemi.com

ELECTRICAL CONNECTION




N-Channel MOSFET




Power Clip 56
(PGFN8 5x6)
CASE 483AR

PIN ASSIGNMENT



*PAD10 V+(HSD)

MARKING DIAGRAM



- \$Y = ON Semiconductor Logo
- &Z = Assembly Plant Code
- &3 = Numeric Date Code
- &K = Lot Code
- 05OD 15OD = Specific Device Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

FDPC8016S

PINOUT DESCRIPTION

Pin	Name	Description	Pin	Name	Description	Pin	Name	Description
1	HSG	High Side Gate	3, 4, 10	V+(HSD)	High Side Drain	8	LSG	Low Side Gate
2	GR	Gate Return	5, 6, 7	SW	Switching Node, Low Side Drain	9	GND(LSS)	Low Side Source

MOSFET MAXIMUM RATINGS (T_A = 25°C, Unless otherwise specified)

Symbol	Parameter	Q1	Q2	Unit
V _{DS}	Drain to Source Voltage	25 (Note 5)	25 (Note 5)	V
V _{GS}	Gate to Source Voltage	±12	±12	V
I _D	Drain Current Continuous (T _C = 25°C) Continuous (T _A = 25°C) Pulsed (T _A = 25°C) (Note 4)	60 20 (Note 1a) 75	100 35 (Note 1b) 140	A
E _{AS}	Single Pulsed Avalanche Energy (Note 3)	73	216	mJ
P _D	Power Dissipation for Single Operation (T _C = 25°C) (T _A = 25°C)	21 2.1 (Note 1a)	42 2.3 (Note 1b)	W
T _J , T _{STG}	Operating and Storage Junction Temperature Range	-55 to +150		°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

Symbol	Parameter	Q1	Q2	Unit
R _{θJC}	Thermal Resistance, Junction to Case	6.0	3.0	°C/W
R _{θJA}	Thermal Resistance, Junction to Ambient	60 (Note 1a)	55 (Note 1b)	°C/W
R _{θJA}	Thermal Resistance, Junction to Ambient	130 (Note 1c)	120 (Note 1d)	°C/W

PACKAGE MARKING AND ORDERING INFORMATION

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
05OD/15OD	FDPC8016S	Power Clip 56	13"	12 mm	3,000 Units

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Type	Min	Typ	Max	Unit
--------	-----------	-----------------	------	-----	-----	-----	------

OFF CHARACTERISTICS

BV _{DSS}	Drain to Source Breakdown Voltage	I _D = 250 μA, V _{GS} = 0 V I _D = 1 mA, V _{GS} = 0 V	Q1 Q2	25 25	- -	- -	V
ΔBV _{DSS} /ΔT _J	Breakdown Voltage Temperature Coefficient	I _D = 250 μA, referenced to 25°C I _D = 10 mA, referenced to 25°C	Q1 Q2	- -	24 28	- -	mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 20 V, V _{GS} = 0 V V _{DS} = 20 V, V _{GS} = 0 V	Q1 Q2	- -	- -	1 500	μA
I _{GSS}	Gate to Source Leakage Current, Forward	V _{GS} = 12 V / -8 V, V _{DS} = 0 V V _{GS} = 12 V / -8 V, V _{DS} = 0 V	Q1 Q2	- -	- -	±100 ±100	nA nA

ON CHARACTERISTICS

V _{GS(th)}	Gate to Source Threshold Voltage	V _{GS} = V _{DS} , I _D = 250 μA V _{GS} = V _{DS} , I _D = 1 mA	Q1 Q2	0.8 1.0	1.3 1.5	2.5 2.5	V
ΔV _{GS(th)} /ΔT _J	Gate to Source Threshold Voltage Temperature Coefficient	I _D = 250 μA, referenced to 25°C I _D = 10 mA, referenced to 25°C	Q1 Q2	- -	-4 -3	- -	mV/°C

FDPC8016S

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Type	Min	Typ	Max	Unit
--------	-----------	-----------------	------	-----	-----	-----	------

ON CHARACTERISTICS

R _{DS(on)}	Drain to Source On Resistance	V _{GS} = 10 V, I _D = 20 A V _{GS} = 4.5 V, I _D = 18 A V _{GS} = 10 V, I _D = 20 A, T _J = 125°C	Q1	–	2.8	3.8	mΩ
		Q2	–	3.4	4.7		
		V _{GS} = 10 V, I _D = 35 A V _{GS} = 4.5 V, I _D = 32 A V _{GS} = 10 V, I _D = 35 A, T _J = 125°C	Q1	–	1.1	1.4	
			Q2	–	1.3	1.7	
g _{FS}	Forward Transconductance	V _{DS} = 5 V, I _D = 20 A V _{DS} = 5 V, I _D = 35 A	Q1	–	182	–	S
			Q2	–	241	–	

DYNAMIC CHARACTERISTICS

C _{iss}	Input Capacitance	Q1: V _{DS} = 13 V, V _{GS} = 0 V, f = 1 MHz	Q1	–	1695	2375	pF
			Q2	–	4715	6600	
C _{oss}	Output Capacitance	Q2: V _{DS} = 13 V, V _{GS} = 0 V, f = 1 MHz	Q1	–	495	710	pF
			Q2	–	1195	1675	
C _{rss}	Reverse Transfer Capacitance		Q1	–	54	100	pF
			Q2	–	159	290	
R _g	Gate Resistance		Q1	0.1	0.4	1.2	Ω
			Q2	0.1	0.5	1.5	

SWITCHING CHARACTERISTICS

t _{d(on)}	Turn-On Delay Time	Q1: V _{DD} = 13 V, I _D = 20 A, R _{GEN} = 6 Ω	Q1	–	8	16	ns
			Q2	–	13	24	
t _r	Rise Time	Q2: V _{DD} = 13 V, I _D = 35 A, R _{GEN} = 6 Ω	Q1	–	2	10	ns
			Q2	–	4	10	
t _{d(off)}	Turn-Off Delay Time		Q1	–	24	38	ns
			Q2	–	38	61	
t _f	Fall Time		Q1	–	2	10	ns
			Q2	–	3	10	
Q _g	Total Gate Charge	V _{GS} = 0 V to 10 V Q1: V _{DD} = 13 V, I _D = 20 A Q2: V _{DD} = 13 V, I _D = 35 A	Q1	–	25	35	nC
			Q2	–	67	94	
Q _g	Total Gate Charge	V _{GS} = 0 V to 4.5 V Q1: V _{DD} = 13 V, I _D = 20 A Q2: V _{DD} = 13 V, I _D = 35 A	Q1	–	11	16	nC
			Q2	–	31	44	
Q _{gs}	Gate to Source Gate Charge	Q1: V _{DD} = 13 V, I _D = 20 A Q2: V _{DD} = 13 V, I _D = 35 A	Q1	–	3.4	–	nC
			Q2	–	10	–	
Q _{gd}	Gate to Drain "Miller" Charge	Q1: V _{DD} = 13 V, I _D = 20 A Q2: V _{DD} = 13 V, I _D = 35 A	Q1	–	2.2	–	nC
			Q2	–	6.3	–	

DRAIN-SOURCE DIODE CHARACTERISTICS


V _{SD}	Source to Drain Diode Forward Voltage	V _{GS} = 0 V, I _S = 20 A V _{GS} = 0 V, I _S = 35 A (Note 2)	Q1	–	0.8	1.2	V
			Q2	–	0.8	1.2	
t _{rr}	Reverse Recovery Time	Q1: I _F = 20 A, di/dt = 100 A/μs Q2: I _F = 35 A, di/dt = 200 A/μs	Q1	–	25	40	ns
			Q2	–	33	53	
Q _{rr}	Reverse Recovery Charge		Q1	–	10	20	nC
			Q2	–	31	50	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.


NOTES:

1. R_{θJA} is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 × 1.5 in. board of FR-4 material. R_{θCA} is determined by the user's board design.


FDPC8016S




a) 60°C/W when mounted on a 1 in² pad of 2 oz copper.



b) 55°C/W when mounted on a 1 in² pad of 2 oz copper.



c) 130°C/W when mounted on a minimum pad of 2 oz copper.



d) 120°C/W when mounted on a minimum pad of 2 oz copper.

2. Pulse Test: Pulse Width < 300 μs, Duty cycle < 2.0%.

3. Q1:

E_{AS} of 73 mJ is based on starting $T_J = 25^\circ\text{C}$; N-ch: $L = 3\text{ mH}$, $I_{AS} = 7\text{ A}$, $V_{DD} = 30\text{ V}$, $V_{GS} = 10\text{ V}$, 100% tested at $L = 0.1\text{ mH}$, $I_{AS} = 24\text{ A}$.

Q2:

E_{AS} of 216 mJ is based on starting $T_J = 25^\circ\text{C}$; N-ch: $L = 3\text{ mH}$, $I_{AS} = 12\text{ A}$, $V_{DD} = 25\text{ V}$, $V_{GS} = 10\text{ V}$, 100% tested at $L = 0.1\text{ mH}$, $I_{AS} = 39\text{ A}$.

4. Pulsed I_d limited by junction temperature, $t_d \leq 10\ \mu\text{s}$. Please refer to SOA curve for more details.

5. The continuous V_{DS} rating is 25 V; However, a pulse of 30 V peak voltage for no longer than 100 ns duration at 600 KHz frequency can be applied.

TYPICAL CHARACTERISTICS (Q1 N-Channel)

($T_J = 25^\circ\text{C}$ unless otherwise noted)




Figure 1. On-Region Characteristics




Figure 2. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 3. Normalized On-Resistance vs. Junction Temperature




Figure 4. On-Resistance vs. Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs. Source Current

TYPICAL CHARACTERISTICS (Q1 N-Channel)

($T_J = 25^\circ\text{C}$ unless otherwise noted)




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs. Drain to Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Maximum Continuous Drain Current vs. Case Temperature




Figure 11. Forward Bias Safe Operating Area




Figure 12. Single Pulse Maximum Power Dissipation

FDPC8016S

TYPICAL CHARACTERISTICS (Q1 N-Channel)

($T_J = 25^\circ\text{C}$ unless otherwise noted)




Figure 13. Junction-to-Case Transient Thermal Response Curve

TYPICAL CHARACTERISTICS (Q2 N-Channel)

($T_J = 25^\circ\text{C}$ unless otherwise noted)




Figure 14. On-Region Characteristics




Figure 15. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 16. Normalized On-Resistance vs. Junction Temperature




Figure 17. On-Resistance vs. Gate to Source Voltage




Figure 18. Transfer Characteristics




Figure 19. Source to Drain Diode Forward Voltage vs. Source Current

FDPC8016S

TYPICAL CHARACTERISTICS (Q2 N-Channel)

($T_J = 25^\circ\text{C}$ unless otherwise noted)




Figure 20. Gate Charge Characteristics




Figure 21. Capacitance vs. Drain to Source Voltage




Figure 22. Unclamped Inductive Switching Capability




Figure 23. Maximum Continuous Drain Current vs. Case Temperature




Figure 24. Forward Bias Safe Operating Area




Figure 25. Single Pulse Maximum Power Dissipation

TYPICAL CHARACTERISTICS (Q2 N-Channel)

($T_J = 25^\circ\text{C}$ unless otherwise noted)




Figure 26. Junction-to-Case Transient Thermal Response Curve

FDPC8016S

TYPICAL CHARACTERISTICS (continued)

SyncFET Schottky Body Diode Characteristics

ON's SyncFET process embeds a Schottky diode in parallel with PowerTrench MOSFET. This diode exhibits similar characteristics to a discrete external Schottky diode in parallel with a MOSFET. Figure 27 shows the reverse recovery characteristic of the FDPC8016S.

Schottky barrier diodes exhibit significant leakage at high temperature and high reverse voltage. This will increase the power in the device.




Figure 27. FDPC8016S SyncFET Body Diode Reverse Recovery Characteristic




Figure 28. SyncFET Body Diode Reverse Leakage vs. Drain-Source Voltage