onsemi

MOSFET – N-Channel, POWERTRENCH[®]

40 V, 20 A, 5.8 m Ω

FDMC8462

General Description

This N-Channel MOSFET is produced using **onsemi**'s advanced POWERTRENCH process that has been especially tailored to minimize the on-state resistance and yet maintain superior switching performance.

Features

- Max $r_{DS(on)} = 5.8 \text{ m}\Omega$ at $V_{GS} = 10 \text{ V}$, $I_D = 13.5 \text{ A}$ Max $r_{DS(on)} = 8.0 \text{ m}\Omega$ at $V_{GS} = 4.5 \text{ V}$, $I_D = 11.8 \text{ A}$
- Low Profile 1 mm Max in Power 33
- 100% UIL Tested
- Pb-Free, Halide Free and RoHS Compliant

Applications

• DC – DC Conversion

ABSOLUTE MAXIMUM RATINGS (T_A = 25°C unless otherwise noted)

Symbol	Parameter	Value	Unit
V _{DS}	Drain to Source Voltage	40	V
V _{GS}	Gate to Source Voltage	±20	V
ID	$ \begin{array}{ll} \mbox{Drain Current} & & \\ - \mbox{ Continuous (Package Limited)} & T_C = 25^\circ C \\ - \mbox{ Continuous (Silicon Limited)} & T_C = 25^\circ C \\ - \mbox{ Continuous (Note 1a)} & T_A = 25^\circ C \\ - \mbox{ Pulsed} & \end{array} $	20 64 14 50	A
E _{AS}	Single Pulse Avalanche Energy (Note 3)	216	mJ
PD	$\begin{array}{ll} \mbox{Power Dissipation} & T_{C} = 25^{\circ}C \\ \mbox{Power Dissipation (Note 1a)} & T_{A} = 25^{\circ}C \end{array}$	41 2.0	W
T _J , T _{STG}	Operating and Storage Junction Temperature Range	–55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


THERMAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case	3	°C/W
$R_{ hetaJA}$	Thermal Resistance, Junction to Ambient (Note 1a)	53	°C/W

V _{DS} r _{DS(ON)} MAX		I _D MAX
40 V	5.8 mΩ @ 10 V	20 A
	8.0 mΩ @ 4.5 V	








N-Channel MOSFET

MARKING DIAGRAM



ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.


ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
OFF CHAR	ACTERISTICS					
BV_{DSS}	Drain to Source Breakdown Voltage	$I_D = 250 \ \mu A, \ V_{GS} = 0 \ V$	40	-	-	V
$\frac{\Delta \text{BV}_{\text{DSS}}}{\Delta \text{T}_{\text{J}}}$	Breakdown Voltage Temperature Coefficient	I_D = 250 µA, Referenced to 25°C	_	31	_	mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{GS} = 0 V, V _{DS} = 32 V	-	-	1	μA
I _{GSS}	Gate to Source Leakage Current	$V_{GS} = \pm 20 \text{ V}, V_{DS} = 0 \text{ V}$	-	-	±100	nA
ON CHARA	ACTERISTICS					
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_{D} = 250 \ \mu A$	1.0	2.0	3.0	V
$\frac{\Delta V_{\text{GS(th)}}}{\Delta T_{\text{J}}}$	Gate to Source Threshold Voltage Temperature Coefficient	I_D = 250 µA, Referenced to 25°C	-	-6.6	-	mV/°C
r _{DS(on)}	Static Drain to Source On-Resistance	$ \begin{array}{l} V_{GS} = 10 \text{ V, } I_D = 13.5 \text{ A} \\ V_{GS} = 4.5 \text{ V, } I_D = 11.8 \text{ A} \\ V_{GS} = 10 \text{ V, } I_D = 13.5 \text{ A, } T_J = 125^\circ \text{C} \end{array} $		4.7 6.4 7.1	5.8 8.0 9.3	mΩ
9 FS	Forward Transconductance	V _{DD} = 5 V, I _D = 13.5 A	-	60	_	S
DYNAMIC	CHARACTERISTICS					
C _{iss}	Input Capacitance	V _{DS} = 20 V, V _{GS} = 0 V, f = 1 MHz		2000	2660	pF
Coss	Output Capacitance			545	725	pF
C _{rss}	Reverse Transfer Capacitance		-	80	120	pF
Rg	Gate Resistance	f = 1 MHz	-	2.7	-	Ω
SWITCHIN	G CHARACTERISTICS					
t _{d(on)}	Turn–On Delay Time	$V_{DD} = 20 \text{ V, } I_D = 13.5 \text{ A,}$ $V_{GS} = 10 \text{ V, } R_{GEN} = 6 \Omega$		12	21	ns
t _r	Rise Time			4	10	ns
t _{d(off)}	Turn–Off Delay Time		-	27	43	ns
t _f	Fall Time		-	3	10	ns
Qg	Total Gate Charge	V_{GS} = 0 V to 10 V, V_{DD} = 20 V, I_{D} = 13.5 A	-	30	43	nC
		V_{GS} = 0 V to 4.5 V, V_{DD} = 20 V, I_{D} = 13.5 A	-	15	21	nC
Q _{gs}	Gate to Source Charge	V _{DD} = 20 V, I _D = 13.5 A	1	6	-	nC
Q _{gd}	Gate to Drain "Miller" Charge		-	5	-	nC
DRAIN-SO	URCE DIODE CHARACTERISTICS					
V_{SD}	Source to Drain Diode Forward	V _{GS} = 0 V, I _S = 13.5 A (Note 2)	-	0.8	1.3	V
	Voltage	V _{GS} = 0 V, I _S = 1.7 A (Note 2)	-	0.7	1.2	
t _{rr}	Reverse Recovery Time	I _F = 13.5 A, di/dt = 100 A/μs	_	35	57	ns
Q _{rr}	Reverse Recovery Charge		-	20	32	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

NOTES:

1. $R_{\theta JA}$ is determined with the device mounted on a 1in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.



a) 53°C/W when mounted on a 1 in² pad of 2 oz copper


b) 125°C/W when mounted on a minimum pad of 2 oz copper




- 2. Pulse Test: Pulse Width < 300 μ s, Duty Cycle < 2.0%.
- 3. Starting T_J = 25°C; N–ch: L = 3 mH, I_{AS} = 12 A, V_{DD} = 40 V, V_{GS} = 10 V.

TYPICAL CHARACTERISTICS

(T_J = 25°C unless otherwise noted)








Forward Voltage vs. Source Current


TYPICAL CHARACTERISTICS (continued)


(T_J = 25°C unless otherwise noted)

















Figure 8. Capacitance vs. Drain to Source Voltage




Figure 10. Maximum Continuous Drain Current vs Case Temperature




Figure 12. Single Pulse Maximum Power Dissipation

TYPICAL CHARACTERISTICS (continued)

(T_J = 25°C unless otherwise noted)




Figure 13. Transient Thermal Response Curve

PACKAGE MARKING AND ORDERING INFORMATION

Device	Device Marking	Package Type	Reel Size	Tape Width	Shipping [†]
FDMC8462	FDMC8462	PQFN8 3.3 x 3.3, 0.65P (Power 33) (Pb–Free/Halide Free)	13"	12 mm	3000 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, <u>BRD8011/D</u>.

POWERTRENCH is a registered trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.

DUDSem

MAX.

1.10

0.05

0.37

3.40

2.37

0.62


3.40

1.70

0.30

0.49

0.50



DOCUMENT NUMBER:	98AON13660G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.				
DESCRIPTION:	: PQFN8 3.3X3.3, 0.65P		PAGE 1 OF 1			
onsemi and ONSEMi. are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.						

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>