ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari





40V N-Channel PowerTrench[®] MOSFET

General Description


This N-Channel MOSFET has been designed specifically to improve the overall efficiency of DC/DC converters using either synchronous or conventional switching PWM controllers. It has been optimized for low gate charge, low $R_{DS(ON)}$ and fast switching speed.


Applications

DC/DC converter

Features

- 10.8 A, 40 V. $R_{\text{DS(ON)}}$ = 12 m Ω @ V_{GS} = 10 V
- Low gate charge (29 nC)
- High performance trench technology for extremely low $R_{\text{DS}(\text{ON})}$
- High power and current handling capability





Absolute Maximum Ratings $T_A=25^{\circ}C$ unless otherwise noted

Symbol	Parameter		Ratings	Units
V _{DSS}	Drain-Source Voltage		40	V
V _{GSS}	Gate-Source Voltage		+30/-20	V
I _D	Drain Current – Continuous	(Note 1a)	10.8	А
	– Pulsed		45	
PD	Power Dissipation for Single Operation	(Note 1a)	2.5	W
		(Note 1b)	1.4	
		(Note 1c)	1.2	
T _J , T _{STG}	Operating and Storage Junction Temperat	ure Range	-55 to +175	°C
Therma	I Characteristics	·		·
Raia	Thermal Resistance Junction-to-Ambient	(Note 1a)	50	°C/W

$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	(Note 1a)	50	°C/W
R _{eJA}	Thermal Resistance, Junction-to-Ambient	(Note 1c)	125	°C/W
$R_{ ext{ heta}JC}$	Thermal Resistance, Junction-to-Case	(Note 1)	25	°C/W

Package Marking and Ordering Information

Device Marking	Device	Reel Size	Tape width	Quantity
FDS4480	FDS4480	13"	12mm	2500 units
		•	•	


©2002 Semiconductor Components Industries, LLC. September-2017, Rev 4

	Test Conditions	Min	Тур	Max	Units
urce Avalanche Ratings (Note 2	2)				
Drain-Source Avalanche Energy	Single Pulse, V _{DD} =40V, I _D =10.8A			240	mJ
Drain-Source Avalanche Current				10.8	А
cteristics					
Drain–Source Breakdown Voltage	$V_{GS} = 0 V$, $I_{D} = 250 \mu A$	40			V
Breakdown Voltage Temperature Coefficient	I_D = 250 µA, Referenced to 25°C		42		mV/°C
Zero Gate Voltage Drain Current	$V_{\text{DS}} = 32 \text{ V}, V_{\text{GS}} = 0 \text{ V}$			1	μΑ
Gate–Body Leakage, Forward	$V_{GS}=30~V, ~~V_{DS}=0~V$			100	nA
Gate–Body Leakage, Reverse	$V_{GS} = -20 \text{ V}, V_{DS} = 0 \text{ V}$			-100	nA
Cteristics (Note 2)					
Gate Threshold Voltage	$V_{DS} = V_{GS}$, $I_D = 250 \ \mu A$	2	3.9	5	V
Gate Threshold Voltage Temperature Coefficient	$I_D = 250 \ \mu$ A, Referenced to 25° C		-8		mV/°C
Static Drain–Source On–Resistance			8 13	12 21	mΩ
On-State Drain Current	$V_{GS}=10~V, V_{DS}=5~V$	22			Α
Forward Transconductance	$V_{DS} = 10 \text{ V}, I_D = 10.8 \text{ A}$		36		S
Characteristics					
Input Capacitance	$V_{DS} = 20 V$, $V_{CS} = 0 V$.		1686		pF
Output Capacitance	f = 1.0 MHz		384		pF
Reverse Transfer Capacitance	1		185		pF
1 Characteristics (Note 2)	•		•		
·	$V_{DD} = 20 V_{c}$ $I_{D} = 1 A_{c}$		12	22	ns
Turn–On Rise Time	$V_{GS} = 10$ V, $R_{GEN} = 6 \Omega$		9	18	ns
Turn–Off Delay Time	1		30	48	ns
Turn–Off Fall Time			15	27	ns
Total Gate Charge			29	41	nC
Gate-Source Charge			8.7		nC
Gate-Drain Charge			8.0		nC
	Drain–Source Breakdown Voltage Breakdown Voltage Temperature Coefficient Zero Gate Voltage Drain Current Gate–Body Leakage, Forward Gate–Body Leakage, Reverse Cteristics (Note 2) Gate Threshold Voltage Gate Characteristics (Note 2) Furn–On Delay Time Furn–On Rise Time Furn–Off Delay Time Furn–Off Fall Time Gate Charge Gate–Source Charge	Drain-Source Breakdown Voltage $V_{GS} = 0 \text{ V}$, $I_D = 250 \mu\text{A}$ Breakdown Voltage Temperature Coefficient $I_D = 250 \mu\text{A}$, Referenced to 25°C Zero Gate Voltage Drain Current $V_{DS} = 32 \text{ V}$, $V_{GS} = 0 \text{ V}$ Gate-Body Leakage, Forward $V_{GS} = 30 \text{ V}$, $V_{DS} = 0 \text{ V}$ Gate-Body Leakage, Reverse $V_{GS} = -20 \text{ V}$, $V_{DS} = 0 \text{ V}$ Gate-Body Leakage, Reverse $V_{GS} = -20 \text{ V}$, $V_{DS} = 0 \text{ V}$ Gate Threshold Voltage $V_{DS} = V_{GS}$, $I_D = 250 \mu\text{A}$ Gate Threshold Voltage $I_D = 250 \mu\text{A}$, Referenced to 25°C Gate Threshold Voltage $I_D = 250 \mu\text{A}$, Referenced to 25°C Gate Threshold Voltage $I_D = 250 \mu\text{A}$, Referenced to 25°C Gate Threshold Voltage $I_D = 250 \mu\text{A}$, Referenced to 25°C Gate Threshold Voltage $I_D = 10.8 \text{A}$ V_{GS} = 10 V, I_D = 10.8 \text{A} $V_{GS} = 10 \text{V}$, $I_D = 10.8 \text{A}$ Torn-State Drain Current $V_{GS} = 10 \text{V}$, $I_D = 10.8 \text{A}$ Characteristics $V_{DS} = 20 \text{V}$, $I_D = 10.8 \text{A}$ Characteristics $V_{DS} = 20 \text{V}$, $I_D = 10.8 \text{A}$ Characteristics (Note 2) $V_{DS} = 20 \text{V}$, $I_D = 1 \text{A}$,Furn-On Delay Time $V_{DS} = 20 \text{V}$, $I_D = 1 \text{A}$,Furn-Off Delay Time $V_{DS} = 20 \text{V}$, $I_D = 10.8 \text{A}$,Gate-Source Charge $V_{DS} = 20 \text{V}$, $I_D = 10.8 \text{A}$,	Drain-Source Breakdown Voltage $V_{GS} = 0 \text{ V}$, $I_D = 250 \ \mu\text{A}$ 40Breakdown Voltage Temperature Coefficient $I_D = 250 \ \mu\text{A}$, Referenced to 25°C 40Breakdown Voltage Drain Current $V_{DS} = 32 \text{ V}$, $V_{GS} = 0 \text{ V}$ 53Gate-Body Leakage, Forward $V_{GS} = 30 \text{ V}$, $V_{DS} = 0 \text{ V}$ 53Gate-Body Leakage, Reverse $V_{GS} = -20 \text{ V}$, $V_{DS} = 0 \text{ V}$ 53Gate-Body Leakage, Reverse $V_{GS} = -20 \text{ V}$, $V_{DS} = 0 \text{ V}$ 53Cteristics (Note 2)531D = 250 \ \mu\text{A}, Referenced to 25°C Gate Threshold Voltage $I_D = 250 \ \mu\text{A}$, Referenced to 25°C 53Femperature Coefficient $I_D = 250 \ \mu\text{A}$, Referenced to 25°C 53Static Drain-Source On-Resistance $V_{GS} = 10 \text{ V}$, $I_D = 10.8 \text{ A}$ 2 $V_{OS} = 10 \text{ V}$, $I_D = 10.8 \text{ A}$ $V_{GS} = 10 \text{ V}$, $I_D = 10.8 \text{ A}$ 2 $V_{DS} = 10 \text{ V}$, $I_D = 10.8 \text{ A}$ $V_{DS} = 5 \text{ V}$ 22Forward Transconductance $V_{DS} = 20 \text{ V}$, $V_{GS} = 0 \text{ V}$,2 $V_{DT} = 20 \text{ V}$, $I_D = 10.8 \text{ A}$ $V_{CS} = 10 \text{ V}$, $I_D = 1.8 \text{ A}$ 2 $V_{DT} = 0$ $V_{DS} = 20 \text{ V}$, $I_D = 1.8 \text{ A}$ $V_{CS} = 10 \text{ V}$, $R_{GEN} = 6 \Omega$ $V_{DT} = 0$ $V_{DS} = 20 \text{ V}$, $I_D = 1.8 \text{ A}$, $V_{CS} = 10 \text{ V}$ $I_D = 10.8 \text{ A}$ $V_{DT} = 0$ $V_{DS} = 20 \text{ V}$, $I_D = 1.8 \text{ A}$, $V_{CS} = 10 \text{ V}$ $I_D = 10.8 \text{ A}$ $V_{DT} = 0$ $V_{DS} = 20 \text{ V}$, $I_D = 10.8 \text{ A}$ $I_D = 10.8 \text{ A}$ $I_D = 10.8 \text{ A}$ V	$\begin{array}{c c c c c c c c } \hline \label{eq:constraint} Drain-Source Breakdown Voltage V_{GS} = 0 \ V, I_D = 250 \ \mu A & 40 \\ \hline I_D = 250 \ \mu A, \ Referenced \ to \ 25^\circ C & 42 \\ \hline I_D = 250 \ \mu A, \ Referenced \ to \ 25^\circ C & 42 \\ \hline \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \$	$\begin{array}{c c c c c c c } \hline \begin{tabular}{ c c } \hline \hline \begin{tabular}{ c c c } \hline \begin{tabular}{ c c c c } \hline \hline \begin{tabular}{ c c c } \hline \hline \b$

LICCUI	cal Characteristics	$T_A = 25^{\circ}C$ unless otherwise noted				
Symbol	Parameter	Test Conditions	Min	Тур	Мах	Units
Drain-S	ource Diode Characteristics a	and Maximum Ratings				
ls	Maximum Continuous Drain-Source	Diode Forward Current			2.1	Α
V _{SD}	Drain–Source Diode Forward Voltage	$V_{GS} = 0 V$, $I_S = 2.1 A$ (Note 2)		0.7	1.2	V
t _{rr}	Diode Reverse Recovery Time	$I_F = 10.8 \text{ A}, d_{iF}/d_t = 100 \text{ A}/\mu\text{s}$		27		nS
Q _{rr}	Diode Reverse Recovery Charge			58		nC

Notes:

1. R_{8JA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. R_{8JC} is guaranteed by design while R_{8CA} is determined by the user's board design.




a) 50°C/W when mounted on a 1in² pad of 2 oz copper




b) 105°C/W when mounted on a .04 in² pad of 2 oz copper c) 125°C/W when mounted on a minimum pad.

Scale 1 : 1 on letter size paper

2. Pulse Test: Pulse Width < 300µs, Duty Cycle < 2.0%





ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such uninten

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative