ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,



FDMS2D4N03S

N-Channel PowerTrench[®] SyncFETTM 30 V, 163 A, 1.8 m Ω

Features

- Max $r_{DS(on)}$ = 1.8 m Ω at V_{GS} = 10 V, I_D = 28 A
- Max $r_{DS(on)}$ = 2.34 m Ω at V_{GS} = 4.5 V, I_D = 26 A
- High Performance Technology for Extremely Low r_{DS(on)}
- SyncFETTM Schottky Body Diode
- 100% UIL Tested
- RoHS Compliant


General Description


The FDMS2D4N03S has been designed to minimize losses in power conversion application. Advancements in both silicon and package technologies have been combined to offer the lowest $r_{\text{DS}(\text{on})}$ while maintaining excellent switching performance. This device has the added benefit of an efficient monolithic schottky body diode.

Applications

- Synchronous Rectifier for DC/DC Converters
- Notebook Vcore/ GPU Low Side Switch
- Networking Point of Load Low Side Switch
- Telecom Secondary Side Rectification







Power 56

MOSFET Maximum Ratings T_A = 25 °C unless otherwise noted.

Symbol	Parame		Ratings	Units	
V_{DS}	Drain to Source Voltage			30	V
V_{GS}	Gate to Source Voltage			±16	V
	Drain Current -Continuous	T _C = 25 °C	(Note 5)	163	
	-Continuous	T _C = 100 °C	(Note 5)	103	^
ID	-Continuous	T _A = 25 °C	(Note 1a)	28	Α
	-Pulsed		(Note 4)	694	
E _{AS}	Single Pulse Avalanche Energy		(Note 3)	175	mJ
В	Power Dissipation	T _C = 25 °C		74	W
P_{D}	Power Dissipation	T _A = 25 °C	(Note 1a)	2.5	VV
T _J , T _{STG}	Operating and Storage Junction Tempera	ture Range		-55 to +150	°C

Thermal Characteristics

$R_{\theta JC}$	Thermal Resistance, Junction to Case	1.7	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1a	50	C/VV

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDMS2D4N03S	FDMS2D4N03S	Power 56	13 "	12 mm	3000 units

Electrical Characteristics T_J = 25 °C unless otherwise noted.

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Units
Off Chara	cteristics					
BV _{DSS}	Drain to Source Breakdown Voltage	I _D = 1 mA, V _{GS} = 0 V	30			V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	I _D = 10 mA, referenced to 25 °C		18		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 24 V, V _{GS} = 0 V			500	μΑ
I _{GSS}	Gate to Source Leakage Current	V _{GS} = ±16 V, V _{DS} = 0 V			±100	nA

On Characteristics

V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 1 \text{ mA}$	1.0	1.6	3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I _D = 10 mA, referenced to 25 °C		-4		mV/°C
		$V_{GS} = 10 \text{ V}, I_D = 28 \text{ A}$		1.4	1.8	
r _{DS(on)}	Static Drain to Source On Resistance	$V_{GS} = 4.5 \text{ V}, I_D = 26 \text{ A}$		1.7	2.34	mΩ
		$V_{GS} = 10 \text{ V}, I_D = 28 \text{ A}, T_J = 125 \text{ °C}$		2.0	2.8	
9 _{FS}	Forward Transconductance	V _{DS} = 5 V, I _D = 28 A		200		S

Dynamic Characteristics

C _{iss}	Input Capacitance	V 45.V.V 0.V		4670	6540	pF
Coss	Output Capacitance	V _{DS} = 15 V, V _{GS} = 0 V, f = 1 MHz		1395	1955	pF
C _{rss}	Reverse Transfer Capacitance	1 - 1 1011 12		63	120	pF
R _a	Gate Resistance		0.1	0.5	1.5	Ω

Switching Characteristics


t _{d(on)}	Turn-On Delay Time		15	28	ns
t _r	Rise Time	V _{DD} = 15 V, I _D = 28 A,	4	10	ns
t _{d(off)}	Turn-Off Delay Time	$V_{GS} = 10 \text{ V}, R_{GEN} = 6 \Omega$	38	61	ns
t _f	Fall Time		3	10	ns
Q_g	Total Gate Charge	V _{GS} = 0 V to 10 V	63	88	nC
Q_{g}	Total Gate Charge	$V_{GS} = 0 \text{ V to } 4.5 \text{ V} V_{DD} = 15 \text{ V},$	28	40	nC
Q _{gs}	Gate to Source Charge	I _D = 28 A	9.8		nC
Q_{gd}	Gate to Drain "Miller" Charge		4.9		nC

Drain-Source Diode Characteristics

V_{SD}	Source to Drain Diode Forward Voltage	$V_{GS} = 0 \text{ V}, I_{S} = 2.1 \text{ A}$ (Note 2)	0.65	1.2	V
	Source to Drain blode 1 of ward voltage	$V_{GS} = 0 \text{ V}, I_S = 28 \text{ A}$ (Note 2)	0.78	1.3	·
t _{rr}	Reverse Recovery Time	I _E = 28 A, di/dt = 300 A/μs	37	59	ns
Q_{rr}	Reverse Recovery Charge	1 _F - 20 A, αι/αι - 300 A/μS	51	81	nC

Notes:

^{1.} R_{0JA} is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. R_{0CA} is determined by the user's board design.



50 °C/W when mounted on a 1 in² pad of 2 oz copper



125 °C/W when mounted on a minimum pad of 2 oz copper.

- 2. Pulse Test: Pulse Width < 300 µs, Duty cycle < 2.0%.
 3. E_{AS} of 175 mJ is based on starting T_J = 25 °C; N-ch: L = 3 mH, I_{AS} = 10.8 A, V_{DD} = 30 V, V_{GS} =10 V. 100% test at L = 0.1 mH, I_{AS} = 33 A.
 4. Pulsed Id please refer to Fig 11 SOA graph for more details.
 5. Computed continuous current limited to Max Junction Temperature only, actual continuous current will be limited by thermal & electro-mechanical application board design.

Typical Characteristics T_J = 25 °C unless otherwise noted.




Figure 1. On Region Characteristics




Figure 3. Normalized On Resistance vs. Junction Temperature




Figure 5. Transfer Characteristics




Figure 2. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 4. On-Resistance vs. Gate to Source Voltage




Figure 6. Source to Drain Diode Forward Voltage vs. Source Current

Typical Characteristics $T_J = 25$ °C unless otherwise noted.




Figure 7. Gate Charge Characteristics




Figure 9. Unclamped Inductive Switching Capability




Figure 11. Forward Bias Safe Operating Area




Figure 8. Capacitance vs. Drain to Source Voltage




Figure 10. Maximum Continuous Drain Current vs Case Temperature




Figure 12. Single Pulse Maximum Power Dissipation

Typical Characteristics T_J = 25 °C unless otherwise noted.




Figure 13. Junction-to-Case Transient Thermal Response Curve

Typical Characteristics (continued)

SyncFETTM Schottky body diode Characteristics

Fairchild's SyncFETTM process embeds a Schottky diode in parallel with PowerTrench MOSFET. This diode exhibits similar characteristics to a discrete external Schottky diode in parallel with a MOSFET. Figure 14 shows the reverse recovery characteristic of the FDMS2D4N03S.

Schottky barrier diodes exhibit significant leakage at high temperature and high reverse voltage. This will increase the power in the device.




Figure 14. FDMS2D4N03S SyncFETTM Body Diode Reverse Recovery Characteristic





Figure 15. SyncFETTM Body Diode Reverse Leakage vs. Drain-Source Voltage

Dimensional Outline and Pad Layout



BOTTOM VIEW

ON Semiconductor and the ON Logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other

countries.

ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by
ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual

Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.