

# **MOSFET** - N-Channel, POWERTRENCH®

**80 V, 80 A, 4.5** m $\Omega$ 

### FDWS86368-F085

#### **Features**

- Typical  $R_{DS(on)} = 3.7 \text{ m}\Omega$  at  $V_{GS} = 10 \text{ V}$ ,  $I_D = 80 \text{ A}$
- Typical  $Q_{g(tot)}$  = 57 nC at  $V_{GS}$  = 10 V,  $I_D$  = 80 A
- UIS Capability
- Wettable Flanks for Automatic Optical Inspection (AOI)
- AEC-Q101 Qualified and PPAP Capable
- This Device is Pb-Free and is RoHS Compliant

#### **Applications**

- Automotive Engine Control
- PowerTrain Management
- Solenoid and Motor Drivers
- Integrated Starter/Alternator
- Primary Switch for 12 V Systems

#### MOSFET MAXIMUM RATINGS (T<sub>J</sub> = 25°C, Unless otherwise noted)


Symbol	Parameter	Ratings	Units
V <sub>DSS</sub>	Drain-to-Source Voltage	80	V
V <sub>GS</sub>	Gate-to-Source Voltage	tte-to-Source Voltage ±20	
I <sub>D</sub>	Drain Current (T <sub>C</sub> = 25°C) Continuous (V <sub>GS</sub> = 10 V) (Note 1) Pulsed	80 (See Figure 4)	А
E <sub>AS</sub>	Single Pulse Avalanche Energy (Note 2)	82	mJ
P <sub>D</sub>	Power Dissipation	214	W
	Derate Above 25°C	1.43	W/°C
TJ, T <sub>STG</sub>	Operating and Storage Temperature	-55 to +175	°C
Rejc	Thermal Resistance, Junction to Case	0.7	°C/W
ReJA	Maximum Thermal Resistance, Junction to Ambient (Note 3)	50	°C/W

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


- 1. Current is limited by bondwire configuration.
- 2. Starting  $T_J = 25^{\circ}$ C,  $\dot{L} = 40 \,\mu$ H,  $I_{AS} = 64 \,$ A,  $V_{DD} = 80 \,$ V during inductor charging and  $V_{DD} = 0 \,$ V during time in avalanche.
- 3. ReJA is the sum of the junction–to–case and case–to–ambient thermal resistance, where the case thermal reference is defined as the solder mounting surface of the drain pins. ReJC is guaranteed by design, while ReJA is determined by the board design. The maximum rating presented here is based on mounting on a 1 in pad of 2 oz copper.

V <sub>DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX	
80 V	4.5 mΩ @ 10 V	80 A	

#### **ELECTRICAL CONNECTION**



**N-Channel MOSFET** 



#### **MARKING DIAGRAM**



= Assembly Location

Y = Year

WW = Work Week

WL = Assembly Lot

FDWS = Device Code

86368 = Device Code

(Note: Microdot may be in either location)

#### ORDERING INFORMATION

	Device	Package	Shipping <sup>†</sup>
FDWS	886368-F085	DFNW8 (Power56) (Pb-Free)	3000 / Tape & Reel

<sup>†</sup>For information on tape and reel specifications,


#### **ELECTRICAL CHARACTERISTICS** ( $T_A = 25^{\circ}C$ unless otherwise noted)

Symbol	Parameter	Test Conditions		Min.	Тур.	Max.	Units
OFF CHAF	ACTERISTICS				•	•	•
B <sub>VDSS</sub>	Drain-to-Source Breakdown Voltage	$I_D = 250 \mu A, V_{GS} = 0 V$		80			٧
I <sub>DSS</sub> Drain-to-Source Leakage		V <sub>DS</sub> = 80 V, V <sub>GS</sub> = 0 V, T <sub>J</sub> = 25°C				1	μΑ
	Current	V <sub>DS</sub> = 80 V, V <sub>GS</sub> = 0 V, T <sub>J</sub> = 175°C (Note 4)				1	mA
I <sub>GSS</sub>	Gate-to-Source Leakage Current	V <sub>GS</sub> = ±20 V				±100	nA
ON CHAR	ACTERISTICS					•	
V <sub>GS(th)</sub>	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 250 \mu A$		2.0	3.0	4.0	V
R <sub>DS(on)</sub>	Drain to Source On Resistance	I <sub>D</sub> = 80 A, V <sub>GS</sub> = 10 V, T <sub>J</sub> = 25°C			3.7	4.5	mΩ
		I <sub>D</sub> = 80 A, V <sub>GS</sub> = 10 V, T <sub>J</sub> = 175°C (Note 4)			7.4	9.0	1
OYNAMIC	CHARACTERISTICS				•	•	
C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> = 40 V, V <sub>GS</sub> = 0 V, f = 1 MHz			4350		pF
C <sub>oss</sub>	Output Capacitance				636		pF
C <sub>rss</sub>	Reverse Transfer Capacitance				20		pF
R <sub>g</sub>	Gate Resistance	f = 1 MHz			2.5		Ω
Q <sub>g(TOT)</sub>	Total Gate Charge	V <sub>GS</sub> = 0 V to 10 V	V <sub>DD</sub> = 64 V, I <sub>D</sub> = 80 A		57	75	nC
Q <sub>g(th)</sub>	Threshold Gate Charge	V <sub>GS</sub> = 0 V to 2 V			8		nC
$Q_{gs}$	Gate-to-Source Gate Charge				23		nC
Q <sub>gd</sub>	Gate-to-Drain "Miller" Charge				11		nC
WITCHIN	G CHARACTERISTICS						
t <sub>on</sub>	Turn-On Time	$V_{DD} = 40 \text{ V}, I_D = 80 \text{ A},$	$V_{GS}$ = 10V, $R_{GEN}$ = 6 $\Omega$			60	ns
t <sub>d(on)</sub>	Turn-On Delay				23		ns
t <sub>r</sub>	Rise Time				22		ns
t <sub>d(off)</sub>	Turn-Off Delay				32		ns
t <sub>f</sub>	Fall Time				13		ns
t <sub>off</sub>	Turn-Off Time					59	ns
PRAIN-SC	OURCE DIODE CHARACTERISTI	cs					
V <sub>SD</sub>	Source-to-Drain Diode Voltage	V <sub>GS</sub> = 0 V, I <sub>SD</sub> = 80 A V <sub>GS</sub> = 0 V, I <sub>SD</sub> = 40 A				1.25 1.2	V
t	Reverse-Recovery Time	$I_F = 80 \text{ A}, \ \Delta I_{SD}/\Delta t = 100 \text{ A/}\mu\text{s}, \ V_{DD} = 64 \text{ V}$			58	75	ns
Q <sub>rr</sub>	Reverse-Recovery Charge				49	67	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product

performance may not be indicated by the Electrical Characteristics if operated under different conditions. 4. The maximum value is specified by design at  $T_J = 175^{\circ}$ C. Product is not tested to this condition in production.

#### **TYPICAL CHARACTERISTICS**



200 CURRENT LIMITED V<sub>GS</sub> = 10V 175 BY PACKAGE ₹ 150 CURRENT LIMITED ID, DRAIN CURRENT 125 100 75 50 25 75 100 125 150 175 T<sub>C</sub>, CASE TEMPERATURE(°C) 200 25

Figure 1. Normalized Power Dissipation vs.

Case Temperature

Figure 2. Maximum Continuous Drain Current vs. Case Temperature




Figure 3. Normalized Maximum Transient Thermal Impedance




Figure 4. Peak Current Capability

#### **TYPICAL CHARACTERISTICS**




Figure 5. Forward Bias Safe Operating Area




Figure 7. Transfer Characteristics





Figure 9. Saturation Characteristics



NOTE: Refer to **onsemi** Application Notes <u>AN7514</u> and <u>AN7515</u>

Figure 6. Unclamped Inductive Switching Capability




Figure 8. Forward Diode Characteristics




Figure 10. Saturation Characteristics

#### **TYPICAL CHARACTERISTICS**




Figure 11. R<sub>DSON</sub> vs. Gate Voltage




Figure 13. Normalized Gate Threshold Voltage vs. Temperature




Figure 15. Capacitance vs. Drain to Source Voltage




Figure 12. Normalized R<sub>DSON</sub> vs. Junction Temperature




Figure 14. Normalized Drain to Source Breakdown Voltage vs. Junction Temperature






Figure 16. Single Pulse Maximum Power Dissipation

#### **PACKAGE DIMENSIONS**

## **DFNW8 5.2x6.3, 1.27P**CASE 507AU ISSUE A





RECOMMENDATION

\*FOR ADDITIONAL INFORMATION ON OUR
PB-FREE STRATEGY AND SOLDERING DETAILS,
PLEASE DOWNLOAD THE ON SEMICONDUCTOR
SOLDERING AND MOUNTING TECHNIQUES
REFERENCE MANUAL, SOLDERRIMD.

LAND PATTERN

DIM	MILLIMETERS			
Diw	MIN.	NOM.	MAX.	
Α	0.90	1.00	1.10	
A1	-	•	0.05	
A2	0.65	0.75	0.85	
A3		0.30 REF		
b	0.47	0.52	0.57	
b1	0.13	0.18	0.23	
b2	(0.54)			
D	5.00	5.10	5.20	
D1	4.80	4.90	5.00	
D2	3.72	3.82	3.92	
Е	6.20	6.30	6.40	
E1	5.70	5.80	5.90	
E2	3.38	3.48	3.58	
E3	0.30 REF			
E4	0.45 REF			
Ф	1.27 BSC			
e/2	0.635BSC			
k	1.30	1.40	1.50	
L	0.64	0.74	0.84	
z	0.24	0.29	0.34	
z1	(0.28)			
θ	0°		12°	

POWERTRENCH is a registered trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer pu

#### **PUBLICATION ORDERING INFORMATION**

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative