

# MOSFET – Power, Dual P-Channel

**-40 V, -20 A, 12.5 mΩ**

## FDWS9520L-F085

### Features

- Small Footprint (5x6 mm) for Compact Design
- Low  $R_{DS(on)}$  to Minimize Conduction Losses
- Low QG and Capacitance to Minimize Driver Losses
- Wettable Flanks for Enhanced Optical Inspection
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

### MAXIMUM RATINGS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V <sub>DSS</sub>	−40	V
Gate-to-Source Voltage			V <sub>GS</sub>	±16	V
Continuous Drain Current R <sub>θJC</sub> (Notes 1, 3)	Steady State	T <sub>C</sub> = 25°C	I <sub>D</sub>	−60.8	A
		T <sub>C</sub> = 100°C		−43.0	
Power Dissipation R <sub>θJC</sub> (Note 1)		T <sub>C</sub> = 25°C	P <sub>D</sub>	75	W
		T <sub>C</sub> = 100°C		37.5	
Continuous Drain Current R <sub>θJA</sub> (Notes 1, 2, 3)	Steady State	T <sub>C</sub> = 25°C	I <sub>D</sub>	−12.2	A
		T <sub>C</sub> = 100°C		−8.6	
Power Dissipation R <sub>θJA</sub> (Notes 1 & 2)		T <sub>C</sub> = 25°C	P <sub>D</sub>	3.0	W
		T <sub>C</sub> = 100°C		1.5	
Pulsed Drain Current	T <sub>C</sub> = 25°C, t <sub>p</sub> = 10 μs		I <sub>DM</sub>	−281	A
Operating Junction and Storage Temperature			T <sub>J</sub> , T <sub>stg</sub>	−55 to +175	°C
Source Current (Body Diode)			I <sub>S</sub>	−20	A
Single Pulse Drain-to-Source Avalanche Energy (I <sub>L</sub> (pk) = −19)			E <sub>AS</sub>	90	mJ
Lead Temperature for Soldering Purposes (1/83 from case for 10 s)			T <sub>L</sub>	260	°C



Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

### THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case – Steady State	$R_{\theta JC}$	2	$^\circ\text{C/W}$
Junction-to-Ambient – Steady State (Note 2)	$R_{\theta JA}$	50	$^\circ\text{C/W}$

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
2. Surface-mounted on FR4 board using a 650 mm<sup>2</sup>, 2 oz. Cu pad.
3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.

$V_{(BR)DSS}$	$R_{DS(ON)} \text{ MAX}$	$I_D \text{ MAX}$
-40 V	12.5 mΩ @ -10 V	-20 A
	19.5 mΩ @ -4.5 V	



PQFN8 5x6, 1.27P  
CASE 483BL

### ORDERING INFORMATION

See detailed ordering, marking and shipping information on page 3 of this data sheet.

# FDWS9520L-F085

## ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
-----------	--------	----------------	-----	-----	-----	------

### Off Characteristics

Drain to Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0\text{ V}, I_D = -250\text{ }\mu\text{A}$	-40			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$V_{(BR)DSS}/T_J$			21		mV/ $^\circ\text{C}$
Zero Gate Voltage Drain Current	$I_{DSS}$	$V_{GS} = 0\text{ V}, V_{DS} = -40\text{ V}$	$T_J = 25^\circ\text{C}$		-1	$\mu\text{A}$
			$T_J = 175^\circ\text{C}$		-1	mA
Zero Gate Voltage Drain Current	$I_{GSS}$	$V_{DS} = 0\text{ V}, V_{GS} = \pm 16\text{ V}$			$\pm 100$	nA

### On Characteristics (Note 4)

Gate Threshold Voltage	$V_{GS(TH)}$	$V_{GS} = V_{DS}, I_D = -250\text{ }\mu\text{A}$	-1	-1.8	-3	V
Threshold Temperature Coefficient	$V_{GS(TH)}/T_J$			-5.5		mV/ $^\circ\text{C}$
Drain-to-Source On Resistance	$R_{DS(on)}$	$V_{GS} = -10\text{ V}, I_D = -20\text{ A}$		10.4	12.5	$\text{m}\Omega$
		$V_{GS} = -4.5\text{ V}, I_D = -10\text{ A}$		14.6	19.5	

### Charges, Capacitances & Gate Resistance

Input Capacitance	$C_{iss}$	$V_{GS} = 0\text{ V}, f = 1\text{ MHz}, V_{DS} = -20\text{ V}$		2370		pF
Output Capacitance	$C_{oss}$			940		pF
Reverse Transfer Capacitance	$C_{rss}$			40		pF
Gate Resistance	$R_g$	$V_{GS} = 0.5\text{ V}, f = 1\text{ MHz}$		17		$\Omega$
Total Gate Charge	$Q_{G(TOT)}$	$V_{GS} = -10\text{ V}, V_{DS} = -32\text{ V}, I_D = -20\text{ A}$		33		nC
		$V_{GS} = -4.5\text{ V}, V_{DS} = -32\text{ V}, I_D = -20\text{ A}$		13		
Threshold Gate Charge	$Q_{g(th)}$	$V_{GS} = 0\text{ to }-1\text{ V}$		2		
Gate to Source Gate Charge	$Q_{gs}$	$V_{DD} = -20\text{ V}, I_D = -20\text{ A}$		7		
Gate to Drain "Miller" Charge	$Q_{gd}$			4		
Plateau Voltage	$V_{GP}$			-4		V

### Switching Characteristics

Turn-On Delay Time	$t_{d(ON)}$	$V_{DD} = -20\text{ V}, I_D = -20\text{ A}, V_{GS} = -10\text{ V}, R_{GEN} = 6\text{ }\Omega$		8		ns
Turn-On Rise Time	$t_r$			21		ns
Turn-Off Delay Time	$t_{d(OFF)}$			120		ns
Turn-Off Fall Time	$t_f$			34		ns

### Drain-Source Diode Characteristics

Source to Drain Diode Voltage	$V_{SD}$	$I_{SD} = -20\text{ A}, V_{GS} = 0\text{ V}$		-0.9	-1.25	V
		$I_{SD} = -10\text{ A}, V_{GS} = 0\text{ V}$		-0.83	-1.2	V
Reverse Recovery Time	$T_{RR}$	$V_{GS} = 0\text{ V}, dI_{SD}/dt = 100\text{ A}/\mu\text{s}, I_S = -20\text{ A}$		46		ns
Charge Time	$t_a$			22		
Discharge Time	$t_b$			24		
Reverse Recovery Charge	$Q_{RR}$			37		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Pulse Test: pulse width  $\leq 300\text{ }\mu\text{s}$ , duty cycle  $\leq 2\%$

5. Switching characteristics are independent of operating junction temperatures.

## FDWS9520L–F085

### ORDERING INFORMATION

Device	Device Marking	Package	Shipping†
FDWS9520L–F085	FDWS9520L	PQFN8 5x6, 12.7P (Pb–Free, Halogen Free)	3,000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D

**DISCONTINUED**  
THIS DEVICE IS NOT RECOMMENDED FOR NEW DESIGN  
PLEASE CONTACT YOUR **onsemi**  
REPRESENTATIVE FOR INFORMATION

## TYPICAL CHARACTERISTICS




Figure 1. Normalized Power Dissipation vs. Case Temperature




Figure 2. Maximum Continuous Drain Current vs. Case Temperature




Figure 3. Normalized Maximum Transient Thermal Impedance




Figure 4. Peak Current Capability

## TYPICAL CHARACTERISTICS




Figure 5. Forward Bias Safe Operating Area




Figure 6. Unclamped Inductive Switching Capability

(Note: Refer to onsemi Applications Notes [AN7514](#) and [AN7515](#))




Figure 7. Transfer Characteristics




Figure 8. Forward Diode Characteristics





Figure 9. Saturation Characteristics

Figure 10. Normalized  $R_{DS(on)}$  vs. Drain Current

## TYPICAL CHARACTERISTICS




Figure 11.  $R_{DS(on)}$  vs. Gate VoltageFigure 12. Normalized  $R_{DS(on)}$  vs. Junction Temperature

Figure 13. Normalized Gate Threshold Voltage vs. Temperature




Figure 14. Normalized Drain-to-Source Breakdown Voltage vs. Junction Temperature




Figure 15. Capacitance vs. Drain-to-Source Voltage






Figure 16. Gate Charge vs. Gate-to-Source Voltage


**PQFN8 5X6, 1.27P**  
**CASE 483BL**  
**ISSUE A**


DATE 23 APR 2021

## NOTES:


1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
2. CONTROLLING DIMENSION: MILLIMETERS
3. COPLANARITY APPLIES TO THE EXPOSED PADS AS WELL AS THE TERMINALS.
4. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
5. SEATING PLANE IS DEFINED BY THE TERMINALS. "A1" IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.
6. IT IS RECOMMENDED TO HAVE NO TRACES OR VIAS WITHIN THE KEEP OUT AREA.




TOP VIEW




SIDE VIEW




FRONT VIEW




DETAIL "B"



DETAIL "A"



BOTTOM VIEW


LAND PATTERN  
RECOMMENDATION

\*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.90	1.00	1.10
A1	0.00	-	0.05
A3	0.23	0.28	0.33
b	0.26	0.31	0.36
b1	0.36	0.41	0.46
D	5.00	5.10	5.20
D1	4.80	4.90	5.00
D2	1.51	1.61	1.71
D3	0.54 REF		
E	6.20	6.30	6.40
E1	5.70	5.80	5.90
E2	3.58	3.68	3.78
E3	0.30 REF		
E4	0.10	0.20	0.30
E5	0.72 REF		
E6	0.59	0.69	0.79
e	1.27 BSC		
e1	3.81 BSC		
e/2	0.635 BSC		
k	1.19 REF		
k1	0.60 REF		
k2	0.45 REF		
L	0.64	0.74	0.84
L2	0.15	0.25	0.35
z	0.39 REF		
θ	0°	-	7°

DOCUMENT NUMBER: 98AON13690G

Electronic versions are uncontrolled except when accessed directly from the Document Repository.  
Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.

DESCRIPTION: PQFN8 5X6, 1.27P

PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)