

Is Now Part of




ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an equif prese





TO-220


Symbol	Parameter	FDP070AN06A0	Unit
V _{DSS}	Drain to Source Voltage	60	V
V _{DSS} V _{GS}	Gate to Source Voltage	±20	V
	Drain Current		
I _D	Continuous ($T_C < 97^{\circ}C$, $V_{GS} = 10V$)	80	А
	Pulsed	Figure 4	А
E _{AS}	Single Pulse Avalanche Energy (Note 1)	190	mJ
	Power dissipation	175	W
P _D	Derate above 25°C	1.17	W/ ^o C
T _J , T _{STG}	Operating and Storage Temperature	-55 to 175	°C

Thermal Characteristics


$R_{ extsf{ heta}JC}$	Thermal Resistance Junction to Case, Max.	0.86	°C/W
$R_{\theta JA}$	Thermal Resistance Junction to Ambient, Max. (Note 2)	62	°C/W

Device	Marking	Device Package Reel Size		Reel Size	Tape \	Nidth	Quar	ntity
FDP070AN06A0		FDP070AN06A0	TO-220 N/A		N/A		50 units	
Electric	al Chara	acteristics T _c = 25°0	C unless otherw	ise noted.				
Symbol		Parameter	Test Conditions		Min	Тур	Max	Unit
Off Chara	cteristics	6						
B _{VDSS}	Drain to Source Breakdown Voltage		I _D = 250μA,	V _{GS} = 0V	60	-	-	V
	Zero Gate	-	V _{DS} = 50V		-	-	1	ıιΔ
I _{DSS}	Zero Gate Voltage Drain Current		V _{GS} = 0V	T _C = 150 ^o C	-	-	250	μA
I _{GSS}	Gate to Sc	ource Leakage Current	V _{GS} = ±20V		-	-	±100	nA
On Chara	cteristics	5						
V _{GS(TH)}		ource Threshold Voltage	V _{GS} = V _{DS} ,	I _D = 250μA	2	-	4	V
			I _D = 80A, V ₀	_{es} = 10V	-	0.0061	0.007	
r _{DS(ON)}	Drain to So	ource On Resistance	$I_D = 80A, V_{GS} = 10V,$ $T_J = 175^{\circ}C$		-	0.0127	0.015	Ω
Dynamic	Characte	ristics						
C _{ISS}	Input Capa				-	3000	_	pF
C _{OSS}	Output Ca		V _{DS} = 25V, 1 f = 1MHz	$V_{GS} = 0V,$	-	510	-	pF
C _{RSS}	Reverse Ti	ansfer Capacitance			-	230	-	pF
Q _{g(TOT)}	Total Gate	Charge at 10V	V _{GS} = 0V to	10V		51	66	nC
Q _{g(TH)}	Threshold	Gate Charge	V _{GS} = 0V to	2V V _{DD} = 30V	-	5.4	7	nC
Q _{gs}	Gate to Sc	ource Gate Charge		I _D = 80A	-	17	-	nC
Q _{gs2}	Gate Char	ge Threshold to Plateau		I _g = 1.0mA	-	11.6	-	nC
Q _{gd}	Gate to Dr	ain "Miller" Charge			-	16	-	nC
Switching	g Charact	eristics (V _{GS} = 10V)						
t _{ON}	Turn-On T	ime			-	-	256	ns
t _{d(ON)}	Turn-On D	elay Time			-	12	-	ns
t _r	Rise Time		V _{DD} = 30V, I	_D = 80A	-	159	-	ns
t _{d(OFF)}	Turn-Off D	elay Time	V _{GS} = 10V,	R _{GS} = 5.6Ω	-	27	-	ns
t _f	Fall Time				-	35	-	ns
t _{OFF}	Turn-Off T	ime			-	-	93	ns
Drain-Sou	urce Diod	e Characteristics						
V.	Source to	Course to Durin Diada Maltana			-	-	1.25	V
V _{SD}	Source to Drain Diode Voltage	I _{SD} = 80A I _{SD} = 40A		- /	-	1.0	V	
t _{rr}		ecovery Time		I _{SD} /dt = 100A/μs		-	34	ns
Q _{RR}	Reverse R	ecovered Charge	I_{SD} = 75A, dI_{SD}/dt = 100A/µs		-	-	35	nC

FDP070AN06A0 — N-Channel PowerTrench® MOSFET




FDP070AN06A0 Rev. C2




©2003 Fairchild Semiconductor Corporation FDP070AN06A0 Rev. C2


www.fairchildsemi.com



©2003 Fairchild Semiconductor Corporation FDP070AN06A0 Rev. C2




©2003 Fairchild Semiconductor Corporation FDP070AN06A0 Rev. C2 www.fairchildsemi.com




©2003 Fairchild Semiconductor Corporation FDP070AN06A0 Rev. C2

www.fairchildsemi.com

SABER Electrical Model








Figure 21. TO-220, Molded, 3-Lead, Jedec Variation AB

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:

http://www.fairchildsemi.com/package/packageDetails.html?id=PN_TT220-003



N-Channel PowerTrench® MOSFET

Obsolete

Not In Production

Datasheet contains specifications on a product that is discontinued by Fairchild

Semiconductor. The datasheet is for reference information only.

Rev 166

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC