onsemi

MOSFET – N-Channel, POWERTRENCH[®]

30 V, 10.2 A, 14 mΩ

FDS8878, FDS8878-F123

General Description

This N-Channel MOSFET has been designed specifically to improve the overall efficiency of DC/DC converters using either synchronous or conventional switching PWM controllers. It has been optimized for low gate charge, low r_{DS(on)} and fast switching speed.

Features

- $r_{DS(on)} = 14 \text{ m}\Omega$, $V_{GS} = 10 \text{ V}$, $I_D = 10.2 \text{ A}$
- $r_{DS(on)} = 17 \text{ m}\Omega$, $V_{GS} = 4.5 \text{ V}$, $I_D = 9.3 \text{ A}$
- High Performance Trench Technology for Extremely Low r_{DS(on)}
- · Low Gate Charge
- High Power and Current Handling Capability
- These Devices are Pb-Free and are RoHS Compliant

Applications

• DC/DC Converters

Symbol		Parameter	Ratings	Unit		
V _{DSS}	Drain to S	ource Voltage	30	V		
V _{GSS}	Gate to So	ource Voltage	±20	V		
۱ _D	Drain Current	Continuous (T _A = 25°C, V _{GS} = 10 V, R _{θJA} = 50°C/W)	10.2	A		
		Continuous (T _A = 25°C, V _{GS} = 4.5 V, R _{θJA} = 50°C/W)	9.3	A		
		Pulsed	80	А		
E _{AS}	Single Pulse Avalanche Energy (Note 1)		57	mJ		
PD	Power Dissipation		2.5	W		
	Derate above 25°C		20	mW/°C		
T_{J}, T_{STG}	Operating	and Storage Temperature	-55 to 150	°C		

MOSFFT MAXIMUM RATINGS ($T_A = 25^{\circ}C$ unless otherwise noted)

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Starting $T_J = 25^{\circ}C$, L = 1 mH, $I_{AS} = 10.7 \text{ A}$, $V_{DD} = 30 \text{ V}$, $V_{GS} = 10 \text{ V}$.

V _{DSS} MAX	r _{DS(on)} MAX	I _D MAX
30 V	14 mΩ @ 10 V	10.2 A
	17 mΩ @ 4.5 V	





= Wafer I of Number

L .	
YW	= Assembly Start Week

= onsemi Logo

\$Y

&Z

&2 &K

- = Assembly Plant Code
- = 2-Digit Code Format
- = 2-Digits Lot Run Traceability Code

PIN CONNECTIONS



ORDERING INFORMATION

See detailed ordering and shipping information on page 13 of this data sheet.

NOTE: Some of the devices on this data sheet have been DISCONTINUED. Please refer to the table on page 13.

THERMAL CHARACTERISTICS

Symbol	Parameter	Ratings	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case (Note 2)	25	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient (Note 2a)	50	°C/W
R _{θJA}	Thermal Resistance, Junction-to-Ambient (Note 2b)	125	°C/W

2. R_{0JA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. $R_{\theta JC}$ is guaranteed by design while $R_{\theta JA}$ is determined by the user's board design. a. 50°C/W when mounted on a 1in² pad of 2 oz copper. b. 125°C/W when mounted on a minimum pad.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
OFF CHAR	ACTERISTICS					
B _{VDSS}	Drain to Source Breakdown Voltage	$I_D = 250 \ \mu A, \ V_{GS} = 0 \ V$	30	-	-	V
I _{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 24 V, V_{GS} = 0 V$	-	-	1	μΑ
		$V_{DS} = 24 \text{ V}, V_{GS} = 0 \text{ V}, T_{J} = 150^{\circ}\text{C}$	-	-	250	
I _{GSS}	Gate to Source Leakage Current	$V_{GS} = \pm 20 V$	-	_	±100	nA
ON CHARA	CTERISTICS					
V _{GS(TH)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 250 \ \mu A$	1.2	-	2.5	V
r _{DS(on)}	Drain to Source On Resistance	$I_D = 10.2 \text{ A}, \text{ V}_{GS} = 10 \text{ V}$	-	11.0	14.0	mΩ
		$I_{D} = 9.3 \text{ A}, \text{ V}_{GS} = 4.5 \text{ V}$	-	13.8	17.0	
		I_D = 10.2 A, V_{GS} = 10 V, T_J = 150°C	-	17.5	22.7	
DYNAMIC C	CHARACTERISTICS					
C _{ISS}	Input Capacitance	V_{DS} = 15 V, V_{GS} = 0 V, f = 1 MHz	-	897	-	pF
C _{OSS}	Output Capacitance		-	190	-	pF
C _{RSS}	Reverse Transfer Capacitance		-	111	-	pF
R _G	Gate Resistance	$V_{GS} = 0.5 V$, f = 1 MHz	0.7	2.9	5.0	Ω
Q _{g(TOT)}	Total Gate Charge at 10 V	$V_{GS} = 0 V \text{ to } 10 V, V_{DD} = 15 V,$ $I_{D} = 10.2 A, I_{g} = 1.0 \text{ mA}$	-	17	26	nC
Q _{g(5)}	Total Gate Charge at 5 V	$V_{GS} = 0 V \text{ to } 5 V, V_{DD} = 15 V,$ $I_{D} = 10.2 A, I_{g} = 1.0 \text{ mA}$	-	9	14	nC
Q _{g(TH)}	Threshold Gate Charge	$V_{GS} = 0 V \text{ to } 1 V, V_{DD} = 15 V,$ $I_{D} = 10.2 A, I_{g} = 1.0 \text{ mA}$	-	0.9	1.4	nC
Q _{gs}	Gate to Source Gate Charge	V _{DD} = 15 V, I _D = 10.2 A, I _g = 1.0 mA	-	2.5	-	nC
Q _{gs2}	Gate Charge Threshold to Plateau		-	1.7	-	nC
Q _{gd}	Gate to Drain "Miller" Charge		_	3.3	_	nC
SWITCHING	G CHARACTERISTICS (V _{GS} = 10 V)					
t _{ON}	Turn–On Time	$V_{DD} = 15 \text{ V}, \text{ I}_{D} = 10.2 \text{ A}, \text{ V}_{GS} = 10 \text{ V},$	-	-	54	ns
t _{d(ON)}	Turn-On Delay Time	$R_{GS} = 16 \Omega$	-	7	-	ns
t _r	Rise Time		-	29	-	ns
t _{d(OFF)}	Turn-Off Delay Time		-	45	_	ns
t _f	Fall Time		-	18	-	ns
t _{OFF}	Turn–Off Time		-	-	94	ns
DRAIN-SO	URCE DIODE CHARACTERISTICS ANI	D MAXIMUM RATINGS				
V _{SD}	Source to Drain Diode Voltage	I _{SD} = 10.2 A	-	-	1.25	V
		I _{SD} = 2.1 A	-	-	1.0	V
t _{rr}	Reverse Recovery Time	$I_{SD} = 10.2$ A, $dI_{SD}/dt = 100$ A/ μ s	-	-	19	ns
Q _{RR}	Reverse Recovered Charge	$I_{SD} = 10.2 \text{ A}, \text{ d}I_{SD}/\text{d}t = 100 \text{ A}/\mu\text{s}$	-	-	9.5	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS

(T_J = 25°C unless otherwise noted)







Figure 2. Maximum Continuous Drain Current vs. Ambient Temperature



Figure 3. Normalized Maximum Transient Thermal Impedance





TYPICAL CHARACTERISTICS

(T_J = 25°C unless otherwise noted) (continued)







Figure 7. Saturation Characteristics





Figure 6. Transfer Characteristics



Figure 8. Drain to Source On Resistance vs. Gate Voltage and Drain Current





TYPICAL CHARACTERISTICS

 $(T_J = 25^{\circ}C \text{ unless otherwise noted})$ (continued)



Figure 12. Capacitance vs. Drain to Source Voltage



Figure 11. Forward Bis Safe Operating Area



Figure 13. Gate Charge Waveforms for Constant Gate Currents

TEST CIRCUITS AND WAVEFORMS



Figure 14. Unclamped Inductive Load Test Circuit



Figure 16. Gate Charge Test Circuit



Figure 18. Switching Time Test Circuit



Figure 15. Unclamped Inductive Waveforms



Figure 17. Gate Charge Waveforms



Figure 19. Switching Time Waveforms

THERMAL RESISTANCE VS. MOUNTING PAD AREA

The maximum rated junction temperature, T_{JM} , and the thermal resistance of the heat dissipating path determines the maximum allowable device power dissipation, P_{DM} , in an application. Therefore the application's ambient temperature, T_A (°C), and thermal resistance $R_{\theta JA}$ (°C/W) must be reviewed to ensure that T_{JM} is never exceeded. Equation 1 mathematically represents the relationship and serves as the basis for establishing the rating of the part.

$$P_{DM} = \frac{(T_{JM} - T_A)}{R_{\theta JA}}$$
 (eq. 1)

In using surface mount devices such as the SO8 package, the environment in which it is applied will have a significant influence on the part's current and maximum power dissipation ratings. Precise determination of P_{DM} is complex and influenced by many factors:

- 1. Mounting pad area onto which the device is attached and whether there is copper on one side or both sides of the board.
- 2. The number of copper layers and the thickness of the board.
- 3. The use of external heat sinks.
- 4. The use of thermal vias.
- 5. Air flow and board orientation.
- 6. For non steady state applications, the pulse width, the duty cycle and the transient thermal response of the part, the board and the environment they are in.

onsemi provides thermal information to assist the designer's preliminary application evaluation. Figure 20 defines the $R_{\theta JA}$ for the device as a function of the top copper (component side) area. This is for a horizontally positioned FR-4 board with 1 oz copper after 1000 seconds of steady state power with no air flow. This graph provides the necessary information for calculation of the steady state junction temperature or power dissipation. Pulse applications can be evaluated using the **onsemi** device Spice thermal model or manually utilizing the normalized maximum transient thermal impedance curve.

Thermal resistances corresponding to other copper areas can be obtained from Figure 20 or by calculation using Equation 2. The area, in square inches is the top copper area including the gate and source pads.

$$R_{\theta JA} = 64 + \frac{26}{0.23 + Area}$$
 (eq. 2)

The transient thermal impedance $(Z_{\theta JA})$ is also effected by varied top copper board area. Figure 21 shows the effect of copper pad area on single pulse transient thermal impedance. Each trace represents a copper pad area in square inches corresponding to the descending list in the graph. Spice and SABER thermal models are provided for each of the listed pad areas.

Copper pad area has no perceivable effect on transient thermal impedance for pulse widths less than 100 ms. For pulse widths less than 100 ms the transient thermal impedance is determined by the die and package. Therefore, CTHERM1 through CTHERM5 and RTHERM1 through RTHERM5 remain constant for each of the thermal models. A listing of the model component values is available in Table 1.



Figure 20. Thermal Resistance vs. Mounting Pad Area



Figure 21. Thermal Impedance vs. Mounting Pad Area

PSPICE ELECTRICAL MODEL

ESLC 51 50 VALUE={(V(5,51)/ABS(V(5,51)))*(PWR(V(5,51)/(1e-6*170),5))}

.MODEL DbodyMOD D (IS=2.0E-12 IKF=10 N=1.01 RS=7.0e-3 TRS1=8e-4 TRS2=2e-7 +CJO=3.5e-10 M=0.55 TT=7e-11 XTI=2) .MODEL DbreakMOD D (RS=0.2 TRS1=1e-3 TRS2=-8.9e-6) .MODEL DplcapMOD D (CJO=3.8e-10 IS=1e-30 N=10 M=0.45)

.MODEL MstroMOD NMOS (VTO=2.36 KP=150 IS=1e-30 N=10 TOX=1 L=1u W=1u) .MODEL MmedMOD NMOS (VTO=1.95 KP=5.0 IS=1e-30 N=10 TOX=1 L=1u W=1u RG=2.3) .MODEL MweakMOD NMOS (VTO=1.57 KP=0.02 IS=1e-30 N=10 TOX=1 L=1u W=1u RG=23 RS=0.1)

.MODEL RbreakMOD RES (TC1=8.3e-4 TC2=-8e-7) .MODEL RdrainMOD RES (TC1=15e-3 TC2=0.1e-5) .MODEL RSLCMOD RES (TC1=1e-4 TC2=1e-6) .MODEL RsourceMOD RES (TC1=1e-3 TC2=3e-6) .MODEL RvtempMOD RES (TC1=-1.8e-3 TC2=2e-7) .MODEL RvthresMOD RES (TC1=-2.0e-3 TC2=-6e-6) .MODEL S1AMOD VSWITCH (RON=1e-5 ROFF=0.1 VON=-4 VOFF=-3.5) .MODEL S1BMOD VSWITCH (RON=1e-5 ROFF=0.1 VON=-3.5 VOFF=-4) .MODEL S2AMOD VSWITCH (RON=1e-5 ROFF=0.1 VON=-1.5 VOFF=-1.0) .MODEL S2BMOD VSWITCH (RON=1e-5 ROFF=0.1 VON=-1.0 VOFF=-1.5)

.ENDS

NOTE: For further discussion of the PSPICE model, consult A New PSPICE Sub-Circuit for the Power MOSFET Featuring Global Temperature Options; IEEE Power Electronics Specialist Conference Records, 1991, written by William J. Hepp and C. Frank Wheatley.



Figure 22.

SABER ELECTRICAL MODEL

```
REV February 2005
template FDS8878 n2,n1,n3
electrical n2,n1,n3
var i iscl
dp..model \ dbodymod = (isl=2.0e-12, ikf=10, nl=1.01, rs=7.0e-3, trs1=8e-4, trs2=2e-7, cjo=3.5e-10, m=0.55, tt=7e-11, xti=2)
dp..model dbreakmod = (rs=0.2, trs1=1e-3, trs2=-8.9e-6)
dp..model dplcapmod = (cjo=3.8e-10, isl=10e-30, nl=10, m=0.45)
m..model mstrongmod = (type=_n, vto=2.36, kp=150, is=1e-30, tox=1)
m..model mmedmod = (type=_n, vto=1.95, kp=5.0, is=1e-30, tox=1)
m..model mweakmod = (type=_n, vto=1.57, kp=0.02, is=1e-30, tox=1, rs=0.1)
sw vcsp..model s1amod = (ron=1e-5,roff=0.1,von=-4,voff=-3.5)
sw vcsp..model s1bmod = (ron=1e-5, roff=0.1, von=-3.5, voff=-4)
sw vcsp..model s2amod = (ron=1e-5, roff=0.1, von=-1.5, voff=-1.0)
sw_vcsp..model s2bmod = (ron=1e-5, roff=0.1, von=-1.0, voff=-1.5)
c.ca n12 n8 = 7.8e - 10
c.cb n15 n14 = 7.8e - 10
c.cin n6 n8 = .78e-9
dp.dbody n7 n5 = model=dbodymod
dp.dbreak n5 n11 = model=dbreakmod
dp.dplcap n10 n5 = model=dplcapmod
spe.ebreak n11 n7 n17 n18 = 32.9
spe.eds n14 n8 n5 n8 = 1
spe.egs n13 n8 n6 n8 = 1
spe.esg n6 n10 n6 n8 = 1
spe.evthres n6 n21 n19 n8 = 1
spe.evtemp n20 n6 n18 n22 = 1
i.it n8 n17 = 1
1.1gate n1 n9 = 5.29e-9
1.1 drain n2 n5 = 1.0 e-9
1.1source n3 n7 = 0.18e-9
res.rlgate n1 n9 = 52.9
res.rldrain n2 n5 = 10
res.rlsource n3 n7 = 1.8
m.mmed n16 n6 n8 n8 = model=mmedmod, l=1u, w=1u
m.mstrong n16 n6 n8 n8 = model=mstrongmod, l=1u, w=1u
m.mweak n16 n21 n8 n8 = model=mweakmod, l=1u, w=1u
res.rbreak n17 n18 = 1, tc1=8.3e-4,tc2=-8e-7
res.rdrain n50 n16 = 1.6e-3, tc1=15e-3,tc2=0.1e-5
res.rgate n9 n20 = 2.3
res.rslc1 n5 n51 = 1e-6, tc1=1e-4, tc2=1e-6
res.rslc2 n5 n50 = 1e3
res.rsource n8 n7 = 8.9e-3, tc1=1e-3,tc2=3e-6
res.rvthres n22 n8 = 1, tc1 = -2.0e - 3, tc2 = -6e - 6
res.rvtemp n18 n19 = 1, tc1=-1.8e-3,tc2=2e-7
sw vcsp.s1a n6 n12 n13 n8 = model=s1amod
sw_vcsp.s1b n13 n12 n13 n8 = model=s1bmod
sw vcsp.s2a n6 n15 n14 n13 = model=s2amod
```

```
sw_vcsp.s2b n13 n15 n14 n13 = model=s2bmod
```

```
v.vbat n22 n19 = dc=1
equations {
 i (n51->n50) +=iscl
 iscl: v(n51,n50) = ((v(n5,n51)/(1e-9+abs(v(n5,n51))))*((abs(v(n5,n51)*1e6/170))** 5))
 }
}
```



Figure 23.

SPICE THERMAL MODEL

REV February 2005 FDS8878T Copper Area =1.0 in² CTHERM1 TH 8 2.0e-3 CTHERM2 8 7 5.0e-3 CTHERM3 7 6 1.0e-2 CTHERM4 6 5 4.0e-2 CTHERM5 5 4 9.0e-2 CTHERM6 4 3 2e-1 CTHERM6 4 3 21 CTHERM7 3 2 1 CTHERM8 2 TL 3

SABER THERMAL MODEL

Copper Area = 1.0 in^2 template thermal_model th tl thermal_c th, tl { ctherm.ctherm1 th 8 = 2.0e - 3ctherm.ctherm2 8 7 = 5.0e-3ctherm.ctherm3 7 6 =1.0e-2 ctherm.ctherm4 6 5 = 4.0e-2ctherm.ctherm5 5 4 = 9.0e-2ctherm.ctherm643 = 2e - 1ctherm.ctherm7 3 2 1 ctherm.ctherm8 2 tl 3 rtherm.rtherm1 th 8 = 1e-1rtherm.rtherm2 8 7 = 5e-1 rtherm.rtherm376=1rtherm.rtherm4 6 5 = 5 rtherm.rtherm5 5 4 = 8 rtherm.rtherm6 4 3 =12 rtherm.rtherm7 3 2 = 18rtherm.rtherm8 2 tl =25

}



Table 1. THERMAL MODES

COMPONANT	0.04 in ²	0.28 in ²	0.52 in ²	0.76 in ²	1.0 in ²
CTHERM6	1.2e–1	1.5e–1	2.0e-1	2.0e-1	2.0e-1
CTHERM7	0.5	1.0	1.0	1.0	1.0
CTHERM8	1.3	2.8	3.0	3.0	3.0
RTHERM6	26	20	15	13	12
RTHERM7	39	24	21	19	18
RTHERM8	55	38.7	31.3	29.7	25

PACKAGE MARKING AND ORDERING INFORMATION

Device	Device Marking	Package Type	Reel Size	Tape Width	Shipping [†]
FDS8878	FDS8878	SOIC8 (SO-8) (Pb-Free)	330 mm	12 mm	2500 / Tape & Reel

DISCONTINUED (Note 3)

FDS8878-F123	FDS8878	SOIC8 (SO-8)	13"	12 mm	2500 / Tape & Reel
		(Pb-Free)			

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.
3. DISCONTINUED: This device is not recommended for new design. Please contact your onsemi representative for information. The most

current information on this device may be available on www.onsemi.com.

POWERTRENCH is registered trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.

MECHANICAL CASE OUTLINE PACKAGE DIMENSIONS





onsemi and OI ISCITIL are trademarks or Semiconductor Components industries, LLC doa onsemi or its subsidiaries in the United States and/or other countries. Onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>