

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unavteries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or i, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor and is officers, employees, uniotificated use, even if such claim any manner.



FGPF4565 650 V Field Stop Trench IGBT


Features

- High Current Capability
- Low Saturation Voltage: V_{CE(sat)} =1.5 V(Typ.) @ I_C = 30 A
- High Input Impedance
- RoHS Compliant

Applications

• IPL (Intense Pulsed Light)

G C E TO-220F (Retractable)



Using innovative field stop IGBT technology, Fairchild's new series of field stop trench IGBTs offer the optimum performance

General Description

for IPL (Intense Pulsed Light).

Absolute Maximum Ratings TC = 25°C unless otherwise noted

| Symbol | Description | | Ratings | Unit | |
|---------------------------|--|---------------------------------------|-------------|------|--|
| V _{CES} | Collector to Emitter Voltage | | 650 | V | |
| V _{GES} | Gate to Emitter Voltage | | ± 25 | V | |
| I _{C pulse (1)*} | Pulsed Collector Current | @ T _C = 25°C | 170 | A | |
| P _D | Maximum Power Dissipation | @ T _C = 25 ^o C | 30 | W | |
| | Maximum Power Dissipation | @ T _C = 100 ^o C | 12 | W | |
| TJ | Operating Junction Temperature | | -55 to +150 | °C | |
| T _{stg} | Storage Temperature Range | | -55 to +150 | °C | |
| TL | Maximum Lead Temp. for soldering Purposes, 1/8" from case for 5 seconds | | 300 | °C | |

Thermal Characteristics

| Symbol | Parameter | Тур. | Max. | Unit |
|-----------------------|---|------|------|------|
| $R_{	extsf{	heta}JC}$ | Thermal Resistance, Junction to Case, Max. | - | 4.1 | °C/W |
| $R_{	extsf{	heta}JA}$ | Thermal Resistance, Junction to Ambient, Max. | - | 62.5 | °C/W |

Notes:

1. Half sine wave: D< 0.01, pulse width < 1usec,

* Ic pulse limit by max Tj

November 2014

| Part Nu | nber | er Top Mark | Package | Packing Method | Reel Size | Tape Wi | dth Q | Quantity | |
|---|---|---------------------------|--|--|--------------------|---------|----------|----------|--|
| FGPF4565 | | FGPF4565 | TO-220F | Tube | N/A | N/A | | 50 | |
| Electric | al Cha | aracteristics | s of the IC | BT T _C = 25°C unless otherv | <i>v</i> ise noted | | | | |
| Symbol | | | Test Conditions Min | | . Тур. | Max. | Unit | | |
| Off Charac | teristics | | | | | | | | |
| BV _{CES} | Collecto | or to Emitter Break | lown Voltage | V _{GE} = 0 V, I _C = 1 mA | 650 | - | - | V | |
| ΔBV _{CES} / ΔT _J | Temperature Coefficient of Breakdown Voltage | | $V_{GE} = 0 \text{ V}, \text{ I}_{C} = 1 \text{ mA}$ | | 0.65 | - | V/ºC | | |
| ICES | Collecto | Collector Cut-Off Current | | V _{CE} = V _{CES} , V _{GE} = 0 V | | - | 250 | μA | |
| I _{GES} | G-E Lea | akage Current | | $V_{GE} = V_{GES}, V_{CE} = 0 V$ | - | - | ±400 | nA | |
| On Charac | eristics | | | | | | | | |
| V _{GE(th)} | G-E Th | reshold Voltage | | I _C = 250 μA, V _{CE} = V _{GE} | 3.0 | 4.0 | 5.0 | V | |
| | Collector to Emitter Saturation Voltage | | | $I_{\rm C} = 20$ A, $V_{\rm GE} = 15$ V | - | 1.35 | - | V | |
| V _{CE(sat)} | | | I _C = 30 A, V _{GE} = 15 V | - | 1.50 | 1.88 | V | | |
| | | | | $I_{C} = 30 \text{ A}, V_{GE} = 15 \text{ V},$ $T_{C} = 150^{\circ}\text{C}$ | - | 1.75 | - | v | |
| Dynamic C | haracter | istics | | | | | | | |
| C _{ies} | - | apacitance | | | | 1650 | - | pF | |
| C _{oes} | - | t Capacitance | | $V_{CE} = 30 V, V_{GE} = 0 V,$ | - | 34 | - | pF | |
| C _{res} | Reverse Transfer Capacitance | | f = 1 MHz | - | 17 | - | pF | | |
| Switching | Characte | eristics | | | | | | | |
| t _{d(on)} | Turn-Or | n Delay Time | | | - | 11.2 | - | ns | |
| t _r | Rise Tir | ne | | V_{CC} = 400 V, I _C = 30 A, R _G = 5 Ω , V _{GE} = 15 V, Resistive Load, T _C = 25°C | - | 44.8 | - | ns | |
| t _{d(off)} | Turn-Of | f Delay Time | | | c - | 40.8 | - / | ns | |
| t _f | Fall Tim | e | | | - | 153 | - | ns | |
| t _{d(on)} | Turn-Or | n Delay Time | | | - | 12.8 | - | ns | |
| t _r | Rise Tir | ne | | $V_{CC} = 400 \text{ V}, \text{ I}_{C} = 30 \text{ A},$ | - | 59.2 | - | ns | |
| t _{d(off)} | Turn-Of | f Delay Time | | $R_G = 5 \Omega$, $V_{GE} = 15 V$, Resistive Load, $T_C = 150$ | °C - | 40.8 | - | ns | |
| t _f | Fall Tim | ie | | | - | 202 | - | ns | |
| Qg | Total Ga | ate Charge | | | - | 40.3 | - | nC | |
| Q _{ge} | Gate to | Emitter Charge | | $V_{CE} = 400 \text{ V}, I_{C} = 30 \text{ A},$ $V_{GE} = 15 \text{ V}$ | - | 8.8 | - | nC | |
| Q _{gc} | Gate to | Collector Charge | | GE - 10 V | - | 10.4 | <u> </u> | nC | |

FGPF4565 — 650 V Field Stop Trench IGBT

Typical Performance Characteristics Figure 1. Typical Output Characteristics Figure 2. Typical Output Characteristics 180 180 20V T_C = 25^oC T_C = 150[°]C 12V 10V 5\ 12V 150 150 Collector Current, I_c [A] 20\ Collector Current, Ic [A] 10V 120 120 15V 90 90 V_{GE} = 8V V_{GE} = 8V 60 60 30 30 0 0 0 2 3 4 5 0 2 3 4 5 6 6 1 Collector-Emitter Voltage, V_{CE} [V] Collector-Emitter Voltage, V_{CE} [V] Figure 3. Typical Saturation Voltage Figure 4. Saturation Voltage vs. Case **Characteristics Temperature at Variant Current Level** 2.5 180 Common Emitter $V_{GE} = 15V$ Collector-Emitter Voltage, V_{CE} [V] 150 Collector Current, Ic [A] 60A 2 120 90 30A 60 Common Emitter V_{GE} = 15V T_C = 25^oC ____ 30 T_C = 150^oC ... I_C = 15A 1 0 -55 -30 0 30 60 90 120 0 2 3 4 5 6 Collector-Emitter Case Temperature, T_C [°C] Collector-Emitter Voltage, V_{CE} [V] Figure 5. Saturation Voltage vs. V_{GE} Figure 6. Saturation Voltage vs. V_{GE} 20 20 Common Emitter Common Emitter T_C = 150^oC Collector-Emitter Voltage, V_{CE} [V] $T_c = 25^{\circ}C$ Collector-Emitter Voltage, V_{CE} [V] 16 16 12 12 $I_{\rm C} = 15A$ $I_{\rm C} = 15A$ 30A 30A 8 8 60A 60A 4 Δ 0 ∟ 4 0 8 12 16 20 4 8 12 16 Gate-Emitter Voltage, V_{GE} [V] Gate-Emitter Voltage, V_{GE} [V] ©2014 Fairchild Semiconductor Corporation


FGPF4565 Rev. C0

www.fairchildsemi.com

20


150

FGPF4565 — 650 V Field Stop Trench IGBT




©2014 Fairchild Semiconductor Corporation FGPF4565 Rev. C0

www.fairchildsemi.com



FGPF4565 — 650 V Field Stop Trench IGBT



ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC