

# NPN Epitaxial Silicon Transistor

## FJL4315, 2SC5200

### Features

- High Current Capability:  $I_C = 17\text{ A}$
- High Power Dissipation: 150 W
- High Frequency: 30 MHz
- High Voltage:  $V_{CEO} = 250\text{ V}$
- Wide S.O.A. for Reliable Operation
- Excellent Gain Linearity for Low THD
- Complement to 2SA1943 / FJL4215
- Thermal and Electrical Spice Models are Available
- Same Transistor is also Available in:
  - ◆ TO3P Package, 2SC5242 / FJA4313 : 130 Watts
  - ◆ TO220 Package, FJP5200 : 80 Watts
  - ◆ TO220F Package, FJPF5200 : 50 Watts
- These Devices are Pb-Free and are RoHS Compliant

### Applications

- High-Fidelity Audio Output Amplifier
- General Purpose Power Amplifier

### ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Ratings	Units
Collector-Base Voltage	$BV_{CBO}$	250	V
Collector-Emitter Voltage	$BV_{CEO}$	250	V
Emitter-Base Voltage	$BV_{EBO}$	5	V
Collector Current (DC)	$I_C$	17	A
Base Current	$I_B$	1.5	A
Total Device Dissipation ( $T_C = 25^\circ\text{C}$ ) Derate Above $25^\circ\text{C}$	$P_D$	150 1.04	W W/ $^\circ\text{C}$
Junction and Storage Temperature	$T_J, T_{STG}$	-50 ~ +150	$^\circ\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

### THERMAL CHARACTERISTICS (Note 1)


( $T_A = 25^\circ\text{C}$  unless otherwise noted)

Parameter	Symbol	Max.	Units
Thermal Resistance, Junction to Case	$R_{\theta JC}$	0.83	$^\circ\text{C}/\text{W}$


1. Device mounted on minimum pad size.

### $h_{FE}$ CLASSIFICATION

Classification	R	O
$h_{FE1}$	55 ~ 110	80 ~ 160



### MARKING DIAGRAM



A = Assembly Location  
 YWW = Date Code  
 ZZ = Assembly Lot  
 xxxxx = Specific Device Code  
 (J4315O or C5200O)

### ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

## FJL4315, 2SC5200

### ELECTRICAL CHARACTERISTICS (Note 2) ( $T_C = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
$BV_{CBO}$	Collector-Base Breakdown Voltage	$I_C = 5 \text{ mA}, I_E = 0$	250			V
$BV_{CEO}$	Collector-Emitter Breakdown Voltage	$I_C = 10 \text{ mA}, R_{BE} = \infty$	250			V
$BV_{EBO}$	Emitter-Base Breakdown Voltage	$I_E = 5 \text{ mA}, I_C = 0$	5			V
$I_{CBO}$	Collector Cut-Off Current	$V_{CB} = 230 \text{ V}, I_E = 0$			5.0	$\mu\text{A}$
$I_{EBO}$	Emitter Cut-Off Current	$V_{EB} = 5 \text{ V}, I_C = 0$			5.0	$\mu\text{A}$
$h_{FE1}$	DC Current Gain	$V_{CE} = 5 \text{ V}, I_C = 1 \text{ A}$	55		160	
$h_{FE2}$	DC Current Gain	$V_{CE} = 5 \text{ V}, I_C = 7 \text{ A}$	35	60		
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	$I_C = 8 \text{ A}, I_B = 0.8 \text{ A}$		0.4	3.0	V
$V_{BE(on)}$	Base-Emitter On Voltage	$V_{CE} = 5 \text{ V}, I_C = 7 \text{ A}$		1.0	1.5	V
$f_T$	Current Gain Bandwidth Product	$V_{CE} = 5 \text{ V}, I_C = 1 \text{ A}$		30		MHz
$C_{ob}$	Output Capacitance	$V_{CB} = 10 \text{ V}, f = 1 \text{ MHz}$		200		pF

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

2. Pulse Test: Pulse Width = 20  $\mu\text{s}$ , Duty Cycle  $\leq 2\%$

### ORDERING INFORMATION

Part Number	Marking	Package	Shipping	Remarks
2SC5200OTU	C5200O	TO-264-3LD (Pb-Free)	375 Units / Tube	$h_{FE1}$ O grade
FJL4315OTU	J4315O	TO-264-3LD (Pb-Free)	375 Units / Tube	$h_{FE1}$ O grade

TYPICAL CHARACTERISTICS




Figure 1. Static Characteristic




Figure 2. DC Current Gain (R Grade)




Figure 3. DC Current Gain (O Grade)




Figure 4. Collector-Emitter Saturation Voltage




Figure 5. Base-Emitter On Voltage






Figure 6. Base-Emitter Saturation Voltage

# FJL4315, 2SC5200


## TYPICAL CHARACTERISTICS



**Figure 7. Power Derating**




**Figure 8. Safe Operating Area**



**Figure 9. Power Derating**

TO-264-3LD  
CASE 340CA  
ISSUE O

DATE 31 OCT 2016



NOTES:

- A. PACKAGE REFERENCE: JEDEC TO264 VARIATION AA.
- B. ALL DIMENSIONS ARE IN MILLIMETERS.
- C. OUT OF JEDEC STANDARD VALUE.
- D. DIMENSION AND TOLERANCE AS PER ASME Y14.5-1994.
- E. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.

DOCUMENT NUMBER:	98AON13860G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-264-3LD	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

---

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at [www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)