ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,



ON Semiconductor®

FQB10N50CF


N-Channel QFET $^{\mathbb{R}}$ FRFET $^{\mathbb{R}}$ MOSFET 500 V, 10 A, 610 m $_{\Omega}$


Features

- 10 A, 500 V, $R_{DS(on)}$ = 610 m Ω (Max.) @ V_{GS} = 10 V, I_D = 5 A
- Low gate charge (Typ. 45 nC)
- Low Crss (Typ. 17.5 pF)
- · 100% avalanche tested
- · Fast recovery body diode

Description

This N-Channel enhancement mode power MOSFET is produced using ON Semiconductor's proprietary planar stripe and DMOS technology. This advanced MOSFET technology has been especially tailored to reduce on-state resistance, and to provide superior switching performance and high avalanche energy strength. These devices are suitable for switched mode power supplies, active power factor correction (PFC), and electronic lamp ballasts.





MOSFET Maximum Ratings T_C = 25°C unless otherwise noted

Symbol	Parameter			FQB10N50CFTM-WS	Unit	
V_{DSS}	Drain to Source Voltage		500	V		
V _{GSS}	Gate to Source Voltage			±30	V	
1	Drain Current	- Continuous (T _C = 25°C)		10	А	
ID	Dialifourient	- Continuous (T _C = 100°C)	- Continuous (T _C = 100°C)			
I_{DM}	Drain Current	- Pulsed	(Note 1)	40	Α	
E _{AS}	Single Pulsed Avalanche Energy (Note 2)		825	mJ		
I _{AR}	Avalanche Current		(Note 1)	10	Α	
E _{AR}	Repetitive Avalanche Ener	gy	(Note 1)	14.3	mJ	
dv/dt	Peak Diode Recovery dv/d	It	(Note 3)	2.0	V/ns	
D	Dawer Dissination	(T _C = 25°C)		143	W	
P_{D}	Power Dissipation	- Derate above 25°C		1.14	W/°C	
T _J , T _{STG}	Operating and Storage Ter	mperature Range		-55 to +150	°C	
T _L	Maximum Lead Temperatu	•		300	°C	

Thermal Characteristics

Symbol	Parameter	FQB10N50CFTM-WS	Unit
R_{\thetaJC}	Thermal Resistance, Junction to Case, Max	0.87	
В	Thermal Resistance, Junction to Ambient (minimum pad of 2 oz copper), Max.	62.5	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (1 in ² pad of 2 oz copper), Max.	40	

Package Marking and Ordering Information T_C = 25°C unless otherwise noted

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FQB10N50CF	FQB10N50CFTM-WS	D2-PAK	330mm	24mm	800

Electrical Characteristics

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
Off Charac	cteristics					
BV _{DSS}	Drain to Source Breakdown Voltage	$I_D = 250\mu A$, $V_{GS} = 0V$, $T_J = 25^{\circ}C$	500	-	-	V
ΔBV _{DSS} / ΔT _J	Breakdown Voltage Temperature Coefficient	I _D = 250μA, Referenced to 25°C	-	0.5	-	V/°C
1	Zero Gate Voltage Drain Current	V _{DS} = 500V , V _{GS} = 0V	-	-	10	^
DSS	Zero Gate voltage Drain Current	$V_{DS} = 400V, T_{C} = 125^{\circ}C$	-	-	100	μA
I _{GSS}	Gate to Body Leakage Current	$V_{GS} = \pm 30V, V_{DS} = 0V$	-	-	±100	nA

On Characteristics

V _{GS(th)}	Gate Threshold Voltage	$V_{GS} = V_{DS}, I_{D} = 250 \mu A$	2.0	-	4.0	V
R _{DS(on)}	Static Drain to Source On Resistance	$V_{GS} = 10V, I_D = 5A$	1	0.51	0.61	Ω
9 _{FS}	Forward Transconductance	V _{DS} = 20V, I _D = 5A	-	105	-	S

Dynamic Characteristics

C _{iss}	Input Capacitance	\\ - 25\\ \\ - 0\\	V _{DS} = 25V, V _{GS} = 0V	-	1660	2210	pF
Coss	Output Capacitance	v _{DS} = 25v, v _{GS} = 0v f = 1MHz		-	182	240	pF
C _{rss}	Reverse Transfer Capacitance	1 - 11/11/12	•	-	17.5	26	pF
Q _{g(tot)}	Total Gate Charge at 10V			-	45	60	nC
Q_{gs}	Gate to Source Gate Charge	$V_{DS} = 400V, I_{D} = 10A$	•	-	8	-	nC
Q _{gd}	Gate to Drain "Miller" Charge	V _{GS} = 10V	(Note 4)	-	19	-	nC

Switching Characteristics

t _{d(on)}	Turn-On Delay Time			-	25	60	ns
t _r	Turn-On Rise Time	$V_{DD} = 250V, I_{D} = 10A$	•	-	47	105	ns
t _{d(off)}	Turn-Off Delay Time	$R_G = 25\Omega$	•	-	138	285	ns
t _f	Turn-Off Fall Time		(Note 4)	-	55	120	ns

Drain-Source Diode Characteristics

I _S	Maximum Continuous Drain to Source Diode Forward Current			-	10	Α
I _{SM}	Maximum Pulsed Drain to Source Diode Forward Current			-	40	Α
V_{SD}	Drain to Source Diode Forward Voltage V _{GS} = 0V, I _{SD} = 10A		-	-	1.4	V
t _{rr}	Reverse Recovery Time	$V_{GS} = 0V, I_{SD} = 10A$	-	91	-	ns
Q _{rr}	Reverse Recovery Charge	$dI_F/dt = 100A/\mu s$	-	220	-	nC

- **Notes:**1. Repetitive Rating: Pulse width limited by maximum junction temperature 2: L = 16.5mH, I_{AS} = 10A, V_{DD} = 50V, R_{G} = 25 Ω , Starting T_{J} = 25°C 3: $I_{SD} \le$ 10A, $di/dt \le$ 200A/ μ s, $V_{DD} \le$ BV $_{DSS}$, Starting T_{J} = 25°C 4: Essentially Independent of Operating Temperature Typical Characteristics

Typical Performance Characteristics

Figure 1. On-Region Characteristics




Figure 3. On-Resistance Variation vs.
Drain Current and Gate Voltage




Figure 5. Capacitance Characteristics




Figure 2. Transfer Characteristics




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperature





Figure 6. Gate Charge Characteristics



Typical Performance Characteristics (Continued)

Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 9. Maximum Safe Operating Area




Figure 8. On-Resistance Variation vs. Temperature




Figure 10. Maximum Drain Current vs. Case Temperature




Figure 11. Transient Thermal Response Curve




Figure 12. Gate Charge Test Circuit & Waveform




Figure 13. Resistive Switching Test Circuit & Waveforms





Figure 14. Unclamped Inductive Switching Test Circuit & Waveforms







Figure 15. Peak Diode Recovery dv/dt Test Circuit & Waveforms



Mechanical Dimensions

TO-263 2L (D²PAK)




Figure 16. 2LD, TO263, Surface Mount

Package drawings are provided as a service to customers considering ON Semiconductor components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a ON Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of ON Semiconductor's worldwide terms and conditions, specif-ically the warranty therein, which covers ON Semiconductor products.

Dimension in Millimeters

ON Semiconductor and III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative