MBR0520LT1G, SBR80520LT1G, MBR0520LT3G, SBR80520LT3G

Preferred Devices

Surface Mount Schottky Power Rectifier

Plastic SOD-123 Package

The Schottky Power Rectifier employs the Schottky Barrier principle with a barrier metal that produces optimal forward voltage drop-reverse current tradeoff. Ideally suited for low voltage, high frequency rectification, or as free wheeling and polarity protection diodes in surface mount applications where compact size and weight are critical to the system. This package provides an alternative to the leadless 34 MELF style package. These state-of-the-art devices have the following features:

Features

- Guardring for Stress Protection
- Very Low Forward Voltage (0.38 V Max @ 0.5 A, 25°C)
- 125°C Operating Junction Temperature
- Epoxy Meets UL 94 V-0 @ 0.125 in
- Package Designed for Optimal Automated Board Assembly
- AEC-Q101 Qualified and PPAP Capable
- SBR8 Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements
- All Packages are Pb-Free*

Mechanical Characteristics

- Polarity Designator: Cathode Band
- Weight: 11.7 mg (approximately)
- Case: Epoxy, Molded
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Max. for 10 Seconds
- ESD Ratings:
 - ◆ Human Body Model = 3B
 - ♦ Machine Model = C



ON Semiconductor®

http://onsemi.com

SCHOTTKY BARRIER RECTIFIER 0.5 AMPERES, 20 VOLTS



SOD-123 CASE 425 STYLE 1

MARKING DIAGRAM



B2	= Device Code
Μ	= Date Code
•	= Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping [†]		
MBR0520LT1G	SOD-123 (Pb-Free)	3,000 / Tape & Reel **		
SBR80520LT1G	SOD-123 (Pb-Free)	3,000 / Tape & Reel **		
MBR0520LT3G	SOD-123 (Pb-Free)	10,000 / Tape & Reel ***		
SBR80520LT3G	SOD-123 (Pb-Free)	10,000 / Tape & Reel ***		

** 8 mm Tape, 7" Reel

and best overall value.

*** 8 mm Tape, 13" Reel

+ For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

Preferred devices are recommended choices for future use

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

© Semiconductor Components Industries, LLC, 2012 January, 2012 – Rev. 6

MBR0520LT1G, SBR80520LT1G, MBR0520LT3G, SBR80520LT3G

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _R	20	V
Average Rectified Forward Current (Rated V_R , $T_L = 90^{\circ}C$)	I _{F(AV)}	0.5	A
Non-Repetitive Peak Surge Current (Surge Applied at Rated Load Conditions Halfwave, Single Phase, 60 Hz)	I _{FSM}	5.5	А
Storage Temperature Range	T _{stg}	-65 to +150	°C
Operating Junction Temperature	TJ	-65 to +125	°C
Voltage Rate of Change (Rated V _R)	dv/dt	1000	V/μs
ESD Ratings: Machine Model = C Human Body Model = 3B		> 400 > 8000	V

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

THERMAL CHARACTERISTICS

Characteristic		Value	Unit
Thermal Resistance; Junction-to-Ambient (Note 1)	R_{\thetaJA}	206	°C/W
Thermal Resistance; Junction-to-Lead	$R_{ ext{ heta}JL}$	150	°C/W


1. 1 inch square pad size (1 x 0.5 inch for each lead) on FR4 board.

ELECTRICAL CHARACTERISTICS


Characteristic	Symbol	Value		Unit
Maximum Instantaneous Forward Voltage (Note 2)	VF	$T_J = 25^{\circ}C$	$T_{\rm J} = 100^{\circ}{\rm C}$	V
(i _F = 0.1 Amps) (i _F = 0.5 Amps)		0.300 0.385	0.220 0.330	
Maximum Instantaneous Reverse Current (Note 2)	I _R	T _J = 25°C	$T_J = 100^{\circ}C$	mA
(V _R = 10 V) (Rated DC Voltage = 20 V)		75 μΑ 250 μΑ	5 mA 8 mA	

2. Pulse Test: Pulse Width = 300 μ s, Duty Cycle < 2%.

MBR0520LT1G, SBR80520LT1G, MBR0520LT3G, SBR80520LT3G



ONSEM¹.



onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>