## **ON Semiconductor**

## Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,



ON Semiconductor®

## FQA8N90C-F109


# N-Channel QFET $^{\circledR}$ MOSFET 900 V, 8 A, 1.9 $\Omega$


## **Features**

- 8 A, 900 V,  $R_{DS(on)}$  = 1.9  $\Omega$  (Max.) @  $V_{GS}$  = 10 V,  $I_D$  = 4 V
- Low Gate Charge (Typ. 35 nC)
- Low Crss (Typ. 12 pF)
- 100% Avalanche Tested
- · RoHS Compliant

## **Description**

This N-Channel enhancement mode power MOSFET is produced using ON Semiconductor's proprietary planar stripe and DMOS technology. This advanced MOSFET technology has been especially tailored to reduce on-state resistance, and to provide superior switching performance and high avalanche energy strength. These devices are suitable for switched mode power supplies, active power factor correction (PFC), and electronic lamp ballasts.





## Absolute Maximum Ratings T<sub>C</sub> = 25°C unless otherwise noted.

Symbol	Parameter		FQA8N90C-F109	Unit
V <sub>DSS</sub>	Drain-Source Voltage		900	V
I <sub>D</sub>	Drain Current - Continuous ( $T_C = 25^{\circ}C$ )		8.0	Α
	- Continuous ( $T_C = 100^{\circ}C$ )		5.1	Α
I <sub>DM</sub>	Drain Current - Pulsed	(Note 1)	32	Α
V <sub>GSS</sub>	Gate-Source Voltage		± 30	V
E <sub>AS</sub>	Single Pulsed Avalanche Energy	(Note 2)	850	mJ
I <sub>AR</sub>	Avalanche Current	(Note 1)	8.0	Α
E <sub>AR</sub>	Repetitive Avalanche Energy (Note 1)		24	mJ
dv/dt	Peak Diode Recovery dv/dt	(Note 3)	4.0	V/ns
P <sub>D</sub>	Power Dissipation (T <sub>C</sub> = 25°C)		240	W
	- Derate above 25°C		1.92	W/°C
T <sub>J</sub> , T <sub>STG</sub>	Operating and Storage Temperature Range		-55 to +150	°C
T <sub>L</sub>	Maximum lead temperature for soldering purposes, 1/8" from case for 5 seconds		300	°C

## **Thermal Characteristics**

Symbol	Parameter	FQA8N90C-F109	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case, Max.	0.52	°C/W
$R_{\theta CS}$	Thermal Resistance, Case-to-Sink, Typ.	0.24	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient, Max.	40	°C/W

## Package Marking and Ordering Information

Part Number	Top Mark	Package	Packing Method	Reel Size	Tape Width	Quantity
FQA8N90C-F109	FQA8N90C	TO-3PN	Tube	N/A	N/A	30 units

## **Electrical Characteristics** $T_C = 25^{\circ}C$ unless otherwise noted.

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
Off Charac	cteristics					
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	$V_{GS}$ = 0 V, $I_{D}$ = 250 $\mu$ A	900			V
$\Delta BV_{DSS}/$ $\Delta T_{J}$	Breakdown Voltage Temperature Coefficient	$I_D$ = 250 $\mu$ A, Referenced to 25°C		0.95		V/°C
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> = 900 V, V <sub>GS</sub> = 0 V			10	μА
		V <sub>DS</sub> = 720 V, T <sub>C</sub> = 125°C			100	μА
I <sub>GSSF</sub>	Gate-Body Leakage Current, Forward	V <sub>GS</sub> = 30 V, V <sub>DS</sub> = 0 V	-		100	nA
I <sub>GSSR</sub>	Gate-Body Leakage Current, Reverse	V <sub>GS</sub> = -30 V, V <sub>DS</sub> = 0 V			-100	nA
On Charac	teristics					
V <sub>GS(th)</sub>	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_{D} = 250 \mu A$	3.0		5.0	V
R <sub>DS(on)</sub>	Static Drain-Source On-Resistance	V <sub>GS</sub> = 10 V, I <sub>D</sub> = 4.0 A		1.6	1.9	Ω
9 <sub>FS</sub>	Forward Transconductance	V <sub>DS</sub> = 50 V, I <sub>D</sub> = 4.0 A	1	5.5		S
Dynamic C	haracteristics					
C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> = 25 V, V <sub>GS</sub> = 0 V,		1600	2080	pF
C <sub>oss</sub>	Output Capacitance	f = 1.0 MHz		130	170	pF
C <sub>rss</sub>	Reverse Transfer Capacitance	-	-	12	15	pF
Switching (	Characteristics					
t <sub>d(on)</sub>	Turn-On Delay Time	V <sub>DD</sub> = 450 V, I <sub>D</sub> = 11.0A,		40	90	ns
t <sub>r</sub>	Turn-On Rise Time	$R_G = 25 \Omega$	-	110	230	ns
t <sub>d(off)</sub>	Turn-Off Delay Time			70	150	ns
t <sub>f</sub>	Turn-Off Fall Time	(Note 4)		70	150	ns
Qg	Total Gate Charge	V <sub>DS</sub> = 720 V, I <sub>D</sub> = 11.0A,		35	45	nC
Q <sub>gs</sub>	Gate-Source Charge	V <sub>GS</sub> = 10 V	-	10		nC
Q <sub>gd</sub>	Gate-Drain Charge	(Note 4)	-	14		nC
Drain-Sour	ce Diode Characteristics and Maximum Ratings					
I <sub>S</sub>	Maximum Continuous Drain-Source Diode Forward Current				8.0	Α
I <sub>SM</sub>	Maximum Pulsed Drain-Source Diode Forward Current				32.0	Α
V <sub>SD</sub>	Drain-Source Diode Forward Voltage	V <sub>GS</sub> = 0 V, I <sub>S</sub> = 8.0 A			1.4	V
t <sub>rr</sub>	Reverse Recovery Time	$V_{GS} = 0 \text{ V}, I_{S} = 8.0 \text{ A},$		530		ns
Q <sub>rr</sub>	Reverse Recovery Charge	$dI_F / dt = 100 A/\mu s$		5.8		μС

<sup>1.</sup> Repetitive rating: pulse-width limited by maximum junction temperature.

<sup>2.</sup> L = 25 mH, I<sub>AS</sub> = 8 A, V<sub>DD</sub> = 50 V, R<sub>G</sub> = 25  $\Omega$ , starting T<sub>J</sub> = 25°C.

 $<sup>3.</sup>I_{SD} \leq 8 \text{ A, di/dt} \leq 200 \text{ A/}\mu\text{s, V}_{DD} \leq \text{BV}_{DSS}\text{, starting T}_{J} = 25^{\circ}\text{C}.$ 

<sup>4.</sup> Essentially independent of operating temperature typical characteristics.

## **Typical Performance Characteristics**

Figure 1. On-Region Characteristics





Figure 3. On-Resistance Variation vs.

Drain Current and Gate Voltage



**Figure 5. Capacitance Characteristics** 




Figure 2. Transfer Characteristics




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperatue





Figure 6. Gate Charge Characteristics



## Typical Performance Characteristics (Continued)

Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 9. Maximum Safe Operating Area

Figure 8. On-Resistance Variation vs. Temperature




Figure 10. Maximum Drain Current vs. Case Temperature






Figure 11. Transient Thermal Response Curve








Figure 12. Gate Charge Test Circuit & Waveform




Figure 13. Resistive Switching Test Circuit & Waveforms





Figure 14. Unclamped Inductive Switching Test Circuit & Waveforms






Figure 15. Peak Diode Recovery dv/dt Test Circuit & Waveforms

## **Mechanical Dimensions**




Figure 16. TO3PN, 3-Lead, Plastic, EIAJ SC-65

Package drawings are provided as a service to customers considering ON Semiconductor components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a ON Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of ON Semiconductor's worldwide terms and conditions, specifically the warranty therein, which covers ON Semiconductor products.

ON Semiconductor and III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## **PUBLICATION ORDERING INFORMATION**

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative