Switch-mode Dual Schottky Power Rectifier

Features and Benefits

- Highly Stable Oxide Passivated Junction
- Very Low Forward Voltage Drop (0.4 Max @ 10 A, T_C = 150°C)
- High Junction Temperature
- High dv/dt Capability
- Excellent Ability to Withstand Reverse Avalanche Energy Transients
- Low Power Loss/High Efficiency
- High Surge Capacity
- 175°C Operating Junction Temperature
- 20 A Total (10 A Per Diode Leg)
- This Device is Pb-Free and is RoHS Compliant*

Applications

- Power Supply Output Rectification
- Power Management ORING
- Instrumentation

Mechanical Characteristics


- Case: Epoxy, Molded
- Epoxy Meets UL 94 V-0 @ 0.125 in
- Weight: 1.9 Grams (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260°C Max. for 10 Sec
- ESD Rating: Human Body Model 3B Machine Model C



ON Semiconductor®

www.onsemi.com


SCHOTTKY BARRIER RECTIFIER 20 AMPERES, 30 VOLTS



MARKING DIAGRAM



TO-220 CASE 221A STYLE 6



A = Assembly Location

Y = Year

WW = Work Week

B2030L = Device Code

G = Pb-Free Package

AKA = Diode Polarity

ORDERING INFORMATION

Device	Package	Shipping
MBR2030CTLG	TO-220 (Pb-Free)	50 Units/Rail

^{*}For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

MAXIMUM RATINGS (Per Leg)

Rating	Symbol	Value	Unit V	
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _R	30		
Average Rectified Forward Current (T _C = 167°C) Per Diode Per Device	I _{F(AV)}	10 20	A	
Non-repetitive Peak Surge Current (Surge applied at rated load conditions halfwave, single phase, 60 Hz)	I _{FSM}	150	А	
Peak Repetitive Forward Current (Square Wave, 20 kHz, T _C = 166°C)	I _{FRM}	10	А	
Peak Repetitive Reverse Surge Current (2.0 μs, 1.0 kHz)	I _{RRM}	1.0	А	
Operating Junction Temperature (Note 1)	TJ	-65 to +175	°C	
Storage Temperature	T _{stg}	-65 to +175	°C	
Voltage Rate of Change (Rated V _R)	dv/dt	1000	V/μs	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. The heat generated must be less than the thermal conductivity from Junction–to–Ambient: $dP_D/dT_J < 1/R_{\theta JA}$.

THERMAL CHARACTERISTICS (Per Leg)


Characteristic	Symbol	Value	Unit
Maximum Thermal Resistance, Junction-to-Case (Min. Pad)	$R_{ heta JC}$	2.0	°C/W
Maximum Thermal Resistance, Junction-to-Ambient (Min. Pad)	$R_{ heta JA}$	60	°C/W

ELECTRICAL CHARACTERISTICS (Per Leg)

Characteristic	Symbol	Min	Тур	Max	Unit
Maximum Instantaneous Forward Voltage (Note 2) ($i_F = 10 \text{ Amps}, T_J = 25^{\circ}\text{C}$) ($i_F = 10 \text{ Amps}, T_J = 150^{\circ}\text{C}$) ($i_F = 20 \text{ Amps}, T_J = 25^{\circ}\text{C}$) ($i_F = 20 \text{ Amps}, T_J = 150^{\circ}\text{C}$)	VF	- - -	0.45 0.32 0.51 0.41	0.52 0.40 0.58 0.48	V
Maximum Instantaneous Reverse Current (Note 2) (Rated dc Voltage, T _J = 25°C) (Rated dc Voltage, T _J = 100°C) (Rated dc Voltage, T _J = 125°C)	i _R	- - -	0.11 10 –	5.0 40 75	mA

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.


2. Pulse Test: Pulse Width = 5.0 ms, Duty Cycle ≤ 10%.



i F, INSTANTANEOUS FORWARD CURRENT (AMPS) 100 $T_J = 175^{\circ}C$ 10 100°C 150°C 25°C 1.0 0.3 0.4 0.5 0.6 0.7 0.8 0.0 v_{E.} INSTANTANEOUS FORWARD VOLTAGE (VOLTS)

Figure 1. Typical Forward Voltage

Figure 2. Maximum Forward Voltage







Figure 3. Typical Reverse Current

Figure 4. Current Derating, Case Per Leg






Figure 5. Current Derating, Ambient Per Leg

Figure 6. Forward Power Dissipation




Figure 7. Typical Capacitance

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales