MCH6320

Power MOSFET –12V, 70mΩ, –3.5A, Single P-Channel

ON Semiconductor® www.onsemi.com


Features

- 1.8V Drive
- High Speed Switching
- Pb-Free and RoHS Compliance

Specifications


Absolute Maximum Ratings at $Ta = 25^{\circ}C$

Parameter	Symbol	Value	Unit
Drain to Source Voltage	V _{DSS}	-12	V
Gate to Source Voltage	V _{GSS}	±10	V
Drain Current (DC)	ID	-3.5	А
Drain Current (Pulse) PW≤10μs, duty cycle≤1%	IDP	-14	А
Power Dissipation When mounted on ceramic substrate (1200mm ² \times 0.8mm)	PD	1.5	W
Junction Temperature	Tj	150	°C
Storage Temperature	Tstg	-55 to +150	°C



Packing Type : TL

Marking





This product is designed to "ESD immunity < 200V*", so please take care when handling. * Machine Model

Thermal Resistance Ratings

Parameter	Symbol	Value	Unit
Junction to Ambient When mounted on ceramic substrate (1200mm ² \times 0.8mm)	R _{θJA}	83.3	°C/W

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

ORDERING INFORMATION


See detailed ordering and shipping information on page 5 of this data sheet.


Electrical Characteristics at $Ta = 25^{\circ}C$

Parameter	Gumbal	Conditions		Value		
Parameter	Symbol		min	typ	max	Unit
Drain to Source Breakdown Voltage	V(BR)DSS	I _D =-1mA, V _{GS} =0V	-12			V
Zero-Gate Voltage Drain Current	IDSS	V _{DS} =-12V, V _{GS} =0V			-10	μA
Gate to Source Leakage Current	IGSS	$V_{GS}=\pm 8V, V_{DS}=0V$			±10	μΑ
Gate Threshold Voltage	V _{GS} (th)	V _{DS} =-6V, I _D =-1mA	-0.4		-1.4	V
Forward Transconductance	9FS	V _{DS} =-6V, I _D =-1.5A	2.7	4.5		S
Static Drain to Source On-State Resistance	R _{DS} (on)1	I _D =-1.5A, V _{GS} =-4.5V		54	70	mΩ
	R _{DS} (on)2	I _D =-0.8A, V _{GS} =-2.5V		80	115	mΩ
	R _{DS} (on)3	I _D =-0.3A, V _{GS} =-1.8V		125	215	mΩ
Input Capacitance	Ciss	V _{DS} =-6V, f=1MHz		405		pF
Output Capacitance	Coss			145		pF
Reverse Transfer Capacitance	Crss			100		pF
Turn-ON Delay Time	t _d (on)	See specified Test Circuit		8.8		ns
Rise Time	tr			80		ns
Turn-OFF Delay Time	t _d (off)			41		ns
Fall Time	tf	-		50		ns
Total Gate Charge	Qg	V _{DS} =-6V, V _{GS} =-4.5V, I _D =-3.5A		5.6		nC
Gate to Source Charge	Qgs			0.7		nC
Gate to Drain "Miller" Charge	Qgd	1		1.6		nC
Forward Diode Voltage	V _{SD}	I _S =-3.5A, V _{GS} =0V		-0.86	-1.2	V


Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Switching Time Test Circuit





www.onsemi.com 3



Package Dimensions


MCH6320-TL-E / MCH6320-TL-W

MCPH6

CASE 419AS ISSUE O

unit : mm

- 1 : Drain
- 2 : Drain
- 3 : Gate
- 4 : Source
- 5 : Drain
- 6 : Drain



ORDERING INFORMATION

Device	Package	Shipping	Note
MCH6320-TL-E	MCPH6	3,000 pcs. / Tape & Reel	Pb-Free
MCH6320-TL-W	SC-88FL,SC-70-6,SOT-363		Pb-Free and Halogen Free

† For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D. http://www.onsemi.com/pub_link/Collateral/BRD8011-D.PDF

Note on usage : Since the MCH6320 is a MOSFET product, please avoid using this device in the vicinity of highly charged objects.

ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries. SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typical" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications in which the failure of the SCILLC product create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly, or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILC we are negligient regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.