# **ON Semiconductor**

## Is Now



To learn more about onsemi<sup>™</sup>, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

# MMBV3700LT1G

# **High Voltage Silicon Pin Diodes**

These devices are designed primarily for VHF band switching applications but are also suitable for use in general-purpose switching circuits. They are supplied in a cost-effective plastic package for economical, high-volume consumer and industrial requirements. They are also available in surface mount.

#### **Features**

- Long Reverse Recovery Time t<sub>rr</sub> = 300 ns (Typ)
- Rugged PIN Structure Coupled with Wirebond Construction for Optimum Reliability
- Low Series Resistance @ 100 MHz  $R_S = 0.7 \ \Omega \ (Typ) \ @ I_F = 10 \ mA$
- Reverse Breakdown Voltage = 200 V (Min)
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

#### **MAXIMUM RATINGS**


Rating	Symbol	Value	Unit
Reverse Voltage	V <sub>R</sub>	200	V
Forward Power Dissipation @ T <sub>A</sub> = 25°C Derate above 25°C	P <sub>D</sub>	200 2.8	mW mW/°C
Junction Temperature	TJ	+125	°C
Storage Temperature Range	T <sub>stg</sub>	-55 to +150	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.



## ON Semiconductor®

http://onsemi.com



## MARKING DIAGRAM





SOT-23 (TO-236AB) CASE 318-08 STYLE 8

4R = Specific Device Code

M = Date Code\*

= Pb-Free Package

(Note: Microdot may be in either location)

\*Date Code orientation and/or overbar may vary depending upon manufacturing location.

## **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
MMBV3700LT1G	SOT-23 (Pb-Free)	3000/Tape & Reel

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

## MMBV3700LT1G

## **ELECTRICAL CHARACTERISTICS** (T<sub>A</sub> = 25°C unless otherwise noted)

Figure 3. Diode Capacitance

Characteristic	Symbol	Min	Тур	Max	Unit
Reverse Breakdown Voltage (I <sub>R</sub> = 10 μA)	V <sub>(BR)R</sub>	200	-	-	V
Diode Capacitance (V <sub>R</sub> = 20 V, f = 1.0 MHz)	C <sub>T</sub>	-	-	1.0	pF
Series Resistance (Figure 5) (I <sub>F</sub> = 10 mA)	R <sub>S</sub>	_	0.7	1.0	Ω
Reverse Leakage Current (V <sub>R</sub> = 150 V)	I <sub>R</sub>	_	_	0.1	μΑ
Reverse Recovery Time (I <sub>F</sub> = I <sub>R</sub> = 10 mA)	t <sub>rr</sub>	-	300	-	ns

## **TYPICAL CHARACTERISTICS**





Figure 4. Leakage Current

## MMBV3700LT1G

## PACKAGE DIMENSIONS

## SOT-23 (TO-236) CASE 318-08 **ISSUE AN**



#### NOTES:


- 1. DIMENSIONING AND TOLERANCING PER ANSI Y14 5M 1982
- CONTROLLING DIMENSION: INCH.
- MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
- 318-01 THRU -07 AND -09 OBSOLETE, NEW STANDARD 318-08.

ſ		MILLIMETERS					
L	DIM	MIN	NOM	MAX	MIN	NOM	MAX
	Α	0.89	1.00	1.11	0.035	0.040	0.044
Г	A1	0.01	0.06	0.10	0.001	0.002	0.004
	b	0.37	0.44	0.50	0.015	0.018	0.020
Γ	С	0.09	0.13	0.18	0.003	0.005	0.007
	D	2.80	2.90	3.04	0.110	0.114	0.120
Γ	Е	1.20	1.30	1.40	0.047	0.051	0.055
	е	1.78	1.90	2.04	0.070	0.075	0.081
	Ĺ	0.10	0.20	0.30	0.004	0.008	0.012
	L1	0.35	0.54	0.69	0.014	0.021	0.029
Γ	HE	2.10	2.40	2.64	0.083	0.094	0.104

#### STYLE 8:

- PIN 1. ANODE 2. NO CONNECTION
  - CATHODE

#### **SOLDERING FOOTPRINT\***



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and un are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## **PUBLICATION ORDERING INFORMATION**

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA

Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative