

MUR3020PTG, SUR83020PTG, MUR3040PTG, MUR3060PTG, SUR83060PTG



ON Semiconductor®

<http://onsemi.com>

Switch-mode Power Rectifiers

These state-of-the-art devices are designed for use in switching power supplies, inverters and as free wheeling diodes.


Features

- Ultrafast 35 and 60 Nanosecond Recovery Time
- 175°C Operating Junction Temperature
- High Voltage Capability to 600 V
- Low Forward Drop
- Low Leakage Specified @ 150°C Case Temperature
- Current Derating Specified @ Both Case and Ambient Temperatures
- Epoxy Meets UL 94 V-0 @ 0.125 in
- High Temperature Glass Passivated Junction
- ESD Ratings:
 - ◆ Machine Model = C (> 400 V)
 - ◆ Human Body Model = 3B (> 16,000 V)
- AEC-Q101 Qualified and PPAP Capable
- SUR8 Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements
- All Packages are Pb-Free*


Mechanical Characteristics:

- Case: Epoxy, Molded
- Weight: 4.3 Grams (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260°C Max for 10 Seconds
- Shipped 30 Units Per Plastic Tube

ULTRAFAST RECTIFIERS 30 AMPERES, 200-600 VOLTS



SOT-93
(TO-218)
CASE 340D
STYLE 2



MARKING DIAGRAM



A = Assembly Location
Y = Year
WW = Work Week
G = Pb-Free Package
MUR30x0PT = Device Code
x = 2, 4, or 6

ORDERING INFORMATION

| Device | Package | Shipping |
|-------------|---------------------|---------------|
| MUR3020PTG | SOT-93 (Pb-Free) | 30 Units/Rail |
| SUR83020PTG | SOT-93 (Pb-Free) | 30 Units/Rail |
| MUR3040PTG | SOT-93 (Pb-Free) | 30 Units/Rail |
| MUR3060PTG | SOT-93 (Pb-Free) | 30 Units/Rail |
| SUR83060PTG | SOT-93 (Pb-Free) | 30 Units/Rail |

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

MUR3020PTG, SUR83020PTG, MUR3040PTG, MUR3060PTG, SUR83060PTG

MAXIMUM RATINGS (Per Leg)

| Rating | Symbol | MUR3020PTG/ SUR83020PTG | MUR3040PTG | MUR3060PTG/ SUR83060PTG | Unit |
|--|---------------------------------|--|------------|--|------------------|
| Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage | V_{RRM} V_{RWM} V_R | 200 | 400 | 600 | V |
| Average Rectified Forward Current (Rated V_R) Per Leg Per Device | $I_{F(AV)}$ | 15 @ $T_C = 150^\circ\text{C}$ 30 @ $T_C = 150^\circ\text{C}$ | | 15 @ $T_C = 145^\circ\text{C}$ 30 @ $T_C = 145^\circ\text{C}$ | A |
| Peak Rectified Forward Current, Per Leg (Rated V_R , Square Wave, 20 kHz) | I_{FRM} | 30 @ $T_C = 150^\circ\text{C}$ | | 30 @ $T_C = 145^\circ\text{C}$ | A |
| Nonrepetitive Peak Surge Current (Surge applied at rated load conditions, halfwave, single phase, 60 Hz) Per Leg | I_{FSM} | 200 | | | A |
| Operating Junction and Storage Temperature | T_J, T_{stg} | - 65 to +175 | | | $^\circ\text{C}$ |

THERMAL CHARACTERISTICS (Per Diode Leg)

| | | | | |
|--|------------------------------------|-----------|--|--------------------|
| Maximum Thermal Resistance, Junction-to-Case Junction-to-Ambient | $R_{\theta JC}$ $R_{\theta JA}$ | 1.5 40 | | $^\circ\text{C/W}$ |
|--|------------------------------------|-----------|--|--------------------|

ELECTRICAL CHARACTERISTICS (Per Diode Leg)

| | | | | | |
|---|----------|--------------|--------------|------------|---------------|
| Maximum Instantaneous Forward Voltage (Note 1) ($I_F = 15$ Amp, $T_C = 150^\circ\text{C}$) ($I_F = 15$ Amp, $T_C = 25^\circ\text{C}$) | V_F | 0.85 1.05 | 1.12 1.25 | 1.2 1.5 | V |
| Maximum Instantaneous Reverse Current (Note 1) (Rated DC Voltage, $T_J = 150^\circ\text{C}$) (Rated DC Voltage, $T_J = 25^\circ\text{C}$) | i_R | 500 10 | | 1000 10 | μA |
| Maximum Reverse Recovery Time ($I_F = 1.0$ A, $di/dt = 50$ A/ μs) | t_{rr} | 35 | 60 | | ns |

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

1. Pulse Test: Pulse Width = 300 μs , Duty Cycle $\leq 2.0\%$.

MUR3020PTG, SUR83020PTG




Figure 1. Typical Forward Voltage (Per Leg)




Figure 2. Typical Reverse Current (Per Leg)




Figure 3. Current Derating, Case (Per Leg)




Figure 4. Current Derating, Ambient (Per Leg)




Figure 5. Power Dissipation (Per Leg)

MUR3040PTG




Figure 6. Typical Forward Voltage (Per Leg)




Figure 7. Typical Reverse Current (Per Leg)




Figure 8. Current Derating, Case (Per Leg)




Figure 9. Current Derating, Ambient (Per Leg)




Figure 10. Power Dissipation (Per Leg)




Figure 11. Typical Forward Voltage (Per Leg)




Figure 12. Typical Reverse Current (Per Leg)




Figure 13. Current Derating, Case (Per Leg)




Figure 14. Current Derating, Ambient (Per Leg)




Figure 15. Power Dissipation (Per Leg)

MUR3020PTG, SUR83020PTG, MUR3040PTG, MUR3060PTG, SUR83060PTG




Figure 16. Thermal Response




Figure 17. Typical Capacitance (Per Leg)

MECHANICAL CASE OUTLINE

PACKAGE DIMENSIONS

ON Semiconductor®



SOT-93 (TO-218) CASE 340D-02 ISSUE E

DATE 01/03/2002



SCALE 1:1



STYLE 1:
PIN 1. BASE
2. COLLECTOR
3. EMITTER
4. COLLECTOR

STYLE 2:
PIN 1. ANODE
2. CATHODE
3. ANODE
4. CATHODE

- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.

| DIM | MILLIMETERS | | INCHES | |
|-----|-------------|-------|-----------|-------|
| | MIN | MAX | MIN | MAX |
| A | --- | 20.35 | --- | 0.801 |
| B | 14.70 | 15.20 | 0.579 | 0.598 |
| C | 4.70 | 4.90 | 0.185 | 0.193 |
| D | 1.10 | 1.30 | 0.043 | 0.051 |
| E | 1.17 | 1.37 | 0.046 | 0.054 |
| G | 5.40 | 5.55 | 0.213 | 0.219 |
| H | 2.00 | 3.00 | 0.079 | 0.118 |
| J | 0.50 | 0.78 | 0.020 | 0.031 |
| K | 31.00 REF | | 1.220 REF | |
| L | --- | 16.20 | --- | 0.638 |
| Q | 4.00 | 4.10 | 0.158 | 0.161 |
| S | 17.80 | 18.20 | 0.701 | 0.717 |
| U | 4.00 REF | | 0.157 REF | |
| V | 1.75 REF | | 0.069 | |

MARKING DIAGRAM



A = Assembly Location
Y = Year
WW = Work Week
xxxxx = Device Code

| | | |
|-------------------------|--------------------|--|
| DOCUMENT NUMBER: | 98ASB42643B | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION: | SOT-93 | PAGE 1 OF 1 |

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT

North American Technical Support:
Voice Mail: 1 800-282-9855 Toll Free USA/Canada
Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative