**ON Semiconductor** 

Is Now

# Onsemi

To learn more about onsemi<sup>™</sup>, please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

# MPS6724, MPS6725

## One Watt Darlington Transistors

## **NPN Silicon**

### Features

• Pb–Free Packages are Available\*

#### MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector – Emitter Voltage MPS6724 MPS6725	V <sub>CEO</sub>	40 50	Vdc
Collector – Base Voltage MPS6724 MPS6725	V <sub>CBO</sub>	50 60	Vdc
Emitter-Base Voltage	$V_{EBO}$	12	Vdc
Collector Current – Continuous	Ι <sub>C</sub>	1000	mAdc
Total Device Dissipation @ T <sub>A</sub> = 25°C Derate above 25°C	PD	1.0 8.0	W m₩/°C
Total Device Dissipation @ T <sub>C</sub> = 25°C Derate above 25°C	PD	2.5 20	W mW/°C
Operating and Storage Junction Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	-55 to +150	°C

### THERMAL CHARACTERISTICS


Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	125	°C/W
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	50	°C/W


Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.



## **ON Semiconductor®**

http://onsemi.com





MPS672x = Device Code x = 4 or 5 A = Assembly Location Y = Year WW = Work Week = Pb-Free Package

(Note: Microdot may be in either location)

## **ORDERING INFORMATION**

See detailed ordering and shipping information in the package dimensions section on page 4 of this data sheet.


\*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

## MPS6724, MPS6725

## **ELECTRICAL CHARACTERISTICS** (T<sub>A</sub> = 25°C unless otherwise noted)

MPS6724 MPS6725	V <sub>(BR)CES</sub>		· · · ·	
	V <sub>(BR)CES</sub>		-	
		40 50	- -	Vdc
MPS6724 MPS6725	V <sub>(BR)CBO</sub>	50 60		Vdc
	V <sub>(BR)EBO</sub>	12	-	Vdc
MPS6724 MPS6725	I <sub>CBO</sub>		100 100	nAdc
	I <sub>EBO</sub>	-	100	nAdc
	h <sub>FE</sub>	25,000 4,000	40,000	-
	V <sub>CE(sat)</sub>	_	1.5	Vdc
	V <sub>BE(on)</sub>	-	2.0	Vdc
	f <sub>T</sub>	100	1000	MHz
	C <sub>cb</sub>	-	10	pF
	MPS6724 MPS6725 MPS6724	MPS6724 MPS6725 V(BR)CBO   MPS6725 V(BR)EBO   MPS6725 ICBO   MPS6725 IEBO   VCE(sat) VBE(on)   fT Ifter the set of the set	MPS6724 MPS6725 V(BR)CBO 50 60   MPS6725 V(BR)EBO 12   MPS6724 MPS6725 ICBO -   IEBO - -   VCE(sat) - -   VBE(on) - -   ICBO - -	$\begin{tabular}{ c c c c c c c } \hline & V_{(BR)CBO} & & & & & & & & & & & & & & & & & & &$

1. Pulse Test: Pulse Width  $\leq$  300 µs; Duty Cycle  $\leq$  2.0%.



## TYPICAL CHARACTERISTICS

Figure 1. Active Region — Safe Operating Area

## MPS6724, MPS6725






Figure 3. Collector Saturation Region





Figure 4. "ON" Voltages

Figure 5. Temperature Coefficients




## **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
MPS6724	TO-92	
MPS6724G	TO-92 (Pb-Free)	5000 Units / Bulk
MPS6725	TO-92	
MPS6725G	TO-92 (Pb-Free)	5000 Units / Bulk
MPS6724RLRA	TO-92	
MPS6724RLRAG	TO-92 (Pb-Free)	2000 Units / Tape & Reel
MPS6725RLRP	TO-92	
MPS6725RLRPG	TO-92 (Pb-Free)	2000 Units / Tape & Ammo Box

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### PACKAGE DIMENSIONS

TO-92 (TO-226) CASE 29-10 ISSUE AL



NOTES: 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.

- 2. CONTROLLING DIMENSION: INCH.
- CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED.
- L. DIMENSION F APPLIES BETWEEN P AND L DIMENSIONS D AND J APPLY BETWEEN LAND K MIMIMUM. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

	INCHES MILLIMETE		ETERS	
DIM	MIN	MAX	MIN	MAX
Α	0.175	0.205	4.44	5.21
В	0.290	0.310	7.37	7.87
С	0.125	0.165	3.18	4.19
D	0.018	0.021	0.457	0.533
F	0.016	0.019	0.407	0.482
G	0.045	0.055	1.15	1.39
Н	0.095	0.105	2.42	2.66
L	0.018	0.024	0.46	0.61
Κ	0.500		12.70	
Г	0.250		6.35	
Ν	0.080	0.105	2.04	2.66
Ρ		0.100		2.54
R	0.135		3.43	

STYLE 1: PIN 1. EMITTER

2. BASE

3. COLLECTOR

ON Semiconductor and IIII are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other application in which the failure of the SCILLC product create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use persons, and reasonable attorney fees andising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use persons and sensing out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized to applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 61312, Phoenix, Arizona 85082–1312 USA Phone: 480–829–7710 or 800–344–3860 Toll Free USA/Canada Fax: 480–829–7709 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800–282–9855 Toll Free USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center 2–9–1 Kamimeguro, Meguro–ku, Tokyo, Japan 153–0051 Phone: 81–3–5773–3850 ON Semiconductor Website: http://onsemi.com

Order Literature: http://www.onsemi.com/litorder

For additional information, please contact your local Sales Representative.