IGBT - Induction Cooking

This Insulated Gate Bipolar Transistor (IGBT) features a robust and cost effective Field Stop (FS) Trench construction, provides and superior performance in demanding switching applications, and offers low on-state voltage with minimal switching loss. The IGBT is well suited for resonant or soft switching applications.

Features

- Extremely Efficient Trench with Fieldstop Technology
- Low Switching Loss Reduces System Power Dissipation
- Optimized for Low Losses in IH Cooker Application
- This is a Pb-Free Device

Typical Applications

- Inductive Heating
- Consumer Appliances
- Soft Switching

ABSOLUTE MAXIMUM RATINGS

| Rating | Symbol | Value | Unit |
|---|------------------|-------------|------|
| Collector-emitter voltage @ T _J = 25°C | V _{CES} | 1200 | V |
| Collector current @ Tc = 25°C @ Tc = 100°C | lc | 40 20 | А |
| Pulsed collector current, T_{pulse} limited by T_{Jmax} , 10 μs Pulse, V_{GE} = 15 V | I _{CM} | 80 | Α |
| Diode forward current @ Tc = 25°C @ Tc = 100°C | l _F | 40 20 | А |
| Diode pulsed current, T_{pulse} limited by T_{Jmax} , 10 μs Pulse, $V_{GE} = 0$ V | I _{FM} | 80 | А |
| Gate-emitter voltage Transient Gate-emitter voltage $(T_{pulse} = 5 \mu s, D < 0.10)$ | V_{GE} | ±20 ±25 | V |
| Power Dissipation @ Tc = 25°C @ Tc = 100°C | P _D | 341 170 | W |
| Operating junction temperature range | T_J | -40 to +175 | °C |
| Storage temperature range | T _{stg} | -55 to +175 | °C |
| Lead temperature for soldering, 1/8" from case for 5 seconds | T _{SLD} | 260 | °C |


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.




ON Semiconductor®


www.onsemi.com

20 A, 1200 V **V_{CEsat} = 2.20 V** $E_{off} = 0.48 \text{ mJ}$





MARKING DIAGRAM



= Assembly Location Α

= Year WW = Work Week = Pb-Free Package

ORDERING INFORMATION

| Device | Package | Shipping |
|----------------|---------------------|-----------------|
| NGTB20N120IHWG | TO-247 (Pb-Free) | 30 Units / Rail |

THERMAL CHARACTERISTICS

| Rating | Symbol | Value | Unit |
|--|----------------|-------|------|
| Thermal resistance junction-to-case | $R_{	heta JC}$ | 0.44 | °C/W |
| Thermal resistance junction-to-ambient | $R_{	heta JA}$ | 40 | °C/W |

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

| Parameter | Test Conditions | Symbol | Min | Тур | Max | Unit |
|---|--|----------------------|--------|--------------|------------|------|
| STATIC CHARACTERISTIC | | | | | | |
| Collector–emitter breakdown voltage, gate–emitter short–circuited | $V_{GE} = 0 \text{ V}, I_{C} = 500 \mu\text{A}$ | V _{(BR)CES} | 1200 | _ | _ | V |
| Collector-emitter saturation voltage | V _{GE} = 15 V, I _C = 20 A V _{GE} = 15 V, I _C = 20 A, T _J = 175°C | V_{CEsat} | - - | 2.20 2.30 | 2.65 | V |
| Gate-emitter threshold voltage | $V_{GE} = V_{CE}, I_{C} = 250 \mu A$ | V _{GE(th)} | 4.5 | 5.5 | 6.5 | V |
| Collector–emitter cut–off current, gate– emitter short–circuited | $V_{GE} = 0 \text{ V}, V_{CE} = 1200 \text{ V}$ $V_{GE} = 0 \text{ V}, V_{CE} = 1200 \text{ V}, T_{J=} 150^{\circ}\text{C}$ | I _{CES} | - | _ _ | 0.1 2.8 | mA |
| Gate leakage current, collector–emitter short–circuited | V _{GE} = 20 V, V _{CE} = 0 V | I _{GES} | _ | _ | 100 | nA |
| DYNAMIC CHARACTERISTIC | | • | | | | • |
| Input capacitance | V _{CE} = 20 V, V _{GE} = 0 V, f = 1 MHz | C _{ies} | - | 3590 | - | pF |
| Output capacitance | | C _{oes} | - | 90 | - | |
| Reverse transfer capacitance | | C _{res} | - | 70 | - | |
| Gate charge total | | Q_g | - | 150 | - | nC |
| Gate to emitter charge | $V_{CE} = 600 \text{ V}, I_{C} = 20 \text{ A}, V_{GE} = 15 \text{ V}$ | Q _{ge} | - | 31 | - | |
| Gate to collector charge | | Q _{gc} | - | 67 | - | |
| SWITCHING CHARACTERISTIC, INDUCT | TIVE LOAD | | | | | |
| Turn-off delay time | $T_J = 25^{\circ}\text{C}$ $V_{CC} = 600 \text{ V, } I_C = 20 \text{ A}$ $R_q = 10 \Omega$ | t _{d(off)} | - | 170 | - | ns |
| Fall time | | t _f | - | 155 | - | |
| Turn-off switching loss | V _{GE} = 0 V/ 15V | E _{off} | - | 0.48 | - | mJ |
| Turn-off delay time | T _J = 150°C | t _{d(off)} | _ | 185 | _ | ns |
| Fall time | $V_{CC} = 600 \text{ V}, I_{C} = 20 \text{ A}$ $R_{\alpha} = 10 \Omega$ | t _f | - | 210 | - | |
| Turn-off switching loss | $V_{GE} = 0 \text{ V} / 15 \text{V}$ | E _{off} | 1 | 0.92 | 1 | mJ |
| DIODE CHARACTERISTIC | | | _ | | | |
| Forward voltage | V _{GE} = 0 V, I _F = 20 A V _{GE} = 0 V, I _F = 20 A, T _J = 175°C | V _F | _ _ | 2.2 3.8 | 2.75 | V |
| | | L. | | | | |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS




Figure 5. Diode Forward Characteristics

Figure 6. Typical Gate Charge

TYPICAL CHARACTERISTICS




Figure 7. Switching Loss vs. Temperature

Figure 8. Switching Time vs. Temperature

160




Figure 9. Safe Operating Area

Figure 10. Reverse Bias Safe Operating Area




Figure 11. IGBT Transient Thermal Impedance




Figure 12. Test Circuit for Switching Characteristics





Figure 13. Definition of Turn Off Waveform

e -



DATE 17 MAR 2017

- NOTES:


 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
 2. CONTROLLING DIMENSION: MILLIMETERS.
 3. SLOT REQUIRED, NOTCH MAY BE ROUNDED.

 - DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH.
 MOLD FLASH SHALL NOT EXCEED 0.13 PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTERMOST EXTREME OF THE PLASTIC BODY
- LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY
- ©P SHALL HAVE A MAXIMUM DRAFT ANGLE OF 1.5° TO THE TOP OF THE PART WITH A MAXIMUM DIAMETER OF 3.91.

 DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED

| | MILLIMETERS | | |
|-----|-------------|-------|--|
| DIM | MIN | MAX | |
| Α | 4.70 | 5.30 | |
| A1 | 2.20 | 2.60 | |
| b | 1.07 | 1.33 | |
| b2 | 1.65 | 2.35 | |
| b4 | 2.60 | 3.40 | |
| С | 0.45 | 0.68 | |
| D | 20.80 | 21.34 | |
| Е | 15.50 | 16.25 | |
| E2 | 4.32 | 5.49 | |
| е | 5.45 BSC | | |
| F | 2.655 | | |
| L | 19.80 | 20.80 | |
| L1 | 3.81 | 4.32 | |
| P | 3.55 | 3.65 | |
| Q | 5.40 | 6.20 | |
| S | 6.15 BSC | | |

GENERIC MARKING DIAGRAM*



XXXXX = Specific Device Code Α = Assembly Location

Υ = Year WW = Work Week = Pb-Free Package

*This information is generic. Please refer to device data sheet for actual part marking.

Pb-Free indicator, "G" or microdot " ■", may or may not be present.

| | DESCRIPTION: | | Printed Versions are uncontrolled except when stamped CONTROLLED | PAGE 1 OF 1 | |
|------------------------------|--------------|-------------|--|-------------|--|
| | | | Printed versions are uncontrolled except when stamped "CONTROLLED or stamped" | | |
| DOCUMENT NUMBER: 98AON16119F | | 0040N46440E | Electronic versions are uncontrolled except when accessed directly from the Document Repository. | | |

ON Semiconductor and unare trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales