

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild <a href="general-regarding-numbers-n

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



May 2000 Revised December 2005

NC7WB3125 2-Bit Low Power Bus Switch

General Description

The NC7WB3125 is a 2-bit ultra high-speed CMOS FET bus switch with TTL-compatible active LOW control inputs. The low On Resistance of the switch allows inputs to be connected to outputs with minimal propagation delay and without generating additional ground bounce noise. The device is organized as a 2-bit switch with independent bus enable ($\overline{\text{OE}}$) controls. When $\overline{\text{OE}}$ is LOW, the switch is ON and Port A is connected to Port B. When $\overline{\text{OE}}$ is HIGH, the switch is OPEN and a high-impedance state exists between the two ports. Control inputs tolerate voltages up to 5.5V independent of VCC.

Features

- Space saving US8 surface mount package
- MicroPak™ Pb-Free leadless package
- Typical 3Ω switch resistance at 5.0V V_{CC}
- Minimal propagation delay through the switch
- Power down high impedance input/output
- Zero bounce in flow through mode
- TTL compatible active LOW control inputs
- Control inputs are overvoltage tolerant
- Bus switch replacement for Logic x125 part


Ordering Code:

		Product		
Order	Package	Code	Package Description	Supplied As
Number	Number	Top Mark		
NC7WB3125K8X	MAB08A	WB25	8-Lead US8, JEDEC MO-187, Variation CA 3.1mm Wide	3k Units on Tape and Reel
NC7WB3125L8X (Preliminary)	MAC08A	T4	Pb-Free 8-Lead MicroPak, 1.6 mm Wide	5k Units on Tape and Reel

Pb-Free package per JEDEC J-STD-020B.

MircoPak™ is a trademark of Fairchild Semiconductor Corporation.

Logic Diagram




Pin Descriptions

Pin Name	Description
Α	Bus A
В	Bus B
OE	Bus Enable Input


Function Table

Bus Enable Input OE	Function
L	B Connected to A
Н	Disconnected

Connection Diagrams




Pin One Orientation Diagram



AAA represents Product Code Top Mark - see ordering code

Note: Orientation of Top Mark determines Pin One location. Read the top product code mark left to right, Pin One is the lower left pin (see diagram).

Pad Assignments for MicroPak



(Top Through View)

4.0V to 5.5V

250°C/W

Absolute Maximum Ratings(Note 1)

Supply Voltage (V_{CC}) -0.5V to +7.0VDC Switch Voltage (V_S) -0.5V to +7.0VDC Output Voltage (V_{IN}) (Note 2) -0.5V to +7.0V

DC Input Diode Current

 $(I_{IK}) V_{IN} < 0V$ -50 mA DC Output (I_{OUT}) Current 128 mA

 ${\rm DC} \ {\rm V}_{\rm CC} \ {\rm or} \ {\rm Ground} \ {\rm Current}$

±100 mA (I_{CC}/I_{GND}) -65°C to +150°C Storage Temperature Range (T_{STG}) Junction Temperature under Bias (T_.) +150°C

Junction Lead Temperature (T_I)

(Soldering, 10 Seconds) +260°C Power Dissipation (PD) @ +85°C 250 mW

Recommended Operating Conditions (Note 3)

Thermal Resistance (θ_{JA})

Supply Operating (V_{CC}) Control Input Voltage (V_{IN}) 0V to 5.5V Switch Input Voltage (V_{IN}) 0V to 5.5V Output Voltage (V_{OUT}) 0V to 5.5V Operating Temperature (T_A) $-40^{\circ}C$ to $+85^{\circ}C$ Input Rise and Fall Time (t_r, t_f) Switch Control Input 0 ns/V to 5 ns 0 ns/V to DC Switch I/O

Note 1: The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the Electrical Characteristics tables are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Note 2: The input and output negative voltage ratings may be exceeded if the input and output diode current ratings are observed.

Note 3: Unused logic inputs must be held HIGH or LOW. They may not float.

DC Electrical Characteristics

Symbol	Parameter	V _{cc}	Т	_A = -40°C to +85°	C	Units	Conditions
Cymbol	i arameter	(V)	Min	Тур	Max	Oille	Conditions
V _{IK}	Clamp Diode Voltage	4.5			-1.2	V	I _{IN} = -18 mA
V_{IH}	HIGH Level Input Voltage	4.0 to 5.5	2.0			V	
V_{IL}	LOW Level Input Voltage	4.0 to 5.5			0.8	V	
V _{OH}	HIGH Level Output Voltage	4.0 to 5.5		See Figure 3		V	$V_{IN} = V_{CC}$
I _{IN}	Input Leakage Current	5.5			±1.0	μΑ	$0 \le V_{IN} \le 5.5V$
I _{OFF}	Switch OFF Leakage Current	5.5			±1.0	μΑ	0 ≤ A, B ≤ V _{CC}
R _{ON}	Switch On Resistance	4.5		3.0	7.0		V _{IN} = 0V, I _{IN} = 64 mA
	(Note 4)	4.5		3.0	7.0	Ω	V _{IN} = 0V, I _{IN} = 30 mA
		4.5		6.0	15.0	52	V _{IN} = 2.4V, I _{IN} = 15 mA
		4.0		10.0	20.0		V _{IN} = 2.4V, I _{IN} = 15 mA
I _{CC}	Quiescent Supply Current	5.5			3.0	μΑ	V _{IN} = V _{CC} or GND
							I _{OUT} = 0
Δ I _{CC}	Increase in I _{CC} per Input (Note 5)	5.5		1.0	2.5	mA	V _{IN} = 3.4V, One OE Input only,
							Other OE = V _{CC}

Note 4: Measured by the voltage drop between A and B pins at the indicated current through the switch. On Resistance is determined by the lower of the voltages on the two (A or B) pins.

Note 5: Per TTL driven input ($V_{IN} = 3.4V$, control input only). A and B pins do not contribute to I_{CC} .

AC Electrical Characteristics


Symbol	Parameter	v _{cc}	$T_A = -40^{\circ}\text{C to } +85^{\circ}\text{C},$ $C_L = 50 \text{ pF, RU} = \text{RD} = 500\Omega$			Units	Conditions	Figure
		(V)	Min	Тур	Max			Number
t _{PHL} ,	Propagation Delay Bus-to-Bus	4.0 to 5.5			0.25	ns	V _I = OPEN	Figures
t _{PLH}	(Note 6)							1, 2
t_{PZL} ,	Output Enable Time	4.5 to 5.5	0.8	2.5	4.2	ns	V _I = 7V for t _{PZL}	Figures
t_{PZH}		4.0	0.8	3.0	4.6	115	$V_I = 0V$ for t_{PZH}	1, 2
t_{PLZ} ,	Output Disable Time	4.5 to 5.5	0.8	3.1	4.8	ns	V _I = 7V for t _{PLZ}	Figures
t_{PHZ}		4.0	0.8	2.9	4.4	115	$V_I = 0V$ for t_{PHZ}	1Figure 2

Note 6: This parameter is guaranteed by design. The bus switch contributes no propagation delay other than the RC delay of the typical On Resistance of the switch and the 50 pF load capacitance, when driven by an ideal voltage source (zero output impedance). The specified limit is calculated on this basis.

Capacitance

Symbol	Parameter	Тур	Max	Units	Conditions
C _{IN}	Control Pin Input Capacitance	2.5		pF	V _{CC} = 0V
C _{I/O} (OFF)	Port Off Capacitance	6.0		pF	$V_{CC} = 5.0V = \overline{OE}$
C _{I/O} (ON)	Switch ON Capacitance	12.0		pF	$V_{CC} = 5.0V, \overline{OE} = 0V$

AC Loading and Waveforms




Input driven by 50Ω source terminated in 50Ω

 \mathbf{C}_{L} includes load and stray capacitance

Input PRR = 1.0 MHz; $t_W = 500 \text{ ns}$

FIGURE 1. AC Test Circuit








FIGURE 2. AC Waveforms

DC Characteristics









FIGURE 3. Typical High Level Output Voltage vs. Supply Voltage

Tape and Reel Specification

TAPE FORMAT for US8

Package Designator	Tape Section	Number Cavities	Cavity Status	Cover Tape Status
	Leader (Start End)	125 (typ)	Empty	Sealed
K8X	Carrier	250	Filled	Sealed
	Trailer (Hub End)	75 (typ)	Empty	Sealed


TAPE DIMENSIONS inches (millimeters)




TAPE FORMAT for MicroPak

Package	Tape	Number	Cavity	Cover Tape
Designator	Section	Cavities	Status	Status
	Leader (Start End)	125 (typ)	Empty	Sealed
L8X	Carrier	250	Filled	Sealed
	Trailer (Hub End)	75 (typ)	Empty	Sealed

TAPE DIMENSIONS inches (millimeters)





REEL DIMENSIONS inches (millimeters)




Tape Size	Α	В	С	D	N	W1	W2	W3
9 mm	7.0	0.059	0.512	0.795	2.165	0.331 + 0.059/-0.000	0.567	W1 + 0.078/-0.039
8 mm	(177.8)	(1.50)	(13.00)	(20.20)	(55.00)	(8.40 + 1.50/-0.00)	(14.40)	(W1 + 2.00/-1.00)


Physical Dimensions inches (millimeters) unless otherwise noted





LAND PATTERN RECOMMENDATION





GAGE PLANE 0.12 SEATING PLANE 0.20-0.35

NOTES:


- A. CONFORMS TO JEDEC REGISTRATION MO-187 B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
- D. DIMENSIONS AND TOLERANCES PER ANSI Y14.5M, 1982.

DETAIL A

MAB08AREVC

8-Lead US8, JEDEC MO-187, Variation CA 3.1mm Wide Package Number MAB08A

Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



Notes:

- 1. PACKAGE CONFORMS TO JEDEC MO-255 VARIATION UAAD
- 2. DIMENSIONS ARE IN MILLIMETERS
- 3. DRAWING CONFORMS TO ASME Y.14M-1994
- 4/PIN 1 FLAG, END OF PACKAGE OFFSET.

MAC08AREVC

Pb-Free 8-Lead MicroPak, 1.6 mm Wide Package Number MAC08A

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use

provided in the labeling, can be reasonably expected to result in significant injury to the user.

2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild Semiconductor. The datasheet is printed for reference information only.

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdt/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and exp

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative