Switch-mode Power Rectifiers

This LFPAK ultrafast rectifier provides fast switching performance with soft recovery in a compact thermally efficient package. The LFPAK package provides an excellent alternative to the DPAK, offering thermal performance nearly as good in a package occupying less than half the board space. Its low profile makes it a good option for flat panel display and other applications with limited vertical clearance. The device offers low leakage over temperature making it a good match for applications requiring low quiescent current.

Features

- New Package Provides Capability of Inspection and Probe After Board Mounting
- Low Forward Voltage Drop
- 175°C Operating Junction Temperature
- Excellent Ability to Absorb Stresses Associated with Power Temperature Cycling
- NRV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

Mechanical Characteristics:

- Case: Epoxy, Molded
- Epoxy Meets Flammability Rating UL 94-0 @ 0.125 in.
- Lead Finish: 100% Matte Sn (Tin)
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Max. for 10 Seconds
- Device Meets MSL 1 Requirements

Applications

- Excellent Alternative to DPAK in Space-Constrained Automotive Applications
- Very Low Leakage for Higher Temperature Operation
- Output Rectification in Compact Portable Consumer Applications
- Freewheeling Diode used with Inductive Loads



ON Semiconductor®


www.onsemi.com

ULTRAFAST RECTIFIERS 6 AMPERES 200 VOLTS





LFPAK4 CASE 760AB



HP620L = Specific Device Code A = Assembly Location

 LL
 = Wafer Lot

 Y
 = Year

 W
 = Work Week

ORDERING INFORMATION

| Device | Package | Shipping† |
|----------------|---------------------|-----------------------|
| NHP620LFST1G | LFPAK4 (Pb-Free) | 3000 / Tape & Reel |
| NRVHP620LFST1G | LFPAK4 (Pb-Free) | 3000 / Tape & Reel |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

MAXIMUM RATINGS

| Rating | Symbol | Value | Unit |
|---|--|-------------|------|
| Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage | V _{RRM} V _{RWM} V _R | 200 | V |
| Average Rectified Forward Current (Rated V _R , T _C = 169°C) | I _{F(AV)} | 6.0 | А |
| Peak Repetitive Forward Current, (Rated V_R , Square Wave, 20 kHz, T_C = 160°C) | I _{FRM} | 12 | А |
| Non-Repetitive Peak Surge Current (Surge Applied at Rated Load Conditions Halfwave, Single Phase, 60 Hz) | I _{FSM} | 150 | А |
| Storage Temperature Range | T _{stg} | -65 to +175 | °C |
| Operating Junction Temperature | TJ | -55 to +175 | °C |
| ESD Rating (Human Body Model) | | 3B | |
| ESD Rating (Machine Model) | | С | |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

| Characteristic | Symbol | Max | Unit |
|---|----------------|------|------|
| Thermal Resistance, Junction-to-Case, Steady State (Assumes 600 mm² 1 oz. copper bond pad, on a FR4 board) | $R_{	heta JC}$ | 1.31 | °C/W |
| Thermal Resistance, Junction-to-Ambient, Steady State (Assumes 600 mm² 1 oz. copper bond pad, on a FR4 board) | $R_{	hetaJA}$ | 44.4 | °C/W |

ELECTRICAL CHARACTERISTICS

| Characteristic | Symbol | Max | Unit |
|---|-----------------|------------------------------|------|
| Instantaneous Forward Voltage (Note 1) | VF | 0.80 0.95 0.73 0.87 | V |
| Instantaneous Reverse Current (Note 1) (Rated dc Voltage, T_J = 125°C) (Rated dc Voltage, T_J = 25°C) | i _R | 75 0.5 | μА |
| Maximum Reverse Recovery Time (I _F = 1.0 A, di/dt = 50 A/ μ s, V _R = 30 V) | T _{rr} | 50 | ns |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

^{1.} Pulse Test: Pulse Width = 300 μs, Duty Cycle ≤ 2.0%.

TYPICAL CHARACTERISTICS




Figure 1. Typical Instantaneous Forward Characteristics

Figure 2. Maximum Instantaneous Forward Characteristics




Figure 3. Typical Reverse Characteristics

Figure 4. Maximum Reverse Characteristics




Figure 5. Typical Junction Capacitance

TYPICAL CHARACTERISTICS




Figure 6. Current Derating per Device

Figure 7. Forward Power Dissipation





Figure 8. Typical Thermal Characteristics, Junction-to-Ambient



DATE 19 NOV 2019

NOTES:

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- 2. CONTROLLING DIMENSION: MILLIMETERS.
- 3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH PROTRUSIONS OR GATE BURRS SHALL NOT EXCEED 0.150mm PER SIDE.
- 4. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
- 5. DATUMS A AND B ARE DETERMINED AT DATUM PLANE H.

| UNIT IN MILLIMETER | | | | |
|--------------------|-----------|----------|------|--|
| DIM | MIN | NOM | MAX | |
| Α | 1.10 | 1.20 | 1.30 | |
| A1 | 0.00 | 0.08 | 0.15 | |
| A2 | 1.10 | 1.15 | 1.20 | |
| A3 | (| 0.25 REF | | |
| A4 | 0.45 | 0.50 | 0.55 | |
| b | 0.40 | 0.45 | 0.50 | |
| b2 | 3.80 | 4.10 | 4.40 | |
| b3 | 2.00 | 2.10 | 2.20 | |
| b4 | 0.70 | 0.80 | 0.90 | |
| b5 | 0.55 | 0.65 | 0.75 | |
| b6 | 0.31 REF | | | |
| С | 0.19 | 0.22 | 0.25 | |
| c2 | 0.19 | 0.22 | 0.25 | |
| D | 4.05 | 4.15 | 4.25 | |
| D1 | 3.80 | 4.00 | 4.20 | |
| D2 | 3.00 | 3.10 | 3.20 | |
| D3 | 0.30 | 0.40 | 0.50 | |
| D4 | 0.90 | 1.00 | 1.10 | |
| Е | 4.80 | 4.90 | 5.00 | |
| E1 | 3.10 | 3.20 | 3.30 | |
| E2 | 5.00 | 5.15 | 5.30 | |
| е | | 1.27 BSC | | |
| 1/2e | 0.635 BSC | | | |
| e1 | 0.40 REF | | | |
| Н | 6.00 | 6.15 | 6.30 | |
| L | 0.40 | 0.65 | 0.85 | |
| L1 | 0.80 | 0.90 | 1.00 | |
| L2 | 0.90 | 1.10 | 1.30 | |
| L3 | 0.00 | 0.10 | 0.20 | |
| q | 0° | 4° | 8° | |

RECOMMENDED LAND PATTERN

*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

GENERIC MARKING DIAGRAM*

BOTTOM VIEW



XXXXXX = Specific Device Code A = Assembly Location

WL = Wafer Lot
Y = Year

Y = Year W = Work Week

*This information is generic. Please refer to device data sheet for actual part marking. Some products may not follow the Generic Marking.

| DOCUMENT NUMBER: | 98AON82777G | Electronic versions are uncontrolled except when accessed directly from the Document Repository Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. | |
|------------------|-------------|--|-------------|
| DESCRIPTION: | LFPAK4 5x6 | | PAGE 1 OF 1 |

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales