ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,



ON Semiconductor®

NDS9952A Dual N & P-Channel Enhancement Mode Field Effect Transistor


General Description

These dual N- and P-channel enhancement mode power field effect transistors are produced using ON Semiconductors proprietary, high cell density, DMOS technology. This very high density process is especially tailored to minimize on-state resistance, provide superior switching performance, and withstand high energy pulses in the avalanche and commutation modes. These devices are particularly suited for low voltage applications such as notebook computer power management and other battery powered circuits where fast switching, low in-line power loss, and resistance to transients are needed.

Features

- $\begin{tabular}{lll} & N-Channel 3.7A, 30V, & $R_{\rm DS(ON)}$=0.08 Ω & $V_{\rm GS}$=$10V. \\ & P-Channel -2.9A, -30V, & $R_{\rm DS(ON)}$=0.13 Ω & $V_{\rm GS}$=-10V. \\ \end{tabular}$
- High density cell design or extremely low R_{DS(ON)}.
- High power and current handling capability in a widely used surface mount package.
- Dual (N & P-Channel) MOSFET in surface mount package.

D1 D2 D2 D2 SO-8 S1 G1 S2 G2



Absolute Maximum Ratings T_A= 25°C unless otherwise noted

Symbol	Parameter		N-Channel	P-Channel	Units	
V _{DSS}	Drain-Source Voltage		30	-30	V	
V _{GSS}	Gate-Source Voltage		± 20	± 20	V	
I _D	Drain Current - Continuous	(Note 1a)	± 3.7	± 2.9	Α	
	- Pulsed		± 15	± 10		
P _D	Power Dissipation for Dual Operation		2		W	
	Power Dissipation for Single Operation	(Note 1a)	1.6			
		(Note 1b)		1		
		(Note 1c)	C	.9		
T _J ,T _{STG}	Operating and Storage Temperature Range		-55 t	o 150	°C	
THERMA	L CHARACTERISTICS					
R _{eJA}	Thermal Resistance, Junction-to-Ambien	nermal Resistance, Junction-to-Ambient (Note 1a)		78	°C/W	
R _{BJC}	Thermal Resistance, Junction-to-Case	(Note 1)	40		°C/W	

Symbol	Parameter	Conditions		Type	Min	Тур	Max	Units
OFF CHA	RACTERISTICS							
BV _{DSS}	Drain-Source Breakdown Voltage	$V_{GS} = 0 \text{ V}, I_{D} = 250 \mu\text{A}$		N-Ch	30			V
		$V_{gs} = 0 \text{ V, } I_{p} = -250 \mu\text{A}$		P-Ch	-30			V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 24 V, V _{GS} = 0 V		N-Ch			2	μA
			T _J = 55°C				25	μA
		$V_{DS} = -24 \text{ V}, V_{GS} = 0 \text{ V}$	•	P-Ch			-2	μA
			T _J = 55°C				-25	μA
GSSF	Gate - Body Leakage, Forward	V _{GS} = 20 V, V _{DS} = 0 V	1	All			100	nA
I _{GSSR}	Gate - Body Leakage, Reverse	V _{GS} = -20 V, V _{DS} = 0 V		All			-100	nA
ON CHAR	ACTERISTICS (Note 2)	•					•	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_{D} = 250 \mu\text{A}$		N-Ch	1	1.7	2.8	V
			T _J = 125°C		0.7	1.2	2.2	1
		$V_{DS} = V_{GS}, I_{D} = -250 \mu\text{A}$	•	P-Ch	-1	-1.6	-2.8	
			T _J = 125°C		-0.85	-1.25	-2.5	
R _{DS(ON)}	Static Drain-Source On-Resistance	$V_{GS} = 10 \text{ V}, I_{D} = 1.0 \text{ A}$		N-Ch		0.06	0.08	Ω
			T _J = 125°C			0.08	0.13	
		$V_{GS} = 4.5 \text{ V}, I_{D} = 0.5 \text{ A}$				0.08	0.11	
			T _J = 125°C			0.11	0.18	
		$V_{gs} = -10 \text{ V}, I_{D} = -1.0 \text{ A}$	·	P-Ch		0.11	0.13	
			T _J = 125°C			0.15	0.21	
		$V_{GS} = -4.5 \text{ V}, I_{D} = -0.5 \text{ A}$				0.17	0.2	
			T _J = 125°C			0.24	0.32	
I _{D(on)}	On-State Drain Current	$V_{GS} = 10 \text{ V}, V_{DS} = 5 \text{ V}$		N-Ch	15			Α
		$V_{GS} = -10 \text{ V}, V_{DS} = -5 \text{ V}$		P-Ch	-10			
g _{FS}	Forward Transconductance	$V_{DS} = 15 \text{ V}, I_{D} = 3.7 \text{ A}$		N-Ch		6		S
		$V_{DS} = -15 \text{ V}, I_{D} = -2.9 \text{ A}$		P-Ch		4		
DYNAMIC	CHARACTERISTICS							
C _{iss}	Input Capacitance	N-Channel		N-Ch		320		pF
		$V_{DS} = 10 \text{ V}, V_{GS} = 0 \text{ V},$ f = 1.0 MHz		P-Ch		350		
C _{oss}	Output Capacitance			N-Ch		225		pF
		P-Channel $V_{DS} = -10 \text{ V}, V_{GS} = 0 \text{ V},$		P-Ch		260		
C _{rss}	Reverse Transfer Capacitance	f = 1.0 MHz		N-Ch		85		pF
				P-Ch		100		


Symbol	Cal Characteristics (T _A = 25°0 Parameter	Conditions	Type	Min	Тур	Max	Units
SWITCHII	NG CHARACTERISTICS (Note 2)					ı	
t _{D(on)}	Turn - On Delay Time	N-Channel $V_{DD} = 10 \text{ V}, I_{D} = 1 \text{ A},$	N-Ch		10	15	ns
			P-Ch		9	40	
ţ,	Turn - On Rise Time	V_{GEN} = 10 V, R_{GEN} = 6 Ω	N-Ch		13	20	ns
		P-Channel	P-Ch		21	40	
t _{D(off)}	Turn - Off Delay Time	$V_{DD} = -10 \text{ V}, \ I_{D} = -1 \text{ A}, \ V_{GEN} = -10 \text{ V}, \ R_{GEN} = 6 \Omega$	N-Ch		21	50	ns
		GEN 10 V, NGEN 0 11	P-Ch		21	90	
t,	Turn - Off Fall Time		N-Ch		5	50	ns
			P-Ch		8	50	
Q_g	Total Gate Charge	N-Channel	N-Ch		9.5	27	nC
		$V_{DS} = 10 \text{ V},$ $V_{DS} = 3.7 \text{ A}, V_{GS} = 10 \text{ V}$	P-Ch		10	25	
Q_{gs}	Gate-Source Charge	P-Channel V _{DS} = -10 V, I _D = -2.9 A, V _{GS} = -10 V	N-Ch		1.5		nC
			P-Ch		1.6		
Q_{gd}	Gate-Drain Charge		N-Ch		3.3		nC
			P-Ch		3.4		
DRAIN-S	OURCE DIODE CHARACTERISTIC	S AND MAXIMUM RATINGS					
I _s	Maximum Continuous Drain-Source Diode Forward Current		N-Ch			1.2	Α
			P-Ch			-1.2	
V _{SD}	Drain-Source Diode Forward Voltage	$V_{GS} = 0 \text{ V}, I_{S} = 1.25 \text{ A} \text{ (Note 2)}$	N-Ch		8.0	1.3	V
		$V_{GS} = 0 \text{ V}, I_{S} = -1.25 \text{ A} \text{ (Note 2)}$	P-Ch		-0.8	-1.3	
t,	Reverse Recovery Time	$V_{GS} = 0 \text{ V}, I_F = 1.25 \text{ A}, dI_F/dt = 100 \text{ A/}\mu\text{s}$	N-Ch			75	ns
		$V_{GS} = 0 \text{ V}, I_F = -1.25 \text{ A}, dI_F/dt = 100 \text{ A/}\mu\text{s}$	P-Ch			100	


Notes:


$$P_D(t) = \frac{T_{J^-}T_A}{R_{\theta J} A(t)} = \frac{T_{J^-}T_A}{R_{\theta J} d^*R_{\theta C} A(t)} = I_D^2(t) \times R_{DS(ON) \theta T_J}$$

Typical R_{BJA} for single device operation using the board layouts shown below on 4.5"x5" FR-4 PCB in a still air environment:

- a. 78°C/W when mounted on a 0.5 in² pad of 2oz cpper.
- b. 125°C/W when mounted on a 0.02 in² pad of 2oz cpper.
- c. 135°C/W when mounted on a 0.003 in² pad of 2oz cpper.







Scale 1 : 1 on letter size paper

2. Pulse Test: Pulse Width ≤ 300µs, Duty Cycle ≤ 2.0%.

^{1.} $R_{g,A}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. $R_{g,C}$ is guaranteed by design while $R_{g,C}$ is determined by the user's board design.

Typical Electrical Characteristics: N-Channel




Figure 1. N-Channel On-Region Characteristics.




Figure 2. N-Channel On-Resistance Variation with Gate Voltage and Drain Current.




Figure 3. N-Channel On-Resistance Variation with Temperature.




Figure 4. N-Channel On-Resistance Variation with Drain Current and Temperature.




Figure 5. N-Channel Transfer Characteristics.




Figure 6. N-Channel Gate Threshold Variation with Temperature.

Typical Electrical Characteristics: N-Channel (continued)




Figure 7. N-Channel Breakdown Voltage Variation with Temperature.




Figure 8. N-Channel Body Diode Forward Voltage Variation with Current and Temperature.




Figure 9. N-Channel Capacitance Characteristics.




Figure 10. N-Channel Gate Charge Characteristics.




Figure 11. N-Channel Transconductance Variation with Drain Current and Temperature.

Typical Electrical Characteristics: P-Channel (continued)




Figure 12. P-Channel On-Region Characteristics.




Figure 13. P-Channel On-Resistance Variation with Gate Voltage and Drain Current.




Figure 14. P-Channel On-Resistance Variation with Temperature.




Figure 15. P-Channel On-Resistance Variation with Drain Current and Temperature.




Figure 16. P-Channel Transfer Characteristics.




Figure 17. P-Channel Gate Threshold Variation with Temperature.

Typical Electrical Characteristics: P-Channel (continued)




Figure 18. P-Channel Breakdown Voltage Variation with Temperature.




Figure 19. P-Channel Body Diode Forward Voltage Variation with Current and Temperature.




Figure 20. P-Channel Capacitance Characteristics.




Figure 21. P-Channel Gate Charge Characteristics.




Figure 22. P-Channel Transconductance Variation with Drain Current and Temperature.

Typical Thermal Characteristics: N & P-Channel




Figure 23. SO-8 Dual Package Maximum Steady-State Power Dissipation versus Copper Mounting Pad Area.




Figure 25. P-Ch Maximum Steady- State
Drain Current versus Copper Mounting
Pad Area.




Figure 27. P-Channel Maximum Safe Operating Area.




Figure 24. N-Ch Maximum Steady- State
Drain Current versus Copper Mounting
Pad Area.




Figure 26. N-Channel Maximum Safe Operating Area.

Typical Thermal Characteristics: N & P-Channel




Figure 28. Transient Thermal Response Curve.

Thermal characterization performed using the conditions described in note 1c. Transient thermal response will change depending on the circuit board design.




Figure 29. N or P-Channel Switching Test Circuit.

Figure 30. N or P-Channel Switching Waveforms.

ON Semiconductor and III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative