# **ON Semiconductor**

## Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

# Schottky Barrier Rectifier Trench-based, High Performance

# NRTS30120MFS

This Trench Schottky rectifier is high performance device in SO-8 FL package. The lower forward voltage, less leakage current, and small junction capacitance are suitable to high switching frequency high density DC to DC conversion application. Offering higher avalanche energy capability for Oring or reverse protection application. The SO-8 FL package provides an excellent thermal performance, less land area of board space, and low profile.

#### **Features**

- Lower Forward Voltage Drop
- Less Leakage Current in High Temperature
- Small Junction Capacitance for High Switching Frequency
- Higher Avalanche Energy Capability
- 175°C Operating Junction Temperature
- Good Alternative Solution of SMC and DPAK Package
- Small Footprint Land Area: 31.2 mm<sup>2</sup>
- Low Profile Maximum Height of 1.1 mm
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

#### **Mechanical Characteristics:**

- Case: Molded Epoxy
- Epoxy Meets UL 94 V-0 @ 0.125 in
- Weight: 95 mg (Approximately)
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Maximum for 10 Seconds

1

• MSL 1

#### **Applications**

- High Switching Frequency DC/DC Converter
- 2<sup>nd</sup> Rectifier
- Freewheeling Diode used with Inductive Load
- Oring / Reverse Protection




#### ON Semiconductor®

www.onsemi.com

# TRENCH SCHOTTKY RECTIFIER 30 AMPERES 120 VOLTS







MARKING

T30120 = Specific Device Code A = Assembly Location

Y = Year
W = Work Week
ZZ = Lot Traceability

#### **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
NRTS30120MFST3G	SO-8 FL (Pb-Free)	5000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

#### **MAXIMUM RATINGS**

R	ating	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage		V <sub>RRM</sub> V <sub>RWM</sub> V <sub>R</sub>	120	V
Continuous Forward Current (T <sub>C</sub> = 162°	C, DC)	I <sub>F(DC)</sub>	30	Α
Peak Repetitive Forward Current (T <sub>C</sub> =	159°C, Square Wave, Duty = 0.5)	I <sub>FRM</sub>	60	Α
Non-Repetitive Peak Surge Current	Repetitive Peak Surge Current Sinusoidal Halfwave, 8.3 ms I <sub>FSM</sub>	I <sub>FSM</sub>	300	Α
	Square wave, 1 ms		370	
	Square wave, 100 μs		650	
Non-Repetitive Avalanche Energy (T <sub>J</sub> =	25°C)	E <sub>AS</sub>	350	mJ
Storage Temperature Range		T <sub>stg</sub>	-65 to +175	°C
Operating Junction Temperature Range	(Note 1)	TJ	-55 to +175	°C
ESD Rating (Human Body Model)			38	
ESD Rating (Machine Model)			M4	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

#### THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Ambient (Note 2)	$R_{ hetaJA}$	56	°C/W
Thermal Resistance, Junction-to-Case Bottom (Note 2)	$R_{ heta JCB}$	0.71	°C/W
Thermal Characterization, Junction-to-Case Top (Note 2)	ΨЈСТ	3.8	°C/W
Thermal Characterization, Junction-to-Lead of Cathode (Note 2)	ΨJLC	1.6	°C/W

<sup>2.</sup> Assume 600 mm<sup>2</sup>, 1 oz. copper bond pad on a FR4 board.


#### **ELECTRICAL CHARACTERISTICS**

Characteristic	Symbol	Тур	Max	Unit
Instantaneous Forward Voltage	V <sub>F</sub>			V
$(I_F = 15 \text{ A}, T_J = 25^{\circ}\text{C})$		0.65	-	
$(I_F = 15 \text{ A}, T_J = 125^{\circ}\text{C})$		0.58	-	
$(I_F = 30 \text{ A}, T_J = 25^{\circ}\text{C})$		0.85	0.95	
$(I_F = 30 \text{ A}, T_J = 125^{\circ}\text{C})$		0.67	0.73	
Instantaneous Reverse Current	I <sub>R</sub>			
(V <sub>R</sub> = Rated DC Voltage, T <sub>J</sub> = 25°C)		22	150	μΑ
(V <sub>R</sub> = Rated DC Voltage, T <sub>J</sub> = 125°C)		14	40	mA
Junction Capacitance	СЈ			pF
$(V_R = 1 \text{ V}, T_J = 25^{\circ}\text{C}, f = 1 \text{ MHz})$		1470	ı	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 3. Pulse Test: Pulse Width = 300  $\mu$ s, Duty Cycle  $\leq$  2.0%.

<sup>1.</sup> The heat generated must be less than the thermal conductivity from Junction–to–Ambient  $dP_D/dT_J < 1/R_{\theta JA}$ 


#### **TYPICAL CHARACTERISTICS**



30 I<sub>F(PK)</sub>, PEAK FORWARD CURRENT (A)  $T_J = 175^{\circ}C$  $R_{\theta JA} = 56^{\circ}C/W$ 25 D = 0.2Square Wave 20 D = 0.315 D = 0.510 DC 5 25 40 55 85 100 115 130 TA, AMBIENT TEMPERATURE (°C)

Figure 1. Forward Current Derating of Case Temperature

Figure 2. Forward Current Derating of Ambient Temperature







Figure 3. Typical Forward Characteristics

Figure 4. Maximum Forward Characteristics






Figure 5. Typical Reverse Characteristics

Figure 6. Maximum Reverse Characteristics

#### **TYPICAL CHARACTERISTICS**




Figure 7. Typical Junction Capacitance

Figure 8. Average Forward Power Dissipation





Figure 9. Typical Thermal Characteristics, Junction-to-Ambient

#### PACKAGE DIMENSIONS



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and the are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="https://www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor newsen owarranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold

#### **PUBLICATION ORDERING INFORMATION**

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative