Dual DPDT Ultra-Low R_{ON} Switch

The NLAS3699 is a dual independent ultra-low R_{ON} DPDT analog switch. This device is designed for low operating voltage, high current switching of speaker output for cell phone applications. It can switch a balanced stereo output. The NLAS3699 can handle a balanced microphone/speaker/ring-tone generator in a monophone mode. The device contains a break-before-make feature.

Features

- Single Supply Operation 1.65 to 3.6 V V_{CC}
- Maximum Breakdown Voltage: 4.6 V
- Tiny 3 x 3 mm QFN Pb–Free Package Meet JEDEC MO–220 Specifications
- Low Static Power
- This is a Pb-Free Device*

Typical Applications

- Cell Phone Speaker/Microphone Switching
- Ringtone-Chip/Amplifier Switching
- Four Unbalanced (Single-Ended) Switches
- Stereo Balanced (Push-Pull) Switching

Important Information

• ESD Protection:

HBM (Human Body Model) > 8000 V MM (Machine Model) > 400 V

- Continuous Current Rating Through each Switch ±300 mA
- Conforms to: JEDEC MO-220, Issue H, Variation VEED-6
- Pin for Pin Compatible with STG3699




ON Semiconductor®

http://onsemi.com

MARKING DIAGRAMS




QFN-16 CASE 485AE



A = Assembly Location

L = Wafer Lot Y = Year W = Work Week = Pb-Free Package

(Note: Microdot may be in either location)



ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 9 of this data sheet.

^{*}For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.




Figure 1. Input Equivalent Circuit

PIN DESCRIPTION

QFN PIN #	Symbol	Name and Function
1, 3, 5, 7, 9, 11, 13, 15	1S1 to 4S1, 1S2 to 4S2	Independent Channels
2, 10	1-2IN, 3-4IN	Controls
4, 8, 12, 16	D1 to D4	Common Channels
6	GND	Ground (V)
14	V _{CC}	Positive Supply Voltage

TRUTH TABLE

IN	\$1	S2
Н	ON	OFF(*)
L	OFF(*)	ON

^{*}High impedance.

MAXIMUM RATINGS

Symbol	Parameter	Val	ue	Unit	
V _{CC}	Positive DC Supply Voltage	- 0.5 to	+4.6	V	
V _{IS}	Analog Input Voltage (V _{NO} , V _{NC} , or V _{COM})	Analog Input Voltage ($V_{NO}, V_{NC}, \text{ or } V_{COM}$) $-0.5 \le V_{IS} \le V_{CC}$		$V_{IS} \leq V_{CC}$	V
V _{IN}	Digital Select Input Voltage	$-0.5 \le V_{I} \le +4.6$		V	
I _{anl1}	Continuous DC Current from COM to NC/NO	±3	800	mA	
I _{anl-pk 1}	Peak Current from COM to NC/NO, 10 duty cycle (Note 1)	± 500		mA	
I _{clmp}	Continuous DC Current into COM/NO/NC with respect to V _{CC} or	±100		mA	
t _r , t _f	Input Rise or Fall Time, SELECT	CC = 1.6 V - 2.7 V CC = 3.0 V - 3.6 V	0 0	20 10	ns/V

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Defined as 10% ON, 90% off duty cycle.

RECOMMENDED OPERATING CONDITIONS

Symbol	Parameter	Min	Max	Unit	
V _{CC}	DC Supply Voltage		1.65	3.6	V
V _{IN}	Digital Select Input Voltage		GND	V _{CC}	V
V_{IS}	Analog Input Voltage (NC, NO, COM)		GND	V_{CC}	V
T _A	Operating Temperature Range		-40	+ 85	°C
t _r , t _f	Input Rise or Fall Time, SELECT V ₀	_{CC} = 1.6 V - 2.7 V _{CC} = 3.0 V - 3.6 V	0	20 10	ns/V

DC CHARACTERISTICS - Digital Section (Voltages Referenced to GND)

				Guaranteed Limit		
Symbol	Parameter	Condition	V _{CC}	-40°C to 25°C	<85°C	Unit
V _{IH}	Minimum High-Level Input		1.8	1.2	1.2	V
	Voltage, Select Inputs		2.5	1.7	1.7	
			3.6	2.2	2.2	
V _{IL}	Maximum Low-Level Input		1.8	0.4	0.4	V
	Voltage, Select Inputs		2.5	0.5	0.5	
			3.6	0.7	0.7	
I _{IN}	Maximum Input Leakage Current, Select Inputs	V _{IN} = V _{CC} or GND	3.6	±0.1	±1.0	μΑ
I _{OFF}	Power Off Leakage Current	V _{IN} = V _{CC} or GND	0	± 0.5	± 2.0	μΑ
I _{CC}	Maximum Quiescent Supply Current (Note 2)	Select and V _{IS} = V _{CC} or GND	1.65 to 3.6	±1.0	± 2.0	μΑ

DC ELECTRICAL CHARACTERISTICS - Analog Section

				Guaranteed Maximum Limit				
				-40°C to 25°C <85°C				
Symbol	Parameter	Condition	V _{CC}	Min	Max	Min	Max	Unit
R _{ON}	NC/NO On-Resistance (Note 2)	$\begin{aligned} &V_{IN} \leq V_{IL} \text{ or } V_{IN} \geq V_{IH} \\ &V_{IS} = GND \text{ to } V_{CC} \\ &I_{IN}I \leq 100 \text{ mA} \end{aligned}$	2.5 3.0 3.6		0.65 0.6 0.55		0.75 0.75 0.7	Ω
R _{FLAT}	NC/NO On–Resistance Flatness (Notes 2, 4)	I _{COM} = 100 mA V _{IS} = 0 to V _{CC}	2.5 3.0 3.6		0.15 0.15 0.15		0.15 0.15 0.15	Ω
ΔR _{ON}	On-Resistance Match Between Channels (Notes 2 and 3)	$V_{IS} = 1.3 \text{ V};$ $I_{COM} = 100 \text{ mA}$ $V_{IS} = 1.5 \text{ V};$ $I_{COM} = 100 \text{ mA}$ $V_{IS} = 1.8 \text{ V};$ $I_{COM} = 100 \text{ mA}$	2.5 3.0 3.6		0.06 0.05 0.05		0.06 0.05 0.05	Ω
I _{NC(OFF)} I _{NO(OFF)}	NC or NO Off Leakage Current (Note 2)	$\begin{aligned} & V_{IN} = V_{IL} \text{ or } V_{IH} \\ & V_{NO} \text{ or } V_{NC} = 0.3 \text{ V} \\ & V_{COM} = 3.3 \text{ V} \end{aligned}$	3.6	-5.0	5.0	-10	10	nA
I _{COM(ON)}	COM ON Leakage Current (Note 2)	$\begin{split} &V_{IN} = V_{IL} \text{ or } V_{IH} \\ &V_{NO} \text{ 0.3 V or 3.3 V with} \\ &V_{NC} \text{ floating or} \\ &V_{NC} \text{ 0.3 V or 3.3 V with} \\ &V_{NO} \text{ floating} \\ &V_{COM} = \text{ 0.3 V or 3.3 V} \end{split}$	3.6	-10	10	-100	100	nA

Guaranteed by design. Resistance measurements do not include test circuit or package resistance.
 ΔR_{ON =} R_{ON(MAX)} - R_{ON(MIN)} between nS1 or nS2.
 Flatness is defined as the difference between the maximum and minimum value of on-resistance as measured over the specified analog signal ranges.

AC ELECTRICAL CHARACTERISTICS (Input $t_r = t_f = 3.0 \text{ ns}$)

					Guaranteed Maximum Limit					
			v _{cc}	V _{IS}	-40°C		C to 25°C < 8		<85°C	
Symbol	Parameter	Test Conditions	(V)			Тур*	Max	Min	Max	Unit
t _{ON}	Turn-On Time	$R_L = 50 \Omega$, $C_L = 35 pF$ (Figures 3 and 4)	2.3 – 3.6	1.5			50		60	ns
t _{OFF}	Turn-Off Time	$R_L = 50 \Omega$, $C_L = 35 pF$ (Figures 3 and 4)	2.3 – 3.6	1.5			30		40	ns
t _{BBM}	Minimum Break-Before-Make Time	$V_{\text{IS}} = 3.0$ $R_{\text{L}} = 50 \ \Omega, \ C_{\text{L}} = 35 \ \text{pF}$ (Figure 2)	3.0	1.5	2	15				ns


		Typical @ 25, V _{CC} = 3.6 V	
C _{IN}	Control Pin Input Capacitance	2.5	pF
C _{SN}	SN Port Capacitance	72	pF
C _D	D Port Capacitance When Switch is Enabled	230	pF

^{*}Typical Characteristics are at 25°C.

ADDITIONAL APPLICATION CHARACTERISTICS (Voltages Referenced to GND Unless Noted)

			V _{CC}	25°C	
Symbol	Parameter	Condition	(V)	Typical	Unit
BW	Maximum On–Channel –3dB Bandwidth or Minimum Frequency Response (Figure 12)	V _{IN} centered between V _{CC} and GND (Figure 5)	1.65 – 3.6	20	MHz
V _{ONL}	Maximum Feed-through On Loss	V_{IN} = 0 dBm @ 100 kHz to 50 MHz V_{IN} centered between V_{CC} and GND (Figure 5)	1.65 – 3.6	-0.06	dB
V _{ISO}	Off-Channel Isolation (Figure 13)	$f = 100 \text{ kHz}$; $V_{IS} = 1 \text{ V RMS}$; $C_L = 5 \text{ pF}$ V_{IN} centered between V_{CC} and GND(Figure 5)	1.65 – 3.6	-62	dB
Q	Charge Injection Select Input to Common I/O (Figure 8)	$V_{IN} = V_{CC \text{ to}} \text{ GND, } R_{IS} = 0 \Omega, C_L = 1 \text{ nF}$ Q = C _L x ΔV_{OUT} (Figure 6)	1.65 – 3.6	50	рС
THD	Total Harmonic Distortion THD + Noise (Figure 7)	F_{IS} = 20 Hz to 20 kHz, R_L = R_{gen} = 600 Ω , C_L = 50 pF V_{IS} = 2 V_{PP}	3.6	0.01	%
VCT	Channel-to-Channel Crosstalk	f = 100 kHz; V_{IS} = 1 V RMS, C_L = 5 pF, R_L = 50 Ω V_{IN} centered between V_{CC} and GND (Figure 5)	1.65 – 3.6	-62	dB

^{5.} Off-Channel Isolation = 20log10 (Vcom/Vno), Vcom = output, Vno = input to off switch.







Figure 2. t_{BBM} (Time Break-Before-Make)







Figure 3. t_{ON}/t_{OFF}







Figure 4. t_{ON}/t_{OFF}



Channel switch control/s test socket is normalized. Off isolation is measured across an off channel. On loss is the bandwidth of an On switch. $V_{\rm ISO}$, Bandwidth and $V_{\rm ONL}$ are independent of the input signal direction.

$$V_{ISO} = Off Channel Isolation = 20 Log \left(\frac{VOUT}{V_{IN}}\right)$$
 for V_{IN} at 100 kHz

 $V_{ONL} = On \; Channel \; Loss = 20 \; Log \left(\frac{V_{OUT}}{V_{IN}} \right) \; \; \text{for} \; V_{IN} \; \text{at} \; 100 \; \text{kHz} \; \text{to} \; 50 \; \text{MHz}$

Bandwidth (BW) = the frequency 3 dB below V_{ONL}

 V_{CT} = Use V_{ISO} setup and test to all other switch analog input/outputs terminated with 50 Ω

Figure 5. Off Channel Isolation/On Channel Loss (BW)/Crosstalk (On Channel to Off Channel)/V_{ONL}




Figure 6. Charge Injection: (Q)




Figure 7. Total Harmonic Distortion Plus Noise Versus Frequency

Figure 8. Charge Injection versus Vis




Figure 9. On-Resistance vs. COM Voltage




Figure 10. R_{ON} vs. V_{IN} vs. Temperature @ V_{CC} = 3.0 V




Figure 11. R_{ON} vs. V_{IN} vs. Temperature @ V_{CC} = 3.6 V




Figure 12. Bandwidth vs. Frequency @ V_{CC} = 1.65 V to 3.6 V




Figure 13. Off-Isolation vs. Frequency @ V_{CC} = 1.65 V to 3.6 V





Figure 14. Phase Angle vs. Frequency @ V_{CC} = 1.65 V to 3.6 V

DEVICE ORDERING INFORMATION

		Devi	ce Nomenc	lature			
Device Order Number	Circuit Indicator	Technology	Device Function	Package Suffix	Tape & Reel Suffix	Package Type	Tape & Reel Size [†]
NLAS3699MN1R2G	NL	AS	3699	MN1	R2	QFN (Pb-Free)	3000 Unit / Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.



DOCUMENT NUMBER:	98AON14949D	Electronic versions are uncontrolled except when accessed directly from the Document Repositor Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.			
DESCRIPTION:	QFN16 3X3, 0.5P		PAGE 1 OF 1		

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI., and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems. or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales