ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

Power MOSFET 23 Amps, 25 Volts N-Channel D²PAK

Designed for low voltage, high speed switching applications in power supplies, converters and power motor controls and bridge circuits.

Features

• Pb-Free Packages are Available

Typical Applications

- Planar HD3e Process for Fast Switching Performance
- Low R_{DS(on)} to Minimize Conduction Loss
- Low C_{iss} to Minimize Driver Loss
- Low Gate Charge
- Optimized for High Side Switching Requirements in High-Efficiency DC-DC Converters

MAXIMUM RATINGS (T_J = 25° C unless otherwise specified)

Parameter	Symbol	Value	Unit
Drain-to-Source Voltage	V _{DSS}	25	Vdc
Gate-to-Source Voltage - Continuous	V _{GS}	±20	Vdc
Drain Current - Continuous @ $T_A = 25^{\circ}C$, Limited by Chip - Continuous @ $T_A = 25^{\circ}C$, Limited by Package - Single Pulse ($t_p = 10 \ \mu$ s)	I _D I _D I _{DM}	23 6.0 60	A
Total Power Dissipation @ T _A = 25°C	PD	37.5	W
Operating and Storage Temperature Range	T _J , T _{stg}	-55 to 150	ů
Thermal Resistance - Junction-to-Case	$R_{\theta JC}$	3.3	°C/W
Maximum Lead Temperature for Soldering Purposes, 1/8" from case for 10 seconds	ΤL	260	°C


Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.




ON Semiconductor®

http://onsemi.com

23 AMPERES, 25 VOLTS $R_{DS(on)} = 32 \text{ m}\Omega$ (Typ)



MARKING DIAGRAM & PIN ASSIGNMENTS



ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise specified)

Characteristics		Symbol	Min	Тур	Max	Unit		
OFF CHARACTERISTICS		•		•	-			
Drain-to-Source Breakdown $V_{GS} = 0 Vdc, I_D = 2$ Temperature Coefficient (Posit	50 μAdc)	V(br) _{DSS}	25 -	28 -		Vdc mV/°C		
Zero Gate Voltage Drain Current ($V_{DS} = 20 \text{ Vdc}, V_{GS} = 0 \text{ Vdc}$) ($V_{DS} = 20 \text{ Vdc}, V_{GS} = 0 \text{ Vdc}, T_J = 150^{\circ}\text{C}$)		$(V_{DS} = 20 \text{ Vdc}, V_{GS} = 0 \text{ Vdc})$		I _{DSS}			1.0 10	μAdc
Gate-Body Leakage Current (V _{GS} = ±20 Vdc, V _{DS} = 0 Vdc)		I _{GSS}	-	-	±100	nAdc		
ON CHARACTERISTICS (Not	e 1)							
Gate Threshold Voltage (Note $(V_{DS} = V_{GS}, I_D = 25)$ Threshold Temperature Coeffic	0 μAdc)	V _{GS(th)}	1.0 -	1.8 -	2.0 -	Vdc mV/°C		
Static Drain-to-Source On-Resistance (Note 1) ($V_{GS} = 4.5 \text{ Vdc}, I_D = 6 \text{ Adc}$) ($V_{GS} = 10 \text{ Vdc}, I_D = 6 \text{ Adc}$)		R _{DS(on)}		50.3 32.3	60 45	mΩ		
Forward Transconductance (N $(V_{DS} = 10 \text{ Vdc}, I_D = $		9fs	_	14	-	Mhos		
DYNAMIC CHARACTERISTIC	S		-					
Input Capacitance		Ciss	-	225	-	pF		
Output Capacitance	(V _{DS} = 20 Vdc, V _{GS} = 0 V, f = 1 MHz)	C _{oss}	-	108	-			
Transfer Capacitance		C _{rss}	-	48	-			
SWITCHING CHARACTERIS	TICS (Note 2)							
Turn-On Delay Time		t _{d(on)}	-	2.0	-	ns		
Rise Time	(V _{GS} = 10 Vdc, V _{DD} = 10 Vdc,	t _r	-	14.9	-			
Turn-Off Delay Time	$I_{\rm D} = 6 {\rm Adc}, {\rm R}_{\rm G} = 3 \Omega)$	t _{d(off)}	-	9.9	-			
Fall Time		t _f	-	2.0	-			
Gate Charge		QT	-	3.76	-	nC		
	(V _{GS} = 4.5 Vdc, I _D = 6 Adc, V _{DS} = 10 Vdc) (Note 1)	Q ₁	-	1.7	-			
		Q ₂	-	1.6	-			
SOURCE-DRAIN DIODE CHA	ARACTERISTICS							
Forward On-Voltage	(I _S = 6 Adc, V _{GS} = 0 Vdc) (Note 1) (I _S = 6 Adc, V _{GS} = 0 Vdc, T _J = 125°C)	V _{SD}	-	0.87	1.2	Vdc		


	(I _S = 6 Adc, V _{GS} = 0 Vdc) (Note 1) (I _S = 6 Adc, V _{GS} = 0 Vdc, T _J = 125°C)	• 50	- -	0.87 0.74	1.2 -	
Reverse Recovery Time		t _{rr}	-	8.7	-	ns
	(I _S = 6 Adc, V _{GS} = 0 Vdc,	t _a	-	5.2	-	
	dI _S /dt = 100 A/µs) (Note 1)	t _b	-	3.5	-	
Reverse Recovery Stored Charge		Q _{RR}	-	0.003	-	μC

Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2%.
Switching characteristics are independent of operating junction temperatures.

ORDERING INFORMATION

Device	Package	Shipping [†]
NTB23N03R	D ² PAK	50 Units / Rail
NTB23N03RG	D ² PAK (Pb-Free)	50 Units / Rail
NTB23N03RT4	D ² PAK	800 Units / Tape & Reel
NTB23N03RT4G	D ² PAK (Pb-Free)	800 Units / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.






Figure 9. Resistive Switching Time Variation versus Gate Resistance

Figure 10. Diode Forward Voltage versus Current

PACKAGE DIMENSIONS


MILLIMETERS

1.14 1.40 7.87 ----

9.65 9.65 10.29 4.06 4.83

0.92

8.64



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other application in which the failure of the SCILLC product create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunit//Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5773-3850 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative