ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

MOSFET - Power, Single N-Channel, TOLL

80 V, 1.7 mΩ, 203 A

NTBLS1D7N08H

Features

- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- Lowers Switching Noise/EMI
- These Devices are Pb–Free and are RoHS Compliant Typical Applications
- Power Tools, Battery Operated Vacuums
- UAV/Drones, Material Handling
- BMS/Storage, Home Automation

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V _{DSS}	80	V
Gate-to-Source Voltage			V _{GS}	±20	V
Continuous Drain		$T_{C} = 25^{\circ}C$	I _D	203	А
Current R _{θJC} (Notes 1, 3)	Steady	T _C = 100°C		143	
Power Dissipation	State	$T_{C} = 25^{\circ}C$	PD	167	W
R _{θJC} (Note 1)		$T_{C} = 100^{\circ}C$		83	
Continuous Drain		$T_A = 25^{\circ}C$	I _D	29	А
Current R _{θJA} (Notes 1, 2, 3)	Steady	T _A = 100°C		21	
Power Dissipation	State	$T_A = 25^{\circ}C$	PD	3.5	W
R _{θJA} (Notes 1, 2)		$T_A = 100^{\circ}C$		1.7	
Pulsed Drain Current	$T_{\rm C} = 25^{\circ}$	°C, t _p = 100 μs	I _{DM}	1173	А
Operating Junction and Storage Temperature Range			T _J , T _{stg}	–55 to +175	°C
Source Current (Body Diode)			I _S	139	А
Single Pulse Drain-to-Source Avalanche Energy ($I_{L(pk)} = 27 \text{ A}$)			E _{AS}	1093.5	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			ΤL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State (Note 1)	$R_{\theta JC}$	0.9	°C/W
Junction-to-Ambient - Steady State (Notes 1, 2)	$R_{\theta JA}$	43	

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

2. Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.


3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.



ON Semiconductor®

www.onsemi.com

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
80 V	1.7 m Ω @ 10 V	203 A



N-CHANNEL MOSFET



CASE 100CU

MARKING DIAGRAM



1D7N08H = Specific Device Code A = Assembly Location Y = Year WW = Work Week ZZ = Lot Traceability

ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.


ELECTRICAL CHARACTERISTICS (T_J = $25^{\circ}C$ unless otherwise noted)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit	
OFF CHARACTERISTICS								
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V_{GS} = 0 V, I_D = 250 μ A		80			V	
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} / TJ				57		mV/°C	
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 V, T_{J} = 25 °C$ $V_{DS} = 80 V T_{J} = 125 °C$				10	μΑ	
						250		
Gate-to-Source Leakage Current	I _{GSS}	V _{DS} = 0 V, V _{GS} = 20 V				100	nA	
ON CHARACTERISTICS								
Gate Threshold Voltage	V _{GS(TH)}	V_{GS} = V_{DS} , I_D = 479 μ A		2.0	2.9	4.0	V	
Threshold Temperature Coefficient	V _{GS(TH)} /T _J	$I_D = 479 \ \mu A$, ref to $25^{\circ}C$			-7.3		mV/°C	
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V I _D = 80 A			1.29	1.7		
		V _{GS} = 6 V	I _D = 43 A		1.76	2.6	mΩ	
Forward Transconductance	9 _{FS}	V _{DS} = 5 V, I _D = 80 A			271		S	
CHARGES, CAPACITANCES & GATE RE	SISTANCE						-	
Input Capacitance	C _{ISS}			7675		pF		
Output Capacitance	C _{OSS}	V _{GS} = 0 V, f = 1 MHz, V _{DS} = 40 V			1059			
Reverse Transfer Capacitance	C _{RSS}				41			
Gate-Resistance	R _G				0.6			
Total Gate Charge	Q _{G(TOT)}				121			
Threshold Gate Charge	Q _{G(TH)}	V _{GS} = 10 V, V _{DS} = 40 V; I _D = 80 A			19		nC	
Gate-to-Source Charge	Q _{GS}				32			
Gate-to-Drain Charge	Q _{GD}				29			
Plateau Voltage	V _{GP}				4.5		V	
Output Charge	Q _{OSS}	V_{GS} = 0 V, V_{DD} = 40 V			149		nC	
SWITCHING CHARACTERISTICS (Note 4	1)					-	-	
Turn-On Delay Time	t _{d(ON)}	V_{GS} = 10 V, V_{DS} = 40 V, I_{D} = 80 A, R_{G} = 6 Ω			29		- ns	
Rise Time	t _r				25			
Turn-Off Delay Time	t _{d(OFF)}				89			
Fall Time	t _f				35			
DRAIN-SOURCE DIODE CHARACTERIS	STICS				-		-	
Forward Diode Voltage	V _{SD}	$V_{GS} = 0 V$, $T_J = 25^{\circ}C$			0.82	1.2		
		$I_{\rm S} = 80 \rm A$	T _J = 125°C		0.69		V	
Reverse Recovery Time	t _{RR}	V_{GS} = 0 V, dIS/dt = 100 A/µs, I _S = 43 A			73		ns	
Reverse Recovery Charge	Q _{RR}				138		nC	


Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS





Figure 13. Transient Thermal Impedance

DEVICE ORDERING INFORMATION

Device	Marking	Package	Shipping [†]
NTBLS1D7N08H	1D7N08H	M0–299A (Pb–Free)	2000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS



ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor hy such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, a

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

Email Requests to: orderlit@onsemi.com
ON Semiconductor Website: www.onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative