# **MOSFET** – Power, Single, P-Channel, TSOP-6 -20 V, -5.8 A

## Features

- Low R<sub>DS(on)</sub> in TSOP-6 Package
- 1.8 V Gate Rating
- Fast Switching
- NV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

# Applications

- Optimized for Battery and Load Management Applications in Portable Equipment
- High Side Load Switch
- Switching Circuits for Game Consoles, Camera Phone, etc.

# MAXIMUM RATINGS (T<sub>J</sub> = 25°C unless otherwise stated)

Param	Symbol	Value	Unit			
Drain-to-Source Voltage	V <sub>DSS</sub>	-20	V			
Gate-to-Source Voltage	9		V <sub>GS</sub>	±8.0	V	
Continuous Drain	Steady	$T_A = 25^{\circ}C$	I <sub>D</sub>	-5.1		
Current (Note 1)	State	$T_A = 85^{\circ}C$		-3.6	А	
	$t \le 5 s$	$T_A = 25^{\circ}C$		-5.8		
Power Dissipation	Steady		PD	1.25		
(Note 1)	State	$T_A = 25^{\circ}C$			W	
	$t \le 5 s$			1.6		
Continuous Drain	Steady State	$T_A = 25^{\circ}C$	I <sub>D</sub>	-3.7	А	
Current (Note 2)		T <sub>A</sub> = 85°C		-2.7	~	
Power Dissipation (Note 2)		$T_A = 25^{\circ}C$	P <sub>D</sub>	0.7	W	
Pulsed Drain Current	t <sub>p</sub> = 10 μ	s	I <sub>DM</sub>	-20	А	
Operating Junction and Storage Temperature			T <sub>J</sub> , T <sub>STG</sub>	–55 to 150	°C	
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			ΤL	260	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Surface-mounted on FR4 board using 1 in sq pad size (Cu area = 1.127 in sq [2 oz] including traces)

 Surface-mounted on FR4 board using the minimum recommended pad size (Cu area = 0.0775 in sq).





# **ON Semiconductor®**

## www.onsemi.com


V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> TYP	I <sub>D</sub> MAX
-20 V	25 mΩ @ –4.5 V	–5.1 A
	32 mΩ @ –2.5 V	-4.5 A
	41 mΩ @ –1.8 V	–2.5 A







# **PIN ASSIGNMENT**



# ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.

Semiconductor Components Industries, LLC, 2015
 May, 2019 – Rev. 2

#### THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Ambient - Steady State (Note 3)	$R_{ hetaJA}$	100	
Junction-to-Ambient – t = 5 s (Note 3)	$R_{ heta JA}$	77	°C/W
Junction-to-Ambient - Steady State (Note 4)	$R_{ hetaJA}$	185	

Surface-mounted on FR4 board using 1 in sq pad size (Cu area = 1.127 in sq [2 oz] including traces)
 Surface-mounted on FR4 board using the minimum recommended pad size (Cu area = 0.0775 in sq).

# ELECTRICAL CHARACTERISTICS (T = 25°C unless otherwise specified)

Parameter	Symbol	Test Cond	ition	Min	Тур	Max	Unit
OFF CHARACTERISTICS						•	
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS}$ = 0 V, I <sub>D</sub> = -250 µA		-20			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> /T <sub>J</sub>	ID = -250 μA, Reference 25°C			-13		mV/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>GS</sub> = 0 V, V <sub>DS</sub> = -20 V	$T_J = 25^{\circ}C$			-1.0	μΑ
			$T_J = 85^{\circ}C$			-5.0	1
Gate-to-Source Leakage Current	I <sub>GSS</sub>	$V_{DS}$ = 0 V, $V_{GS}$	= ±8.0 V			±0.1	μΑ
ON CHARACTERISTICS (Note 5)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}, I_D =$	-250 μA	-0.4		-1.0	V
Negative Threshold Temperature Coefficient	V <sub>GS(TH)</sub> /T <sub>J</sub>				3		mV/°C
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = -4.5 V, I <sub>E</sub>	<sub>)</sub> = -5.1 A		25	33	mΩ
		$V_{GS}$ = -2.5 V, I <sub>C</sub>	$V_{GS}$ = -2.5 V, I <sub>D</sub> = -4.5 A		32	40	
		$V_{GS} = -1.8$ V, $I_D = -2.5$ A			41	51	
Forward Transconductance	9 <sub>FS</sub>	$V_{DS} = -5.0 \text{ V}, \text{ I}_{D} = -5.1 \text{ A}$			22		S
CHARGES, CAPACITANCES AND GATE RES	ISTANCE						
Input Capacitance	C <sub>ISS</sub>			1901		pF	
Output Capacitance	C <sub>OSS</sub>	V <sub>GS</sub> = 0 V, f = 1 MHz, V <sub>DS</sub> = -10 V			274		
Reverse Transfer Capacitance	C <sub>RSS</sub>				175		
Total Gate Charge	Q <sub>G(TOT)</sub>	$V_{GS} = -4.5 \text{ V}, V_{DS} = -10 \text{ V};$ $I_D = -5.1 \text{ A}$			18	29	nC
Threshold Gate Charge	Q <sub>G(TH)</sub>				0.7		
Gate-to-Source Charge	$Q_{GS}$				2.4		
Gate-to-Drain Charge	Q <sub>GD</sub>				4.3		]
Gate Resistance	R <sub>G</sub>			7.6		Ω	
SWITCHING CHARACTERISTICS (Note 6)							
Turn-On Delay Time	t <sub>d(ON)</sub>	$V_{GS}$ = -4.5 V, $V_{DD}$ = -10 V, I <sub>D</sub> = -1.0 A, R <sub>G</sub> = 6.0 $\Omega$			9	19	ns
Rise Time	Tr				9	19	]
Turn–Off Delay Time	t <sub>d(OFF)</sub>				99	160	
Fall Time	T <sub>f</sub>				48	79	
DRAIN-SOURCE DIODE CHARACTERISTICS							
Forward Diode Voltage	V <sub>SD</sub>	$V_{GS} = 0 V,$	$T_J = 25^{\circ}C$		-0.7	-1.2	V
		$I_{\rm S} = -1.7 {\rm A}$ $T_{\rm J} = 125^{\circ}$			-0.6		]

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

t<sub>RR</sub>

 $\label{eq:VGS} \begin{array}{l} V_{GS} = 0 \ V \text{, } d_{IS}/d_t = 100 \ A/\mu \text{s} \text{,} \\ I_S = -1.7 \ A \end{array}$ 

37

60


ns

5. Pulse Test: pulse width  $\leq$  300 µs, duty cycle  $\leq$  2%


**Reverse Recovery Time** 

6. Switching characteristics are independent of operating junction temperatures

#### TYPICAL PERFORMANCE CURVES (T<sub>J</sub> = 25°C unless otherwise noted)



#### TYPICAL PERFORMANCE CURVES (T<sub>J</sub> = 25°C unless otherwise noted)



#### **ORDERING INFORMATION**

Device	Marking	Package	Shipping <sup>†</sup>	
NTGS3136PT1G	SD	TSOP-6	2000 / Tapa & Real	
NVGS3136PT1G*	VSD	(Pb-Free)	3000 / Tape & Reel	

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

\*NV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable.

#### TSOP-6 3.00x1.50x0.90, 0.95P **CASE 318G ISSUE W** DATE 26 FEB 2024 NDTES D DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2018. 1. CONTROLLING DIMENSION: MILLIMETERS. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIMUM 2. З. 6 5 4 LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL. MATERIAL. DIMENSIONS D AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.15 PER SIDE. DIMENSIONS D AND E1 ARE DETERMINED AT DATUM H. PIN 1 INDICATOR MUST BE LOCATED IN THE INDICATED ZONE Ē1 NOTE 5 1 3 MILLIMETERS H DIM MIN NΠΜ MAX e -2 GAUGE PLANE 0.90 1.00 1.10 А TOP VIEW A1 0.01 0.06 0.10 0.80 0.90 1.00 Α2 -A2 0.25 0.38 0.50 b SEATING PLANE Μ Ċ 0.10 0.18 0.26 С 0.05 C 3.00 DETAIL Z D 2.90 3.10 SCALE 3:1 F 2.50 A1-2.75 3.00 SIDE VIEW PLANE Ε1 1.30 1.50 1.70 0.85 0.95 1.05 е 0.20 0.40 DETAIL Z L 0.60 L2 0.25 BSC М 0° 10° 6X --0.60 END VIEW 6X -0.95 3.20 1 -0.95 PITCH RECOMMENDED MOUNTING FOOTPRINT

\*For additional information on our Pb-Free strategy and soldering details, please download th e EN Semiconductor Soldering and Mounting Techniques Reference manual, SELDERRM/D.

DUSEU


DOCUMENT NUMBER:	98ASB14888C Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.					
DESCRIPTION:	ON: TSOP-6 3.00x1.50x0.90, 0.95P P					
the right to make changes without furth purpose, nor does <b>onsemi</b> assume an	onsemi and ONSEMi. are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights of others.					

# onsemí.

#### TSOP-6 3.00x1.50x0.90, 0.95P CASE 318G ISSUE W

DATE 26 FEB 2024

#### GENERIC MARKING DIAGRAM\*



\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

STYLE 1: PIN 1. DRAIN 2. DRAIN 3. GATE 4. SOURCE 5. DRAIN 6. DRAIN	STYLE 2: PIN 1. EMITTER 2 2. BASE 1 3. COLLECTOR 1 4. EMITTER 1 5. BASE 2 6. COLLECTOR 2	STYLE 3: PIN 1. ENABLE 2. N/C 3. R BOOST 4. Vz 5. V in 6. V out	STYLE 4: PIN 1. N/C 2. V in 3. NOT USED 4. GROUND 5. ENABLE 6. LOAD	STYLE 5: PIN 1. EMITTER 2 2. BASE 2 3. COLLECTOR 1 4. EMITTER 1 5. BASE 1 6. COLLECTOR 2	STYLE 6: PIN 1. COLLECTOR 2. COLLECTOR 3. BASE 4. EMITTER 5. COLLECTOR 6. COLLECTOR
STYLE 7: PIN 1. COLLECTOR 2. COLLECTOR 3. BASE 4. N/C 5. COLLECTOR 6. EMITTER	STYLE 8: PIN 1. Vbus 2. D(in) 3. D(in)+ 4. D(out)+ 5. D(out) 6. GND	STYLE 9: PIN 1. LOW VOLTAGE GATE 2. DRAIN 3. SOURCE 4. DRAIN 5. DRAIN 6. HIGH VOLTAGE GATE	2. GND 3. D(OUT)– 4. D(IN)– 5. VBUS	STYLE 11: PIN 1. SOURCE 1 2. DRAIN 2 3. DRAIN 2 4. SOURCE 2 5. GATE 1 6. DRAIN 1/GATE 2	STYLE 12: PIN 1. I/O 2. GROUND 3. I/O 4. I/O 5. VCC 6. I/O
STYLE 13: PIN 1. GATE 1 2. SOURCE 2 3. GATE 2 4. DRAIN 2 5. SOURCE 1 6. DRAIN 1	STYLE 14: PIN 1. ANODE 2. SOURCE 3. GATE 4. CATHODE/DRAIN 5. CATHODE/DRAIN 6. CATHODE/DRAIN		LE 16: N 1. ANODE/CATHODE 2. BASE 3. EMITTER 4. COLLECTOR 5. ANODE 6. CATHODE	STYLE 17: PIN 1. EMITTER 2. BASE 3. ANODE/CATHODE 4. ANODE 5. CATHODE 6. COLLECTOR	

DOCUMENT NUMBER:	98ASB14888C	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.			
DESCRIPTION:	SCRIPTION: TSOP-6 3.00x1.50x0.90, 0.95P F				
onsemi and ONSEMi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.					

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent\_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

#### ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>