

MOSFET - Power, N-Channel, SUPERFET® III, **FAST**

650 V, 40 mΩ, 62 A

NTH4LN040N65S3H

Description

SUPERFET III MOSFET is onsemi's brand-new high voltage super-junction (SJ) MOSFET family that is utilizing charge balance technology for outstanding low on-resistance and lower gate charge performance. This advanced technology is tailored to minimize conduction loss, provides superior switching performance, and withstand extreme dv/dt rate.

Consequently, SUPERFET III MOSFET FAST series is very suitable for the various power systems for miniaturization and higher efficiency.


Features

- $700 \text{ V} @ \text{T}_{\text{J}} = 150^{\circ}\text{C}$
- Typ. $R_{DS(on)} = 32 \text{ m}\Omega$
- Ultra Low Gate Charge (Typ. Q_g = 132 nC)
- Low Effective Output Capacitance (Typ. Coss(eff.) = 1267 pF)
- 100% Avalanche Tested
- These Devices are Pb-Free and are RoHS Compliant


Applications

- Telecom / Server Power Supplies
- Industrial Power Supplies
- UPS / Solar

| V _{DSS} | R _{DS(ON)} MAX | I _D MAX |
|------------------|-------------------------|--------------------|
| 650 V | 40 mΩ @ 10 V | 62 A |



POWER MOSFET



MARKING DIAGRAM



Α YWW 77 T040N65S3H

= Assembly Site Code = Data Code (Year & Week) = Assembly Lot Code

= Specific Device Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^{\circ}C$, Unless otherwise noted)

| Symbol | Parameter | Value | Unit | |
|-----------------------------------|--|---------------------------------------|-------------|------|
| V_{DSS} | Drain to Source Voltage | | 650 | V |
| V_{GSS} | Gate to Source Voltage | - DC | ±30 | V |
| | | - AC (f > 1 Hz) | ±30 | |
| I _D | Drain Current | – Continuous (T _C = 25°C) | 62 | Α |
| | | - Continuous (T _C = 100°C) | 39 | |
| I _{DM} | Drain Current | - Pulsed (Note 1) | 174 | Α |
| E _{AS} | Single Pulsed Avalanche Energy (Note 2) | 675 | mJ | |
| I _{AS} | Avalanche Current (Note 2) | | 8.2 | Α |
| E _{AR} | Repetitive Avalanche Energy (Note 1) | | 3.79 | mJ |
| dv/dt | MOSFET dv/dt | 120 | V/ns | |
| | Peak Diode Recovery dv/dt (Note 3) | | 20 | |
| P_{D} | Power Dissipation | (T _C = 25°C) | 379 | W |
| | | - Derate Above 25°C | 3.03 | W/°C |
| T _J , T _{STG} | Operating and Storage Temperature Range | | -55 to +150 | °C |
| TL | Maximum Lead Temperature for Soldering, 1/8" | 260 | °C | |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- 1. Repetitive rating: pulse width limited by maximum junction temperature.
 2. $I_{AS}=8.2$ A, $R_{G}=25$ Ω , starting $T_{J}=25^{\circ}C$.
 3. $I_{SD}\leq 31$ A, di/dt ≤ 200 A/ μ s, $V_{DD}\leq 400$ V, starting $T_{J}=25^{\circ}C$.

THERMAL CHARACTERISTICS

| Symbol | Parameter | Value | Unit |
|----------------|---|-------|------|
| $R_{	heta JC}$ | Thermal Resistance, Junction to Case, Max. | 0.33 | °C/W |
| $R_{	heta JA}$ | Thermal Resistance, Junction to Ambient, Max. | 40 | |

PACKAGE MARKING AND ORDERING INFORMATION

| Part Number | Top Marking | Package | Packing Method | Reel Size | Tape Width | Quantity |
|-----------------|-------------|--------------------------|----------------|-----------|------------|----------|
| NTH4LN040N65S3H | T040N65S3H | TO-247 L4 Narrow Lead | Tube | N/A | N/A | 30 Units |


ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

| OFF CHARACTI BV _{DSS} ΔBV _{DSS} / ΔT _J | ERISTICS Drain to Source Breakdown Voltage | | | | | |
|---|--|--|-----|------|------|------|
| | Drain to Source Breakdown Voltage | | | | | |
| $\Delta BV_{DSS}/\Delta T_{J}$ | | V_{GS} = 0 V, I_D = 1 mA, T_J = 25°C | 650 | - | - | V |
| $\Delta BV_{DSS}/\Delta T_{J}$ | | $V_{GS} = 0 \text{ V}, I_D = 1 \text{ mA}, T_J = 150^{\circ}\text{C}$ | 700 | - | _ | V |
| | Breakdown Voltage Temperature Coefficient | I _D = 10 mA, Referenced to 25°C | - | 0.63 | - | V/°C |
| I _{DSS} | Zero Gate Voltage Drain Current | V _{DS} = 650 V, V _{GS} = 0 V | - | - | 3 | μΑ |
| | | V _{DS} = 520 V, T _C = 125°C | - | 2.6 | _ | |
| I _{GSS} | Gate to Body Leakage Current | $V_{GS} = \pm 30 \text{ V}, V_{DS} = 0 \text{ V}$ | - | - | ±100 | nA |
| ON CHARACTE | RISTICS | | | | | |
| V _{GS(th)} | Gate Threshold Voltage | $V_{GS} = V_{DS}, I_D = 6.8 \text{ mA}$ | 2.4 | - | 4.0 | V |
| R _{DS(on)} | Static Drain to Source On Resistance | V _{GS} = 10 V, I _D = 31 A | - | 32 | 40 | mΩ |
| 9FS | Forward Transconductance | V _{DS} = 20 V, I _D = 31 A | - | 85 | _ | S |
| DYNAMIC CHAF | RACTERISTICS | | | | | |
| C _{iss} | Input Capacitance | V 400 V V 070 I I | - | 6513 | _ | pF |
| C _{oss} | Output Capacitance | $V_{DS} = 400 \text{ V}, V_{GS} = 0 \text{ V}, f = 250 \text{ kHz}$ | - | 97 | _ | pF |
| C _{oss(eff.)} | Effective Output Capacitance | $V_{DS} = 0 \text{ V to } 400 \text{ V}, V_{GS} = 0 \text{ V}$ | - | 1267 | _ | pF |
| C _{oss(er.)} | Energy Related Output Capacitance | $V_{DS} = 0 \text{ V to } 400 \text{ V}, V_{GS} = 0 \text{ V}$ | - | 170 | _ | pF |
| Q _{g(tot)} | Total Gate Charge at 10 V | | - | 132 | _ | nC |
| Q_{gs} | Gate to Source Gate Charge | $V_{DS} = 400 \text{ V}, I_D = 31 \text{ A}, V_{GS} = 10 \text{ V}$ (Note 4) | - | 36 | _ | nC |
| Q_{gd} | Gate to Drain "Miller" Charge | (, | _ | 34 | _ | nC |
| ESR | Equivalent Series Resistance | f = 1 MHz | - | 0.7 | _ | Ω |
| SWITCHING CH | ARACTERISTICS | | | | | |
| t _{d(on)} | Turn-On Delay Time | | - | 39 | _ | ns |
| t _r | Turn-On Rise Time | $V_{DD} = 400 \text{ V}, I_D = 31 \text{ A},$ | _ | 9 | _ | ns |
| t _{d(off)} | Turn-Off Delay Time | $V_{GS} = 10 \text{ V, } R_g = 2.2 \Omega$ (Note 4) | - | 95 | _ | ns |
| t _f | Turn-Off Fall Time | | - | 2.8 | _ | ns |
| SOURCE-DRAIN | N DIODE CHARACTERISTICS | | | | | |
| I _S | Maximum Continuous Source to Drain Diode Forward Current | | | _ | 62 | Α |
| I _{SM} | Maximum Pulsed Source to Drain Diode Forward Current | | - | _ | 174 | Α |
| V _{SD} | Source to Drain Diode Forward Voltage | V _{GS} = 0 V, I _{SD} = 31 A | - | - | 1.2 | V |
| t _{rr} | Reverse Recovery Time | V _{GS} = 0 V, I _{SD} = 31 A, | - | 503 | - | ns |
| Q _{rr} | Reverse Recovery Charge | $dI_F/dt = 100 A/\mu s$ | - | 11.4 | - | μС |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Essentially independent of operating temperature typical characteristics.

TYPICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)



www.onsemi.com

Figure 6. Gate Charge Characteristics

Figure 5. Capacitance Characteristics

TYPICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)




Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 9. Maximum Safe Operating Area




Figure 11. E_{OSS} vs. Drain to Source Voltage






Figure 10. Maximum Drain Current vs. Case Temperature

TYPICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)




Figure 12. Transient Thermal Impedance




Figure 13. Gate Charge Test Circuit & Waveform




Figure 14. Resistive Switching Test Circuit & Waveforms




Figure 15. Unclamped Inductive Switching Test Circuit & Waveforms





Figure 16. Peak Diode Recovery dv/dt Test Circuit & Waveforms

SUPERFET and FRFET are a registered trademarks of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.


PACKAGE DIMENSIONS

TO-247 4-LEAD, THIN LEADS CASE 340CW



NOTES:

- A. NO INDUSTRY STANDARD APPLIES TO THIS PACKAGE.
- B. DIMENSIONS ARE EXCLUSIVE OF
 BURRS,MOLD FLASH AND TIE BAR
 EXTRUSIONS.
 C. ALL DIMENSIONS ARE IN MILLIMETERS.



| DIM | MILLIMETERS | | | | |
|-----|-------------|-------|-------|--|--|
| DIM | MIN | NOM | MAX | | |
| Α | 4.80 | 5.00 | 5.20 | | |
| A1 | 2.10 | 2.40 | 2.70 | | |
| A2 | 1.80 | 2.00 | 2.20 | | |
| b | 0.57 | 0.70 | 0.83 | | |
| b2 | 1.07 | 1.20 | 1.33 | | |
| b3 | 1.20 | 1.40 | 1.60 | | |
| b4 | 2.02 | 2.22 | 2.42 | | |
| С | 0.50 | 0.60 | 0.70 | | |
| D | 22.34 | 22.54 | 22.74 | | |
| D1 | 16.00 | 16.30 | 16.50 | | |
| D2 | 0.97 | 1.17 | 1.37 | | |
| е | | 2.54 | | | |
| e1 | | 2.79 | | | |
| e2 | | 5.08 | | | |
| E | 15.40 | 15.60 | 15.80 | | |
| E1 | 12.80 | 13.00 | 13.20 | | |
| E2 | 4.80 | 5.00 | 5.20 | | |
| L | 18.12 | 18.42 | 18.72 | | |
| L1 | 2.42 | 2.62 | 2.82 | | |
| Øp | 3.40 | 3.60 | 3.80 | | |
| ØP1 | 6.60 | 6.80 | 7.00 | | |
| Q | 5.97 | 6.17 | 6.37 | | |
| S | 5.97 | 6.17 | 6.37 | | |

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada

Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative