ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

MOSFET - N-Channel Shielded Gate PowerTrench[®]

150 V, 31 mΩ, 31 A

NTMFS034N15MC

Features

- Small Footprint (5 x 6 mm) for Compact Design
- Low R_{DS(on)} to Minimize Conduction Losses
- Low QG and Capacitance to Minimize Driver Losses
- 100% UIL Tested
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

Typical Applications

- Synchronous Rectification
- AC-DC and DC-DC Power Supplies
- AC-DC Adapters (USB PD) SR
- Load Switch

MAXIMUM RATINGS (T_J = 25° C unless otherwise noted)

Parameter		Symbol	Value	Unit	
Drain-to-Source Voltage		V _{DSS}	150	V	
Gate-to-Source Voltage		V _{GS}	±20	V	
Continuous Drain Current $R_{\theta JC}$ (Note 2)	Steady	T _C = 25°C	۱ _D	31	A
Power Dissipation $R_{\theta JC}$ (Note 2)	State		P _D	62.5	W
Continuous Drain Current R _{θJA} (Notes 1, 2)	Steady State	T _A = 25°C	Ι _D	6.1	A
Power Dissipation $R_{\theta JA}$ (Notes 1, 2)	Sidle		P _D	2.5	W
Pulsed Drain Current	$T_{\rm C} = 25^{\circ}$	C, t _p = 100 μs	I _{DM}	131	А
Operating Junction and Storage Temperature Range			T _J , T _{stg}	–55 to +150	°C
Single Pulse Drain-to-Source Avalanche Energy ($I_L = 6 A_{pk}, L = 3 mH$)			E _{AS}	54	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			ΤL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Surface-mounted on FR4 board using a 1 in², 2 oz. Cu pad.


The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.



ON Semiconductor®


www.onsemi.com

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
150 V	31 mΩ @ 10 V	31 A



N-CHANNEL MOSFET





ORDERING INFORMATION

Device	Package	Shipping [†]		
NTMFS034N15MC	Power 56	3000 / Tape		
(Pb-Free/Halogen Free)	(PQFN8)	& Reel		

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit	
Junction-to-Case - Steady State (Note 2)	$R_{ extsf{ heta}JC}$	2.0	°C/W	
Junction-to-Ambient - Steady State (Notes 1, 2)	$R_{ hetaJA}$	50		


ELECTRICAL CHARACTERISTICS (T_J = 25° C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V_{GS} = 0 V, I _D = 250 μ A		150			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} / T _J	$I_D = 250 \ \mu A$, ref to $25^{\circ}C$			86		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	V _{GS} = 0 V, V _{DS} = 120 V	T _J = 25°C			1.0	μΑ
Gate-to-Source Leakage Current	I _{GSS}	V_{DS} = 0 V, V_{GS} = ±20 V				±100	nA
ON CHARACTERISTICS							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D = 7$	70 μA	2.5		4.5	V
Negative Threshold Temperature Coefficient	V _{GS(TH)} /T _J	$I_D = 70 \ \mu A$, ref to	25°C		-7.7		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V, I _D =	13 A		25	31	mΩ
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 8 V, I _D = 6 A			27	36.5	mΩ
Forward Transconductance	9 _{FS}	V _{DS} = 10 V, I _D = 13 A			27		S
CHARGES, CAPACITANCES & GATE RESIS	TANCE						
Input Capacitance	C _{ISS}	V _{GS} = 0 V, f = 1 MHz, V _{DS} = 75 V			905		
Output Capacitance	C _{OSS}				270		pF
Reverse Transfer Capacitance	C _{RSS}				5		
Gate-Resistance	R _G				0.6	1.2	Ω
Total Gate Charge	Q _{G(TOT)}				12		
Threshold Gate Charge	Q _{G(TH)}				3.1		
Gate-to-Source Charge	Q _{GS}	V_{GS} = 10 V, V_{DS} = 75 V; I_{D} = 13 A			4.8		nC
Gate-to-Drain Charge	Q _{GD}				1.8		
Plateau Voltage	V _{GP}				5.4		V
Output Charge	Q _{OSS}	V _{DD} = 75 V, V _{GS} = 0 V			32		nC
SWITCHING CHARACTERISTICS (Note 3)							
Turn-On Delay Time	t _{d(ON)}				12		
Rise Time	t _r	V_{GS} = 10 V, V_{DD} = 75 V, I_{D} = 13 A, R_{G} = 6 Ω			2.2		ns
Turn-Off Delay Time	t _{d(OFF)}				14		
Fall Time	t _f				2.5		
DRAIN-SOURCE DIODE CHARACTERISTIC	S	-			-	-	-
Forward Diode Voltage	V _{SD}	$V_{GS} = 0 \text{ V}, \text{ I}_{S} = 13 \text{ A}$	$T_J = 25^{\circ}C$		0.87	1.2	V
Reverse Recovery Time	t _{RR}	V _{GS} = 0 V, V _{DD} = 75 V dI _S /dt = 300 A/μs, I _S = 13 A			41		ns
Reverse Recovery Charge	Q _{RR}				126		nC
Reverse Recovery Time	t _{RR}	V_{GS} = 0 V, V_{DD} = 75 V dI _S /dt = 1000 A/µs, I _S = 13 A			22		ns
Reverse Recovery Charge	Q _{RR}				164		nC


Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

NOTES:

- Switching characteristics are independent of operating junction temperatures.
 R_{θJA} is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 × 1.5 in. board of FR-4 material. R_{θCA} is determined by the user's board design.




a) 50°C/W when mounted on a 1 in² pad of 2 oz copper.




b) $125^{\circ}C/W$ when mounted on a minimum pad of 2 oz copper.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS





Figure 13. Transient Thermal Impedance

PACKAGE DIMENSIONS

PQFN8 5X6, 1.27P CASE 483AE ISSUE A



ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor hy such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, a

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 **Europe, Middle East and Africa Technical Support:** Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative