# **ON Semiconductor**

## Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

# **MOSFET** - Power, Single N-Channel, D<sup>2</sup>PAK7

60 V, 1.55 mΩ, 267 A

# NTBGS1D5N06C

#### **Features**

- Low R<sub>DS(on)</sub> to Minimize Conduction Losses
- Low Q<sub>G</sub> and Capacitance to Minimize Driver Losses
- Lowers Switching Noise/EMI
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

#### **Typical Applications**

- Power Tools, Battery Operated Vacuums
- UAV/Drones, Material Handling
- BMS/Storage, Home Automation

#### MAXIMUM RATINGS (T<sub>J</sub> = 25°C unless otherwise noted)

Parameter		Symbol	Value	Unit	
Drain-to-Source Voltage		$V_{DSS}$	60	V	
Gate-to-Source Voltage	Gate-to-Source Voltage		V <sub>GS</sub>	±20	٧
Continuous Drain Current R <sub>θJC</sub> (Note 2)	Steady T 0500	I <sub>D</sub>	267	Α	
Power Dissipation $R_{\theta JC}$ (Note 2)	State T <sub>C</sub> = 25°C		P <sub>D</sub>	211	W
Continuous Drain Current $R_{\theta JA}$ (Notes 1, 2)	Steady State T <sub>A</sub> = 25°C	I <sub>D</sub>	35	Α	
Power Dissipation $R_{\theta JA}$ (Notes 1, 2)	State 1A - 23 0		P <sub>D</sub>	3.7	W
Pulsed Drain Current	$T_A = 25^{\circ}C, t_p = 100 \mu s$		I <sub>DM</sub>	1133	Α
Operating Junction and Storage Temperature Range		T <sub>J</sub> , T <sub>stg</sub>	-55 to +175	°C	
Source Current (Body Diode)		I <sub>S</sub>	175	Α	
Single Pulse Drain-to-Source Avalanche Energy (I <sub>L</sub> = 33.2 A <sub>pk</sub> , L = 1 mH)		E <sub>AS</sub>	550	mJ	
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)		TL	260	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


- 1. Surface-mounted on FR4 board using a 1 in<sup>2</sup>, 1 oz. Cu pad.
- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.



#### ON Semiconductor®

#### www.onsemi.com

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX
60 V	1.55 mΩ @ 12 V	267 A
00 V	1.62 mΩ @ 10 V	201 A



**N-CHANNEL MOSFET** 



#### D<sup>2</sup>PAK7 CASE 221BP

#### MARKING DIAGRAM

BGS1D5 N06C AYWWG

BGS1D5N06C = Specific Device Code

A = Assembly Location

Y = Year WW = Work Week G = Pb-Free Package

#### **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
NTBGS1D5N06C	D <sup>2</sup> PAK7 (Pb-Free)	800 / Tape & Reel

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State (Note 2)	$R_{ hetaJC}$	0.71	°C/W
Junction-to-Ambient - Steady State (Note 1)	$R_{ hetaJA}$	40	


#### **ELECTRICAL CHARACTERISTICS** (T<sub>1</sub> = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		60			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> /	I <sub>D</sub> = 318 μA, ref to 25°C			8		mV/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{GS} = 0 \text{ V},   T_{J} = 25^{\circ}\text{C}$				10	μΑ
		$V_{DS} = 60 \text{ V}$ $T_{J} = 60 \text{ V}$	T <sub>J</sub> = 125°C			100	μΑ
Gate-to-Source Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> = 0 V, V <sub>GS</sub> = 20 V				100	nA
ON CHARACTERISTICS (Note 3)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}, I_D = V_{DS}$	= 318 μΑ	2.0	3.0	4.0	V
Negative Threshold Temperature Coefficient	V <sub>GS(TH)</sub> /T <sub>J</sub>	I <sub>D</sub> = 318 μA, re	f to 25°C		-9		mV/°C
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 12 V, I <sub>D</sub> = 64 A			1.23	1.55	
		V <sub>GS</sub> = 10 V, I <sub>D</sub>	<sub>)</sub> = 32 A		1.29 1.62 mΩ		
Gate-Resistance	$R_{G}$	T <sub>A</sub> = 25°C			1.0		Ω
CHARGES, CAPACITANCES & GATE RESIS	TANCE						
Input Capacitance	C <sub>ISS</sub>	V <sub>GS</sub> = 0 V, V <sub>DS</sub> = 30 V, f = 1 MHz			6250		pF
Output Capacitance	C <sub>OSS</sub>				3060		
Reverse Transfer Capacitance	C <sub>RSS</sub>				66		
Total Gate Charge	Q <sub>G(TOT)</sub>	$V_{GS} = 10 \text{ V}, V_{DS} = 30 \text{ V}; I_D = 64 \text{ A}$ $V_{GS} = 0 \text{ V}, V_{DS} = 50 \text{ V}$			78.6		
Threshold Gate Charge	Q <sub>G(TH)</sub>				16.6		nC
Gate-to-Source Charge	$Q_{GS}$				27.3		
Gate-to-Drain Charge	$Q_{GD}$				12.2		
Output Charge	Q <sub>OSS</sub>				150.80		
SWITCHING CHARACTERISTICS (Note 4)							
Turn-On Delay Time	t <sub>d(ON)</sub>				27		
Rise Time	t <sub>r</sub>	$V_{GS}$ = 10 V, $V_{DS}$ = 30 V, $I_{D}$ = 64 A, $R_{G}$ = 6 $\Omega$			16.3		- ns
Turn-Off Delay Time	t <sub>d(OFF)</sub>				58.6		
Fall Time	t <sub>f</sub>				23.3		
DRAIN-SOURCE DIODE CHARACTERISTIC	s						-
Forward Diode Voltage	$V_{SD}$	V <sub>GS</sub> = 0 V,	T <sub>J</sub> = 25°C		0.82	1.2	V
		I <sub>S</sub> = 64 A	T <sub>J</sub> = 125°C		0.69		
Reverse Recovery Time	t <sub>RR</sub>	$V_{GS} = 0 \text{ V, } dI_S/dt = 100 \text{ A/}\mu\text{s,}$ $I_S = 32 \text{ A}$			81.7		ns
Reverse Recovery Charge	Q <sub>RR</sub>				111		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 3. Pulse Test: pulse width  $\leq$  300  $\mu$ s, duty cycle  $\leq$  2%.

<sup>4.</sup> Switching characteristics are independent of operating junction temperatures.

#### **TYPICAL CHARACTERISTICS**



#### **TYPICAL CHARACTERISTICS**




Figure 7. Capacitance Variation

Figure 8. Gate-to-Source vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance

Figure 10. Diode Forward Voltage vs. Current

0.9

1.0




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Drain Current vs. Time in **Avalanche** 

#### **TYPICAL CHARACTERISTICS**





Figure 13. Transient Thermal Impedance


#### **PACKAGE DIMENSIONS**

#### D2PAK7 (TO-263-7LD) 15.4x9.9x4.5 CASE 221BP



- A. PACKAGE CONFORMS TO JEDEC TO-263 VARIATION CB EXCEPT WHERE NOTED. B. ALL DIMENSIONS ARE IN MILLIMETERS.
- OUT OF JEDEC STANDARD VALUE.
  D. DIMENSION AND TOLERANCE AS PER ASME Y14.5-2009.
  E. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.
  F. LAND PATTERN RECOMMENDATION PER IPC. TO127P1524X465-8N.

DIM	MILLIMETERS			
DIM	MIN	NOM	MAX	
Α	4.30	4.50	4.70	
A1	0.00	0.10	0.20	
b2	0.60	0.70	0.80	
b	0.50	0.60	0.70	
С	0.40	0.50	0.60	
c2	1.20	1.30	1.40	
D	9.00	9.20	9.40	
D1	7.30	7.80	8.20	
Е	9.70	9.90	10.20	
E1	7.15	8.05	8.55	
е	~	1.27	~	
Н	15.10	15.40	15.70	
L	2.44	2.64	2.84	
L1	1.00	1.20	1.40	
L3	~	0.25	~	
aaa	~	~	0.25	



2.60 2.20 A1
SEATING PLANE
GAUGE PLANE
5.20 4.80 R0.50
DETAIL A SCALE 2:1

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability. arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com TECHNICAL SUPPORT

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

ON Semiconductor Website: www.onsemi.com

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative