# **ON Semiconductor**

# Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

# **Power MOSFET**

# 16 V, 34.5 A, Single N-Channel, DPAK/IPAK

#### **Features**

- Low R<sub>DS(on)</sub> to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- Optimized Gate Charge to Minimize Switching Losses
- Three Package Variations for Design Flexibility
- These are Pb-Free Devices

### **Applications**

- DC-DC Converters
- High Side Switching

## **MAXIMUM RATINGS** ( $T_J = 25^{\circ}C$ unless otherwise stated)

Para	Parameter					
Drain-to-Source Vol	tage		$V_{DSS}$	16	V	
Gate-to-Source Volt	tage		$V_{GS}$	±16	V	
Continuous Drain		T <sub>A</sub> = 25°C	Ι <sub>D</sub>	10.8	Α	
Current R <sub>θJA</sub> (Note 1)		T <sub>A</sub> = 85°C		8.4		
Power Dissipation $R_{\theta JA}$ (Note 1)		T <sub>A</sub> = 25°C	P <sub>D</sub>	2.5	W	
Continuous Drain		T <sub>A</sub> = 25°C	I <sub>D</sub>	7.6	Α	
Current R <sub>θJA</sub> (Note 2)	Steady State	T <sub>A</sub> = 85°C		5.9		
Power Dissipation R <sub>θJA</sub> (Note 2)	State	T <sub>A</sub> = 25°C	P <sub>D</sub>	1.2	W	
Continuous Drain		T <sub>C</sub> = 25°C	I <sub>D</sub>	34.5	Α	
Current R <sub>θJC</sub> (Note 1)		T <sub>C</sub> = 85°C		26.8		
Power Dissipation $R_{\theta JC}$ (Note 1)		T <sub>C</sub> = 25°C	P <sub>D</sub>	25.9	W	
Pulsed Drain Current	t <sub>p</sub> =10μs	T <sub>A</sub> = 25°C	I <sub>DM</sub>	78	Α	
Current Limited by P	ackage	T <sub>A</sub> = 25°C	I <sub>DmaxPkg</sub>	22	Α	
Operating Junction a Temperature	ind Storage		T <sub>J</sub> , T <sub>STG</sub>	-55 to +175	°C	
Source Current (Bod	y Diode)		IS	21.6	Α	
Drain to Source dV/c	dV/dt	6	V/ns			
Single Pulse Drain-to-Source Avalanche Energy ( $T_J$ = 25°C, $V_{DD}$ = 50 V, $V_{GS}$ = 10 V, $I_L$ = 10 $A_{pk}$ , $L$ = 0.3 mH, $R_G$ = 25 $\Omega$ )			EAS	15	mJ	
Lead Temperature for (1/8" from case for 1		Purposes	TL	260	°C	


Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.



## ON Semiconductor®

#### http://onsemi.com

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX
16 V	13.9 mΩ @ 10 V	34.5 A
10 7	29 mΩ @ 4.5 V	54.5 K










CASE 369AA **DPAK** (Bent Lead) STYLE 2

CASE 369AC 3 IPAK (Straight Lead) (Straight Lead

**CASE 369D IPAK** DPAK)

#### **MARKING DIAGRAMS & PIN ASSIGNMENTS**



= Year WW = Work Week 3817N = Device Code = Pb-Free Package

#### **ORDERING INFORMATION**

See detailed ordering and shipping information in the package dimensions section on page 6 of this data sheet.

#### THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case (Drain)	$R_{ heta JC}$	5.8	°C/W
Junction-to-TAB (Drain)	$R_{\theta JC-TAB}$	4.5	
Junction-to-Ambient - Steady State (Note 1)	$R_{\theta JA}$	59	
Junction-to-Ambient – Steady State (Note 2)	$R_{\theta JA}$	121	

- Surface-mounted on FR4 board using 1 sq-in pad, 1 oz Cu.
   Surface-mounted on FR4 board using the minimum recommended pad size.

## **ELECTRICAL CHARACTERISTICS** (T<sub>1</sub> = 25°C unless otherwise specified)

Parameter	Symbol	Test Cond	lition	Min	Тур	Max	Unit
OFF CHARACTERISTICS			_				
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS} = 0 \text{ V, } I_D = 250 \mu\text{A}$		16			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> /				15.5		mV/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>GS</sub> = 0 V, T <sub>J</sub> = 25°C				1.0	
		V <sub>DS</sub> = 16 V	T <sub>J</sub> = 125°C			10	μΑ
Gate-to-Source Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> = 0 V, V <sub>GS</sub>	<sub>S</sub> = ±16 V			±100	nA
ON CHARACTERISTICS (Note 3)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}, I_{D}$	= 250 μΑ	1.5		2.5	V
Negative Threshold Temperature Coefficient	V <sub>GS(TH)</sub> /T <sub>J</sub>				5.1		mV/°C
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V I <sub>D</sub> = 15 A			12.8	13.9	0
		V <sub>GS</sub> = 4.5 V	I <sub>D</sub> = 15 A		19.2	29	9 mΩ
Forward Transconductance	9FS	V <sub>DS</sub> = 1.5 V, I <sub>D</sub> = 15 A			28		S
CHARGES AND CAPACITANCES							
Input Capacitance	C <sub>ISS</sub>	V <sub>GS</sub> = 0 V, f = 1.0 MHz, V <sub>DS</sub> = 12 V			702		pF
Output Capacitance	C <sub>OSS</sub>				257		
Reverse Transfer Capacitance	C <sub>RSS</sub>				168		1
Total Gate Charge	Q <sub>G(TOT)</sub>				7.0	10.5	
Threshold Gate Charge	Q <sub>G(TH)</sub>	\/ 45\/\/	10 \/ \ 15 \		0.6		nC
Gate-to-Source Charge	Q <sub>GS</sub>	$V_{GS}$ = 4.5 V, $V_{DS}$ =	12 V, I <sub>D</sub> = 15 A		2.5		
Gate-to-Drain Charge	$Q_{GD}$				3.5		
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 10 V, V <sub>DS</sub> =	12 V, I <sub>D</sub> = 15 A		13.5		nC
SWITCHING CHARACTERISTICS (Note	4)						
Turn-On Delay Time	t <sub>d(ON)</sub>				12		
Rise Time	t <sub>r</sub>	V <sub>GS</sub> = 4.5 V, V <sub>I</sub>	ns = 12 V,		50		1
Turn-Off Delay Time	t <sub>d(OFF)</sub>	$V_{GS} = 4.5 \text{ V}, V_{DS} = 12 \text{ V},$ $I_{D} = 15 \text{ A}, R_{G} = 3.0 \Omega$			12		ns
Fall Time	t <sub>f</sub>				4.6		1
Turn-On Delay Time	t <sub>d(ON)</sub>				8.0		
Rise Time	t <sub>r</sub>	V <sub>GS</sub> = 10 V, V <sub>E</sub>	ns = 12 V,		47		1
Turn-Off Delay Time	t <sub>d(OFF)</sub>	$I_{\rm D} = 15  {\rm A, R_{\rm G}}$	= 3.0 Ω		20		ns
Fall Time	t <sub>f</sub>				10		7


- 3. Pulse Test: pulse width  $\leq$  300  $\mu$ s, duty cycle  $\leq$  2%.
- 4. Switching characteristics are independent of operating junction temperatures.5. Assume standoff of 110 mm

# **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub> = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
DRAIN-SOURCE DIODE CHARACTER	RISTICS			•	•	•	
Forward Diode Voltage	V <sub>SD</sub>	V <sub>GS</sub> = 0 V,	T <sub>J</sub> = 25°C		0.96	1.1	\ /
		$V_{GS} = 0 V,$ $I_{S} = 15 A$	T <sub>J</sub> = 125°C		0.86		V
Reverse Recovery Time	t <sub>RR</sub>	V <sub>GS</sub> = 0 V, dIS/dt = 100 A/μs, I <sub>S</sub> = 15 A			11		ns
Charge Time	ta				5.4		
Discharge Time	t <sub>b</sub>				5.6		
Reverse Recovery Charge	Q <sub>RR</sub>				2.8		nC
PACKAGE PARASITIC VALUES							
Source Inductance	L <sub>S</sub>				2.49		nH
Drain Inductance, DPAK	L <sub>D</sub>	T <sub>A</sub> = 25°C			0.0164		
Drain Inductance, IPAK (Note 5)	L <sub>D</sub>				1.88		
Gate Inductance	L <sub>G</sub>				3.46		
Gate Resistance	R <sub>G</sub>				1.0		Ω

<sup>3.</sup> Pulse Test: pulse width  $\leq$  300  $\mu$ s, duty cycle  $\leq$  2%. 4. Switching characteristics are independent of operating junction temperatures. 5. Assume standoff of 110 mm


#### **TYPICAL PERFORMANCE CURVES**



 $V_{DS} \ge 10 \text{ V}$ 35 DRAIN CURRENT (AMPS) 30 25 20 15  $T_J = 125^{\circ}C$  $T_J = 25^{\circ}C$ ڡٞ 5  $T_J = -55^{\circ}C$ 01 3 2 5 V<sub>GS</sub>, GATE-TO-SOURCE VOLTAGE (VOLTS)

Figure 1. On-Region Characteristics

Figure 2. Transfer Characteristics







Figure 3. On-Resistance vs. Gate-to-Source Voltage

Figure 4. On-Resistance vs. Drain Current and Gate Voltage






Figure 5. On–Resistance Variation with Temperature

Figure 6. Drain-to-Source Leakage Current vs. Drain Voltage

#### TYPICAL PERFORMANCE CURVES




Figure 7. Capacitance Variation




Figure 8. Gate-To-Source and Drain-To-Source Voltage vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Avalanche Energy vs. Starting Junction Temperature

### **ORDERING INFORMATION**


Device	Package	Shipping <sup>†</sup>
NTD3817NT4G	DPAK (Pb-Free)	2500 / Tape & Reel
NTD3817N-1G	IPAK (Pb-Free)	75 Units / Rail
NTD3817N-35G	IPAK Trimmed Lead (3.5 ± 0.15 mm) (Pb-Free)	75 Units / Rail

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

### **PACKAGE DIMENSIONS**

## **DPAK (SINGLE GAUGE)**

CASE 369AA-01 **ISSUE A** 




- NOTES:
  1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
  2. CONTROLLING DIMENSION: INCH.

	INC	HES	MILLIM	IETERS
DIM	MIN	MAX	MIN	MAX
Α	0.235	0.245	5.97	6.22
В	0.250	0.265	6.35	6.73
С	0.086	0.094	2.19	2.38
D	0.025	0.035	0.63	0.89
Е	0.018	0.024	0.46	0.61
F	0.030	0.045	0.77	1.14
Н	0.386	0.410	9.80	10.40
J	0.018	0.023	0.46	0.58
L	0.090	BSC	2.29	BSC
R	0.180	0.215	4.57	5.45
S	0.024	0.040	0.60	1.01
U	0.020		0.51	
٧	0.035	0.050	0.89	1.27
Z	0.155		3.93	

STYLE 2: PIN 1. GATE 2. DRAIN 3. SOURCE 4. DRAIN

### **SOLDERING FOOTPRINT\***




\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### PACKAGE DIMENSIONS

#### 3 IPAK, STRAIGHT LEAD

CASE 369AC-01 ISSUE O




#### NOTES:


- 1.. DIMENSIONING AND TOLERANCING
- PER ANSI Y14.5M, 1982. CONTROLLING DIMENSION: INCH.
- SEATING PLANE IS ON TOP OF DAMBAR POSITION.
- DIMENSION A DOES NOT INCLUDE DAMBAR POSITION OR MOLD GATE.

	INCHES		MILLIN	IETERS
DIM	MIN	MAX	MIN	MAX
Α	0.235	0.245	5.97	6.22
В	0.250	0.265	6.35	6.73
C	0.086	0.094	2.19	2.38
D	0.027	0.035	0.69	0.88
Е	0.018	0.023	0.46	0.58
F	0.037	0.043	0.94	1.09
G	0.090	0.090 BSC		BSC
Н	0.034	0.040	0.87	1.01
7	0.018	0.023	0.46	0.58
K	0.134	0.142	3.40	3.60
R	0.180	0.215	4.57	5.46
٧	0.035	0.050	0.89	1.27
w	0.000	0.010	0.000	0.25

#### **IPAK (STRAIGHT LEAD DPAK)**

CASE 369D-01 **ISSUE B** 





- NOTES:
  1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. CONTROLLING DIMENSION: INCH.

	INC	HES	MILLIMETER		
DIM	MIN	MAX	MIN	MAX	
Α	0.235	0.245	5.97	6.35	
В	0.250	0.265	6.35	6.73	
С	0.086	0.094	2.19	2.38	
D	0.027	0.035	0.69	0.88	
E	0.018	0.023	0.46	0.58	
F	0.037	0.045	0.94	1.14	
G	0.090	BSC	2.29	BSC	
Н	0.034	0.040	0.87	1.01	
J	0.018	0.023	0.46	0.58	
K	0.350	0.380	8.89	9.65	
R	0.180	0.215	4.45	5.45	
S	0.025	0.040	0.63	1.01	
V	0.035	0.050	0.89	1.27	
Z	0.155		3.93		

STYLE 2:

PIN 1. GATE

- DRAIN
   SOURCE
- DRAIN

ON Semiconductor and un are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice on semiconductor and are registered raderians of semiconductor Components industries, Ite (SciLLC) solicit esserves the right to make changes without further holice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada

Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center

Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative