MOSFET – Power, Single, N-Channel, DPAK/IPAK 25 V, 73 A

Features

- Trench Technology
- Low R_{DS(on)} to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- Optimized Gate Charge to Minimize Switching Losses
- These are Pb-Free Devices

Applications

- VCORE Applications
- DC-DC Converters
- High/Low Side Switching

MAXIMUM RATINGS (T_J = 25° C unless otherwise stated)

Para	ameter		Symbol	Value	Unit
Drain-to-Source Vo	tage		V _{DSS}	25	V
Gate-to-Source Voltage			V _{GS}	±20	V
Continuous Drain		$T_A = 25^{\circ}C$	۱ _D	14	А
Current R _{0JA} (Note 1)		T _A = 85°C		10.9	
Power Dissipation $R_{\theta JA}$ (Note 1)		T _A = 25°C	PD	2.0	W
Continuous Drain		$T_A = 25^{\circ}C$	ID	11.2	А
Current R _{θJA} (Note 2)	Steady	T _A = 85°C		8.7	
Power Dissipation $R_{\theta JA}$ (Note 2)	State	T _A = 25°C	P _D	1.3	W
Continuous Drain		T _C = 25°C	۱ _D	73	A
Current R _{θJC} (Note 1)		T _C = 85°C		56	
Power Dissipation $R_{\theta JC}$ (Note 1)		T _C = 25°C	P _D	54.5	W
Pulsed Drain Current	t _p =10μs	T _A = 25°C	I _{DM}	146	A
Current Limited by P	ackage	T _A = 25°C	I _{DmaxPkg}	45	А
Operating Junction and Storage Temperature			T _J , T _{STG}	–55 to +175	°C
Source Current (Body Diode)			۱ _S	45	А
Drain to Source dV/dt			dV/dt	6	V/ns
$ \begin{array}{l} \mbox{Single Pulse Drain-to-Source Avalanche} \\ \mbox{Energy } (T_J = 25^\circ C, V_{DD} = 50 \ V, V_{GS} = 10 \ V, \\ \mbox{I}_L = 15 \ A_{pk}, \ L = 1.0 \ mH, \ R_G = 25 \ \Omega) \end{array} $			EAS	112.5	mJ
Lead Temperature for (1/8" from case for 1		Purposes	ΤL	260	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.




ON Semiconductor®


http://onsemi.com

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
25 V	$6.2 \text{ m}\Omega @ 10 \text{ V}$	73 A
25 V	9.3 mΩ @ 4.5 V	73A





MARKING DIAGRAMS & PIN ASSIGNMENTS



* The Assembly Location code (A) is front side optional. In cases where the Assembly Location is stamped in the package, the front side assembly code may be blank.

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 6 of this data sheet.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case (Drain)	$R_{\theta JC}$	2.75	°C/W
Junction-to-TAB (Drain)	$R_{\thetaJC-TAB}$	3.5	
Junction-to-Ambient - Steady State (Note 1)	$R_{\theta JA}$	73.5	
Junction-to-Ambient - Steady State (Note 2)	$R_{ hetaJA}$	116	

Surface-mounted on FR4 board using 1 sq-in pad, 1 oz Cu.
 Surface-mounted on FR4 board using the minimum recommended pad size.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Cond	lition	Min	Тур	Max	Unit
OFF CHARACTERISTICS						-	-
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D =	= 250 μA	25			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} / T _J				22		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 V,$				1.0	•
		V _{DS} = 20 V	T _J = 125°C			10	μΑ
Gate-to-Source Leakage Current	I _{GSS}	$V_{DS} = 0 V, V_{GS}$	_S = ±20 V			±100	nA
ON CHARACTERISTICS (Note 3)							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_{D}$	= 250 μA	1.45		2.5	V
Negative Threshold Temperature Coefficient	V _{GS(TH)} /T _J				5.3		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 30 A		5.2	6.2	
		V _{GS} = 4.5 V	I _D = 30 A		7.3	9.3	mΩ
Forward Transconductance	9 FS	V _{DS} = 1.5 V, I _D = 15 A			55		S
CHARGES AND CAPACITANCES							
Input Capacitance	C _{ISS}				1563		
Output Capacitance	C _{OSS}	V _{GS} = 0 V, f = 1.0 M	Hz, V _{DS} = 12 V		405		pF
Reverse Transfer Capacitance	C _{RSS}				200		
Total Gate Charge	Q _{G(TOT)}				12.8	19.2	
Threshold Gate Charge	Q _{G(TH)}	V_{GS} = 4.5 V, V_{DS} = 15 V, I_{D} = 30 A			1.3		
Gate-to-Source Charge	Q _{GS}				4.7		nC
Gate-to-Drain Charge	Q _{GD}				5.2		
Total Gate Charge	Q _{G(TOT)}	$V_{GS} = 10 \text{ V}, \text{ V}_{DS} = 7$	15 V, I _D = 30 A		25.7		nC

SWITCHING CHARACTERISTICS (Note 4)

Turn–On Delay Time	t _{d(ON)}		12.6	
Rise Time	t _r	V _{GS} = 4.5 V, V _{DS} = 15 V,	20.2	
Turn-Off Delay Time	t _{d(OFF)}	I_D = 15 A, R_G = 3.0 Ω	16.4	ns
Fall Time	t _f		5.1	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. Pulse Test: pulse width \leq 300 µs, duty cycle \leq 2%.


4. Switching characteristics are independent of operating junction temperatures.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified) (continued)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
SWITCHING CHARACTERISTICS (I	Note 4)						
Turn-On Delay Time	t _{d(ON)}				7.7		
Rise Time	t _r	V _{GS} = 11.5 V, V	_{DS} = 15 V,		17.3		
Turn-Off Delay Time	t _{d(OFF)}	V _{GS} = 11.5 V, V I _D = 15 A, R _G	= 3.0 Ω		23.8		ns
Fall Time	t _f				2.8		
DRAIN-SOURCE DIODE CHARACT	ERISTICS			-			
Forward Diode Voltage	V _{SD}	$V_{GS} = 0 V, \\ I_{S} = 30 A \\ T_{J} = 25^{\circ}C \\ T_{J} = 125^{\circ}C$		0.87	1.2	V	
				0.73		v	
Reverse Recovery Time	t _{RR}	V _{GS} = 0 V, dIS/dt = 100 A/µs, I _S = 30 A			11.6		
Charge Time	t _a				7.8		ns
Discharge Time	t _b				3.7		
Reverse Recovery Charge	Q _{RR}				3.0		nC
PACKAGE PARASITIC VALUES							
Source Inductance	LS				2.49		nH
Drain Inductance, DPAK	L _D				0.0164		
Drain Inductance, IPAK	L _D	T _A = 25°C			1.88		
Gate Inductance	L _G				3.46		
Gate Resistance	R _G	-			0.7		Ω

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 3. Pulse Test: pulse width \leq 300 µs, duty cycle \leq 2%. 4. Switching characteristics are independent of operating junction temperatures.

TYPICAL PERFORMANCE CURVES



TYPICAL PERFORMANCE CURVES



TYPICAL PERFORMANCE CURVES





Figure 13. Thermal Response

ORDERING INFORMATION

Device	Package	Shipping [†]
NTD4858NT4G	DPAK (Pb-Free)	2500 / Tape & Reel
NTD4858N-1G	IPAK (Pb-Free)	75 Units / Rail
NTD4858N-35G	IPAK Trimmed Lead $(3.5 \pm 0.15 \text{ mm})$ (Pb-Free)	75 Units / Rail

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

ON



DOCUMENT NUMBER:	98AON10528D	Electronic versions are uncontrolled except when accessed directly from the Document Repositor Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.				
DESCRIPTION:	ON: IPAK (DPAK INSERTION MOUNT) PAGE 1 OF					
ON Semiconductor reserves the right the suitability of its products for any pa	ON Semiconductor and a trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the					

WW


= Work Week

rights of others.

1

L3

L4



*For additional information on our Pb-Free strategy and soldering

SCALE 3:1

Inches

details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DATE 03 JUN 2010


1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.

ON Semiconductor

- 2. CONTROLLING DIMENSION: INCHES. 3. THERMAL PAD CONTOUR OPTIONAL WITHIN DI-
- THERMAL FAD CONTOR OF FIGURE WITHIN DEMONSIONS b3, L3 and Z.
 DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL
- NOT EXCEED 0.006 INCHES PER SIDE 5. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
- 6. DATUMS A AND B ARE DETERMINED AT DATUM

	INC	HES	MILLIM	ETERS
DIM	MIN MAX		MIN	MAX
Α	0.086	0.094	2.18	2.38
A1	0.000	0.005	0.00	0.13
q	0.025	0.035	0.63	0.89
b2	0.030	0.045	0.76	1.14
b3	0.180	0.215	4.57	5.46
c	0.018	0.024	0.46	0.61
c2	0.018	0.024	0.46	0.61
D	0.235	0.245	5.97	6.22
Е	0.250	0.265	6.35	6.73
е	0.090	BSC	2.29 BSC	
Н	0.370	0.410	9.40	10.41
L	0.055	0.070	1.40	1.78
L1	0.108 REF		2.74 REF	
L2	0.020 BSC		0.51	BSC
L3	0.035	0.050	0.89	1.27
L4		0.040		1.01
Ζ	0.155		3.93	

MARKING DIAGRAM*



= Device Code = Assembly Location L = Wafer Lot Y = Year = Work Week WW G = Pb-Free Package


*This information is generic. Please refer to device data sheet for actual part marking.

DOCUMENT NUMBER:	98AON13126D	Electronic versions are uncontrolled except when accessed directly from the Document Reposite Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.				
DESCRIPTION:	DESCRIPTION: DPAK (SINGLE GAUGE)					
ON Semiconductor reserves the right the suitability of its products for any pa	ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the					

rights of others.







DOCUMENT NUMBER:	98AON23319D	Electronic versions are uncontrolled except when accessed directly from the Document Repositor Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.				
DESCRIPTION:	3.5 MM IPAK, STRAIGHT L	HT LEAD PAGE 1 OF				
ON Semiconductor reserves the right the suitability of its products for any pa	ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability. including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent to not					

rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>