ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

MOSFET - Power, Single **N-Channel, DFNW8**

150 V, 6.4 mΩ, 135 A

NTMTS6D0N15MC

Features

- Small Footprint (8x8 mm) for Compact Design
- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Typical Applications

- Power Tools, Battery Operated Vacuums
- UAV/Drones, Material Handling
- BMS/Storage, Home Automation

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

| Symbol | Parameter | | | Value | Unit |
|-----------------------------------|---|-----------------------|---------------------------|----------------|------|
| V _{DSS} | Drain-to-Source Voltage | | | 150 | V |
| V _{GS} | Gate-to-Source Voltage | | | ±20 | V |
| I _D | Continuous Drain Current R _{θJC} (Note 2) | Steady State | T _C = 25°C | 135 | Α |
| P _D | Power Dissipation $R_{\theta JC}$ (Note 2) | | | 245 | W |
| I _D | Continuous Drain Current R _{θJA} (Note 1, 2) | Steady State | T _A = 25°C | 19 | Α |
| P _D | Power Dissipation $R_{\theta JA}$ (Note 1, 2) | | | 4.9 | W |
| I _{DM} | Pulsed Drain Current | T _A = 25°C | C, t _p = 10 μs | 900 | Α |
| T _J , T _{stg} | Operating Junction and Storage Temperature Range | | | -55 to +175 | °C |
| I _S | Source Current (Body Diode) | | | 204 | Α |
| E _{AS} | Single Pulse Drain-to-Source Avalanche Energy (I _L = 46.2 A _{pk} , L = 0.3 mH) | | | 320 | mJ |
| T _L | Lead Temperature Soldering Reflow for Soldering Purposes (1/8" from case for 10 s) | | | 260 | °C |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


- 1. Surface-mounted on FR4 board using 1 in² pad size, 1 oz Cu pad.
- 2. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted




ON Semiconductor®

www.onsemi.com

| V _{(BR)DSS} | R _{DS(ON)} MAX | I _D MAX |
|----------------------|--|--------------------|
| 150 V | $6.4~\mathrm{m}\Omega$ @ $10~\mathrm{V}$ | 135 A |
| | 6.9 mΩ @ 8 V | |



N-CHANNEL MOSFET



DFNW8 8.3x8.4, 2P PQFN88 **CASE 507AP**

MARKING DIAGRAM

6D0N15MC **AWLYWW**

6D0N15MC = Specific Device Code = Assembly Location Α WL = Wafer Lot Code = Year Code WW = Work Week Code

ORDERING INFORMATION

| Device | Package | Shipping [†] |
|---------------|------------------------------|-----------------------|
| NTMTS6D0N15MC | DFNW8 PQFN88 (Pb-Free) | 3000 / Tape & Reel |

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

THERMAL RESISTANCE RATINGS


| Symbol | Parameter | Max | Unit |
|----------------|---|------|------|
| $R_{	hetaJC}$ | Junction-to-Case - Steady State (Note 2) | 0.6 | °C/W |
| $R_{	heta JA}$ | Junction-to-Ambient - Steady State (Note 2) | 30.2 | |

| Symbol | Parameter | Test Co | ondition | Min | Тур | Max | Unit |
|---------------------------------------|--|--|------------------------|-----|-------|----------|-------|
| FF CHARACT | ERISTICS | 1 | | | .1 | I | 1 |
| V _{(BR)DSS} | Drain – to – Source Breakdown Voltage | V _{GS} = 0 V, I _D = 250 μA | | 150 | _ | - | V |
| V _{(BR)DSS} / T _J | Drain – to – Source Breakdown Voltage Temperature Coefficient | I _D = 250 μA, ref to 25°C | | - | 58.67 | = | mV/°C |
| I _{DSS} | Zero Gate Voltage Drain Current | V _{GS} = 0 V, V _{DS} = 120 V | T _J = 25°C | - | - | 1 | μΑ |
| | | V _{DS} = 120 V | T _J = 125°C | - | _ | 10 | μΑ |
| I_{GSS} | Gate – to – Source Leakage Current | $V_{DS} = 0 V, V_{GS}$ | = ±20 V | - | - | ±100 | nA |
| N CHARACTE | ERISTICS (Note 3) | | | | | | |
| V _{GS(TH)} | Gate Threshold Voltage | $V_{GS} = V_{DS}, I_D =$ | = 379 μA | 2.5 | 3.6 | 4.5 | V |
| V _{GS(TH)} / T _J | Negative Threshold Temperature Coefficient | I _D = 250 μA, ref | to 25°C | - | -9.14 | - | mV/°C |
| R _{DS(on)} | Drain – to – Source On Resistance | V _{GS} = 10 V, I _D = 69 A | | - | 4.6 | 6.4 | mΩ |
| | | V _{GS} = 8 V, I _D = | 34 A | _ | 5.0 | 6.9 | |
| 9 _{FS} | Forward Transconductance | V _{DS} = 5 V, I _D = 69 A | | _ | 127 | - | S |
| R _G | Gate-Resistance | T _A = 25°C | | _ | 1.1 | _ | Ω |
| HARGES & C | APACITANCES | | | | I. | | |
| C _{ISS} | Input Capacitance | V _{GS} = 0 V, f = 1 MHz, V _{DS} = 75V | | _ | 4815 | - | pF |
| C _{OSS} | Output Capacitance | | | _ | 1482 | _ | |
| C _{RSS} | Reverse Transfer Capacitance | | | - | 9.7 | - | |
| Q _{G(TOT)} | Total Gate Charge | V _{GS} = 10 V, V _{DS} = 75 V, I _D = 69 A | | _ | 58 | - | nC |
| Q _{G(TH)} | Threshold Gate Charge | | | - | 34 | - | Ī |
| Q _{GS} | Gate-to-Source Charge | | | - | 26 | - | |
| Q _{GD} | Gate-to-Drain Charge | | | - | 8 | - | |
| Q _{OSS} | Output Charge | $V_{GS} = 0 V, V_{DS}$ | = 75 V | - | 173 | _ | nC |
| WITCHING CH | HARACTERISTICS, VGS = 10 V (Note 3) | | | | • | | • |
| t _{d(ON)} | Turn – On Delay Time | V _{GS} = 10 V, V _D | _S =75 V, | - | 30 | - | ns |
| t _r | Rise Time | $I_D = 69 \text{ A}, R_G = 6 \Omega$ | | - | 7 | - | |
| t _{d(OFF)} | Turn – Off Delay Time | | | - | 38 | - | Ī |
| t _f | Fall Time | | | - | 6 | _ | Ī |
| RAIN-SOURC | CE DIODE CHARACTERISTICS | • | | - | - | <u>-</u> | - |
| V _{SD} | Forward Diode Voltage | V _{GS} = 0 V, | T _J = 25°C | - | 0.87 | 1.2 | V |
| | | I _S = 69 A | T _J = 125°C | - | 0.7 | - | 1 |
| t _{RR} | Reverse Recovery Time | $V_{GS} = 0 \text{ V, dI}_{S}/c$ | dt = 100 A/μs, | - | 72 | - | ns |
| t _a | Charge Time | I _S = 69 A | | - | 49 | - | 1 |
| t _b | Discharge Time | | | _ | 23 | - | 1 |
| Q _{RR} | Reverse Recovery Charge | | | _ | 125 | _ | nC |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. Switching characteristics are independent of operating junction temperatures

TYPICAL CHARACTERISTICS



T_J, JUNCTION TEMPERATURE (°C)

Figure 5. On-Resistance Variation with

Temperature

0.5

-50 -25

V_{DS}, DRAIN-TO-SOURCE VOLTAGE (V)

Figure 6. Drain-to-Source Leakage Current
vs. Voltage

TYPICAL CHARACTERISTICS




Figure 12. I_{PEAK} vs. Time in Avalanche

Figure 11. Safe Operating Area

TYPICAL CHARACTERISTICS






Figure 13. Thermal Characteristics

PACKAGE DIMENSIONS

DFNW8 8.3x8.4, 2P CASE 507AP ISSUE C





FRONT VIEW

RECOMMENDED LAND PATTERN*

*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

D2-**♦** 0.10**M** C A B -b1 (8X) -E3 (4X) e1/2 **♦** 0.10**M** C A B b (8X) 0.10**M** C A B e/2 **BOTTOM VIEW**

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
 CONTROLLING DIMENSION: MILLIMETERS
 COPLANARITY APPLIES TO THE EXPOSED PADS AS WELL AS THE TERMINALS.
- 4. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH,
- 4. DIMENSIONS DI AND ET DO NOT INCLUDE MOLES FEACH, PROTRUSIONS, OR GATE BURRS.

 5. SEATING PLANE IS DEFINED BY THE TERMINALS.

 "A1" IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.

| DIM | MILLIMETERS | | | |
|------|-------------|------|------|--|
| Diw | MIN. | NOM. | MAX. | |
| Α | 1.00 | 1.10 | 1.20 | |
| A1 | 0.00 | | 0.05 | |
| b | 0.90 | 1.00 | 1.10 | |
| b1 | 0.43 | 0.53 | 0.63 | |
| O | 0.23 | 0.28 | 0.33 | |
| О | 8.20 | 8.30 | 8.40 | |
| D1 | 7.90 | 8.00 | 8.10 | |
| D2 | 6.80 | 6.90 | 7.00 | |
| D3 | 6.90 | 7.00 | 7.10 | |
| Е | 8.30 | 8.40 | 8.50 | |
| E1 | 7.80 | 7.90 | 8.00 | |
| E2 | 5.24 | 5.34 | 5.44 | |
| E3 | 0.25 | 0.35 | 0.45 | |
| е | 2.00 BSC | | | |
| e/2 | 1.00 BSC | | | |
| e1 | 2.70 BSC | | | |
| e1/2 | 1.35 BSC | | | |
| K | 1.50 | 1.57 | 1.70 | |
| L | 0.64 | 0.74 | 0.84 | |
| L1 | 0.67 | 0.77 | 0.87 | |
| Φ | 0° | | 12° | |

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability. arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative

ON Semiconductor Website: www.onsemi.com

Phone: 011 421 33 790 2910