

MOSFET - Power, Single N-Channel, WDFN6

25 V, 4.1 mΩ, 19.4 A

Product Preview

NTLJS4D7N03H

Features

- Small Footprint (4 mm²) for Compact Design
- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- These Devices are Pb-Free, Halogen-Free/BFR-Free and are RoHS Compliant

Applications

- DC-DC Converters
- Wireless Chargers
- Power Load Switch
- Power Management and Protection
- Battery Management

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

| Parameter | Symbol | Value | Unit |
|---|---|-----------------------|-----------------------|
| Drain-to-Source Voltage | V _{DSS} | 25 | V |
| Gate-to-Source Voltage | V _{GS} | ±20 | V |
| Continuous Drain Current R _{θJA} (Notes 1, 3) | Steady State | T _A = 25°C | I _D 19.4 A |
| | | T _A = 85°C | 14 |
| Power Dissipation R _{θJA} (Notes 1, 3) | T _A = 25°C | P _D 2.40 | W |
| Continuous Drain Current R _{θJA} (Notes 2, 3) | Steady State | T _A = 25°C | I _D 11.6 A |
| | | T _A = 85°C | 8.4 |
| Power Dissipation R _{θJA} (Notes 2, 3) | T _A = 25°C | P _D 0.86 | W |
| Pulsed Drain Current | T _A = 25°C, t _p = 10 μs | I _{DM} 78 | A |
| Operating Junction and Storage Temperature Range | T _J , T _{stg} | -55 to +150 | °C |
| Lead Temperature for Soldering Purposes (1/8" from case for 10 s) | T _L | 260 | °C |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS (Note 1)

| Parameter | Symbol | Value | Unit |
|---|------------------|-------|------|
| Junction-to-Ambient - Steady State (Note 1) | R _{θJA} | 52 | °C/W |
| Junction-to-Ambient - Steady State (Note 2) | R _{θJA} | 145 | |

1. Surface-mounted on FR4 board using 1 in² pad size, 2 oz. Cu pad.
2. Surface-mounted on FR4 board using minimum pad size, 2 oz. Cu pad.
3. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted. Actual continuous current will be limited by thermal & electro-mechanical application board design. R_{θCA} is determined by the user's board design.

This document contains information on a product under development. ON Semiconductor reserves the right to change or discontinue this product without notice.




ON Semiconductor®


www.onsemi.com

| V _{(BR)DSS} | R _{DS(on)} MAX | I _D MAX |
|----------------------|-------------------------|--------------------|
| 25 V | 4.1 mΩ @ 10 V | 19.4 A |
| | 6.25 mΩ @ 4.5 V | |

ELECTRICAL CONNECTION



N-CHANNEL MOSFET



WDFN6 (2.05x2.05)
CASE 483AV

MARKING DIAGRAM



YW = Date Code
ZZ = Assembly Lot Code
A = Assembly Site Code
4D7 = Specific Device Code

ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 4 of this data sheet.

NTLJS4D7N03H

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

| Parameter | Symbol | Test Condition | Min | Typ | Max | Unit |
|---|--------------------------------------|--|------------------------|------|------|-------|
| OFF CHARACTERISTICS | | | | | | |
| Drain-to-Source Breakdown Voltage | V _{(BR)DSS} | V _{GS} = 0 V, I _D = 250 μA | 25 | | | V |
| Drain-to-Source Breakdown Voltage Temperature Coefficient | V _{(BR)DSS} /T _J | I _D = 250 μA, ref to 25°C | | 16.2 | | mV/°C |
| Zero Gate Voltage Drain Current | I _{DSS} | V _{GS} = 0 V, V _{DS} = 20 V | T _J = 25°C | | 1 | μA |
| | | | T _J = 125°C | | 10 | |
| Gate-to-Source Leakage Current | I _{GSS} | V _{DS} = 0 V, V _{GS} = +20/-16 V | | | ±100 | nA |

ON CHARACTERISTICS (Note 4)

| | | | | | | |
|-----------------------------------|---------------------------------|---|-----|-------|------|-------|
| Gate Threshold Voltage | V _{GS(TH)} | V _{GS} = V _{DS} , I _D = 250 μA | 1.2 | | 2.1 | V |
| Threshold Temperature Coefficient | V _{GS} /T _J | I _D = 250 μA, ref to 25°C | | -4.76 | | mV/°C |
| Drain-to-Source On Resistance | R _{DS(on)} | V _{GS} = 10 V, I _D = 10 A | | 3.35 | 4.1 | mΩ |
| | | V _{GS} = 4.5 V, I _D = 10 A | | 5.02 | 6.25 | |
| Forward Transconductance | g _{FS} | V _{DS} = 5 V, I _D = 10 A | | 47 | | S |
| Gate Resistance | R _G | T _A = 25°C | | 1 | | Ω |

CHARGES AND CAPACITANCES

| | | | | | | |
|------------------------------|---------------------|---|--|-----|--|----|
| Input Capacitance | C _{iss} | V _{GS} = 0 V, V _{DS} = 15 V, f = 1.0 MHz | | 851 | | pF |
| Output Capacitance | C _{oss} | | | 524 | | |
| Reverse Transfer Capacitance | C _{rss} | | | 35 | | |
| Total Gate Charge | Q _{G(TOT)} | V _{GS} = 4.5 V, V _{DS} = 15 V, I _D = 10 A | | 6.7 | | nC |
| Threshold Gate Charge | Q _{G(TH)} | | | 1.2 | | |
| Gate-to-Source Charge | Q _{GS} | | | 2.3 | | |
| Gate-to-Drain Charge | Q _{GD} | | | 2.2 | | |
| Total Gate Charge | Q _{G(TOT)} | V _{GS} = 10 V, V _{DS} = 15 V, I _D = 10 A | | 14 | | nC |

SWITCHING CHARACTERISTICS, V_{GS} = 4.5 V (Note 5)

| | | | | | | |
|---------------------|---------------------|---|--|-----|--|----|
| Turn-On Delay Time | t _{d(on)} | V _{GS} = 4.5 V, V _{DD} = 15 V, I _D = 10 A, R _G = 6 Ω | | 9.3 | | ns |
| Rise Time | t _r | | | 8 | | |
| Turn-Off Delay Time | t _{d(off)} | | | 15 | | |
| Fall Time | t _f | | | 7.7 | | |

SWITCHING CHARACTERISTICS, V_{GS} = 10 V (Note 5)

| | | | | | | |
|---------------------|---------------------|--|--|------|--|----|
| Turn-On Delay Time | t _{d(on)} | V _{GS} = 10 V, V _{DD} = 15 V, I _D = 10 A, R _G = 6 Ω | | 6.8 | | ns |
| Rise Time | t _r | | | 2.7 | | |
| Turn-Off Delay Time | t _{d(off)} | | | 19.6 | | |
| Fall Time | t _f | | | 4.8 | | |

DRAIN-SOURCE DIODE CHARACTERISTICS

| | | | | | | | |
|-------------------------|-----------------|---|------------------------|--|------|-----|----|
| Forward Diode Voltage | V _{SD} | V _{GS} = 0 V, I _S = 10 A | T _J = 25°C | | 0.79 | 1.2 | V |
| | | | T _J = 125°C | | 0.65 | | |
| Reverse Recovery Time | t _{RR} | V _{GS} = 0 V, dI _S /dt = 100 A/μs, I _S = 10 A | | | 32.6 | | ns |
| Reverse Recovery Charge | Q _{RR} | | | | 14.3 | | nC |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2%.

5. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate-to-Source Voltage (V)




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On-Resistance Variation with Temperature




Figure 6. Drain-to-Source Leakage Current vs. Voltage

NTLJS4D7N03H

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current

DEVICE ORDERING INFORMATION


| Device | Package | Shipping† |
|-----------------|--------------------|--------------------|
| NTLJS4D7N03HTAG | WDFN6 (Pb-Free) | 3000 / Tape & Reel |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

MECHANICAL CASE OUTLINE


PACKAGE DIMENSIONS

ON Semiconductor®




WDFN6 2.05X2.05, 0.65P
CASE 483AV
ISSUE A

DATE 02 APR 2019



LAND PATTERN RECOMMENDATION



NOTES:

1. CONTROLLING DIMENSION: MILLIMETERS.
2. COPLANARITY APPLIES TO THE EXPOSED PADS AS WELL AS THE TERMINALS.
3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.
4. SEATING PLANE IS DEFINED BY THE TERMINALS. "A1" IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.

| DIM | MILLIMETERS | | |
|-----|-------------|------|------|
| | MIN. | NOM. | MAX. |
| A | 0.60 | 0.70 | 0.80 |
| A1 | 0.00 | - | 0.05 |
| A4 | (0.20) | | |
| b | 0.25 | 0.30 | 0.35 |
| D | 1.95 | 2.05 | 2.15 |
| D2 | 0.84 | 0.89 | 0.94 |
| D3 | (0.95) | | |
| E | 1.95 | 2.05 | 2.15 |
| E2 | 1.45 | 1.50 | 1.55 |
| e | 0.65 BSC | | |
| e1 | 1.30 BSC | | |
| k | (0.35) | | |
| k1 | (0.45) | | |
| L | 0.18 | 0.28 | 0.38 |
| L3 | 0.25 | 0.30 | 0.35 |
| L4 | 0.55 | 0.60 | 0.65 |
| L5 | (0.23) | | |
| aaa | 0.10 | | |
| bbb | 0.10 | | |
| ccc | 0.05 | | |
| ddd | 0.05 | | |
| eee | 0.05 | | |

| | | |
|-------------------------|-------------------------------|--|
| DOCUMENT NUMBER: | 98AON13671G | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION: | WDFN6 2.05X2.05, 0.65P | PAGE 1 OF 1 |

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT

North American Technical Support:

Voice Mail: 1 800-282-9855 Toll Free USA/Canada

Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative