### **ON Semiconductor**

### Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

# Power MOSFET 30 Amps, 60 Volts

### N-Channel TO-220 and D<sup>2</sup>PAK

Designed for low voltage, high speed switching applications in power supplies, converters and power motor controls and bridge circuits.

#### **Features**

• Pb-Free Packages are Available

#### **Typical Applications**

- Power Supplies
- Converters
- Power Motor Controls
- Bridge Circuits

#### **MAXIMUM RATINGS** (T<sub>J</sub> = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
Drain-to-Source Voltage	$V_{DSS}$	60	Vdc
Drain-to-Gate Voltage ( $R_{GS} = 10 \text{ M}\Omega$ )	$V_{DGR}$	60	Vdc
Gate-to-Source Voltage - Continuous - Non-Repetitive (t <sub>p</sub> ≤10 ms)	V <sub>GS</sub> V <sub>GS</sub>	±20 ±30	Vdc
Drain Current - Continuous @ $T_A = 25^{\circ}C$ - Continuous @ $T_A = 100^{\circ}C$ - Single Pulse $(t_p \le 10 \ \mu s)$	I <sub>D</sub> I <sub>D</sub>	27 15 80	Adc Apk
Total Power Dissipation @ T <sub>A</sub> = 25°C Derate above 25°C	P <sub>D</sub>	88.2 0.59	W W/°C
Operating and Storage Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	-55 to +175	°C
Single Pulse Drain-to-Source Avalanche Energy – Starting $T_J = 25^{\circ}C$ ( $V_{DD} = 50$ Vdc, $V_{GS} = 10$ Vdc, $L = 0.3$ mH $I_{L(pk)} = 26$ A, $V_{DS} = 60$ Vdc)	E <sub>AS</sub>	101	mJ
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	1.7	°C/W
Maximum Lead Temperature for Soldering Purposes, 1/8 in from case for 10 seconds	TL	260	°C

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.




### ON Semiconductor®

http://onsemi.com

## 30 AMPERES, 60 VOLTS


 $R_{DS(on)} = 42 \text{ m}\Omega$ 







## MARKING DIAGRAMS & PIN ASSIGNMENTS



NTx30N06 = Device Code x = B or P

A = Assembly Location

Y = Year
WW = Work Week
G = Pb-Free Package

#### **ORDERING INFORMATION**

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.

#### **ELECTRICAL CHARACTERISTICS** (T<sub>.I</sub> = 25°C unless otherwise noted)

	Symbol	Min	Тур	Max	Unit	
OFF CHARACTERISTICS						
Drain-to-Source Breakdown \ (V <sub>GS</sub> = 0 Vdc, I <sub>D</sub> = 250 μAdd Temperature Coefficient (Posit	V <sub>(BR)DSS</sub>	60 -	71.1 70	_ _	Vdc mV/°C	
Zero Gate Voltage Drain Curre $(V_{DS} = 60 \text{ Vdc}, V_{GS} = 0 \text{ Vdc})$ $(V_{DS} = 60 \text{ Vdc}, V_{GS} = 0 \text{ Vdc})$	I <sub>DSS</sub>	_ _	- -	1.0 10	μAdc	
Gate-Body Leakage Current (	I <sub>GSS</sub>	_	_	±100	nAdc	
ON CHARACTERISTICS (Note	1)					
Gate Threshold Voltage (Note $(V_{DS} = V_{GS}, I_D = 250 \mu Adc)$ Threshold Temperature Coeffice	V <sub>GS(th)</sub>	2.0	3.05 7.3	4.0	Vdc mV/°C	
Static Drain-to-Source On-Re (V <sub>GS</sub> = 10 Vdc, I <sub>D</sub> = 15 Adc)	R <sub>DS(on)</sub>	_	35	42	mΩ	
Static Drain-to-Source On-Vounce ( $V_{GS} = 10 \text{ Vdc}$ , $I_D = 30 \text{ Adc}$ ) ( $V_{GS} = 10 \text{ Vdc}$ , $I_D = 15 \text{ Adc}$ )	V <sub>DS(on)</sub>	_ _	1.1 0.98	1.5 -	Vdc	
Forward Transconductance (N	9FS	_	16	-	mhos	
DYNAMIC CHARACTERISTICS	3					
Input Capacitance		C <sub>iss</sub>	_	850	1200	pF
Output Capacitance	$(V_{DS} = 25 \text{ Vdc}, V_{GS} = 0 \text{ Vdc}, f = 1.0 \text{ MHz})$	C <sub>oss</sub>	_	250	350	
Transfer Capacitance	,	C <sub>rss</sub>	_	68	100	
SWITCHING CHARACTERISTI	CS (Note 2)					
Turn-On Delay Time		t <sub>d(on)</sub>	_	11	25	ns
Rise Time	(V <sub>DD</sub> = 30 Vdc, I <sub>D</sub> = 30 Adc,	t <sub>r</sub>	_	36	80	
Turn-Off Delay Time	$V_{GS}$ = 10 Vdc, $R_G$ = 9.1 $\Omega$ ) (Note 1)	t <sub>d(off)</sub>	_	24	50	
Fall Time		t <sub>f</sub>	_	31	60	
Gate Charge		Q <sub>T</sub>	_	23.4	46	nC
	$(V_{DS} = 48 \text{ Vdc}, I_D = 30 \text{ Adc}, V_{GS} = 10 \text{ Vdc}) \text{ (Note 1)}$	Q <sub>1</sub>	_	5.1	_	- -
	VGS = 10 Vd0/ (10tc 1/	Q <sub>2</sub>	_	11	_	
SOURCE-DRAIN DIODE CHAP	RACTERISTICS					
Forward On–Voltage	$(I_S = 30 \text{ Adc}, V_{GS} = 0 \text{ Vdc}) \text{ (Note 1)}$ $(I_S = 30 \text{ Adc}, V_{GS} = 0 \text{ Vdc}, T_J = 150^{\circ}\text{C})$	$V_{SD}$	- -	1.03 1.05	1.15 –	Vdc
Reverse Recovery Time	(I <sub>S</sub> = 30 Adc, V <sub>GS</sub> = 0 Vdc, dI <sub>S</sub> /dt = 100 A/μs) (Note 1)	t <sub>rr</sub>	_	52	-	ns
		t <sub>a</sub>	-	38	-	
	3.0 2	t <sub>b</sub>	_	15	-	
Reverse Recovery Stored Cha	Q <sub>RR</sub>	_	0.094	_	μС	

Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2%.
 Switching characteristics are independent of operating junction temperatures.




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On–Resistance versus Gate–to–Source Voltage




Figure 4. On-Resistance versus Drain Current and Gate Voltage




Figure 5. On–Resistance Variation with Temperature




Figure 6. Drain-to-Source Leakage Current versus Voltage




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source and Drain-to-Source Voltage versus Total Charge




Figure 9. Resistive Switching Time Variation versus Gate Resistance




Figure 10. Diode Forward Voltage versus

Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Avalanche Energy versus Starting Junction Temperature




Figure 13. Thermal Response




Figure 14. Diode Reverse Recovery Waveform


#### **ORDERING INFORMATION**


Device	Package	Shipping <sup>†</sup>
NTP30N06	TO-220AB	50 Units / Rail
NTB30N06	D <sup>2</sup> PAK	50 Units / Rail
NTB30N06G	D <sup>2</sup> PAK (Pb-Free)	50 Units / Rail
NTB30N06T4	D <sup>2</sup> PAK	800 Units / Tape & Reel
NTB30N06T4G	D <sup>2</sup> PAK (Pb-Free)	800 Units / Tape & Reel

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### **PACKAGE DIMENSIONS**

#### D<sup>2</sup>PAK CASE 418B-04 ISSUE J







- NOTES:
  1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
  2. CONTROLLING DIMENSION: INCH.
  3. 418B-01 THRU 418B-03 OBSOLETE, NEW STANDARD 418B-04.

	INCHES		MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	0.340	0.380	8.64	9.65	
В	0.380	0.405	9.65	10.29	
С	0.160	0.190	4.06	4.83	
D	0.020	0.035	0.51	0.89	
E	0.045	0.055	1.14	1.40	
F	0.310	0.350	7.87	8.89	
G	0.100 BSC		2.54 BSC		
Н	0.080	0.110	2.03	2.79	
J	0.018	0.025	0.46	0.64	
K	0.090	0.110	2.29	2.79	
L	0.052	0.072	1.32	1.83	
М	0.280	0.320	7.11	8.13	
N	0.197 REF		5.00 REF		
Р	0.079 REF		2.00 REF		
R	0.039 REF		0.99 REF		
S	0.575	0.625	14.60	15.88	
V	0.045	0.055	1 14	1 40	

- STYLE 2:
  PIN 1. GATE
  2. DRAIN
  3. SOURCE
  4. DRAIN




#### **SOLDERING FOOTPRINT\***



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### PACKAGE DIMENSIONS

TO-220 CASE 221A-09 **ISSUE AA** 



- NOTES:
  1. DIMENSIONING AND TOLERANCING PER ANSI
- CONTROLLING DIMENSION: INCH.
- DIMENSION Z DEFINES A ZONE WHERE ALL BODY AND LEAD IRREGULARITIES ARE ALLOWED.

	INCHES		MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	0.570	0.620	14.48	15.75	
В	0.380	0.405	9.66	10.28	
С	0.160	0.190	4.07	4.82	
D	0.025	0.035	0.64	0.88	
F	0.142	0.147	3.61	3.73	
G	0.095	0.105	2.42	2.66	
Н	0.110	0.155	2.80	3.93	
J	0.018	0.025	0.46	0.64	
K	0.500	0.562	12.70	14.27	
L	0.045	0.060	1.15	1.52	
N	0.190	0.210	4.83	5.33	
Q	0.100	0.120	2.54	3.04	
R	0.080	0.110	2.04	2.79	
S	0.045	0.055	1.15	1.39	
T	0.235	0.255	5.97	6.47	
U	0.000	0.050	0.00	1.27	
٧	0.045		1.15		
Z		0.080		2.04	

STYLE 5: PIN 1.

GATE DRAIN 2.

3. SOURCE

DRAIN

ON Semiconductor and un are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 61312, Phoenix, Arizona 85082-1312 USA Phone: 480-829-7710 or 800-344-3860 Toll Free USA/Canada Fax: 480-829-7709 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Japan: ON Semiconductor, Japan Customer Focus Center 2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051 Phone: 81-3-5773-3850

ON Semiconductor Website: http://onsemi.com

Order Literature: http://www.onsemi.com/litorder

For additional information, please contact your local Sales Representative