ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

MOSFET – Power, Single N-Channel

100 V, 14.4 mΩ, 45 A

NTTFS012N10MD

Features

- Shielded Gate MOSFET Technology
- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- Low Q_{RR}, Soft Recovery Body Diode
- Low Qoss to Improve Light Load Efficiency
- These Devices are Pb-Free, Halogen Free/BFR Free, Beryllium Free and are RoHS Compliant

Typical Applications

- Primary Switch in Isolated DC-DC Converter
- Synchronous Rectification (SR) in DC-DC and AC-DC
- AC-DC Adapters (USB PD) SR
- Load Switch, Hotswap, and ORing Switch
- BLDC Motor and Solar Inverter

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter		Symbol	Value	Unit	
Drain-to-Source Breakdown Voltage		$V_{(BR)DSS}$	100	V	
Gate-to-Source Voltage	Э		V _{GS}	±20	V
Continuous Drain Current $R_{\theta JC}$ (Note 2)	Steady	T _C = 25°C	Ι _D	45	Α
Power Dissipation $R_{\theta JC}$ (Note 2)	State T _C = 25°C		P _D	62	W
Continuous Drain Current R _{0JA} (Notes 1, 2)	Steady	T _A = 25°C	Ι _D	9.2	Α
Power Dissipation R _{θJA} (Notes 1, 2)	State	T _A = 25°C	P _D	2.7	W
Pulsed Drain Current	$T_A = 25^{\circ}C, t_p = 10 \ \mu s$		I _{DM}	217	Α
Operating Junction and Storage Temperature Range		T _J , T _{stg}	-55 to +150	°C	
Source Current (Body Diode)		I _S	51.8	Α	
Single Pulse Drain-to-Source Avalanche Energy (I _{AV} = 9 A, L = 3 mH)		E _{AS}	121	mJ	
Lead Temperature Soldering Reflow for Soldering Purposes (1/8" from case for 10 s)		TL	300	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State (Note 2)	$R_{\theta JC}$	2.0	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	46.5	

- 1. Surface-mounted on FR4 board using a 1 in² pad size, 1 oz Cu pad.
- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.




ON Semiconductor®

www.onsemi.com

V _{(BR)DSS}	R _{DS(on)} MAX	I _D MAX
100 V	14.4 mΩ @ 10 V	45 A
100 V	21.0 mΩ @ 6 V	45 A


N-Channel



MARKING DIAGRAM



WDFN8 (μ8FL) CASE 511DY



XXXX = Specific Device Code A = Assembly Location

Y = Year WW = Work Week = Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping [†]
NTTFS012N10MD	WDFN8	1500 / Tape &
	(Pb-Free)	Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		100			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} / T _J	I _D = 250 μA, ref to 25°C			60		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 V$,	T _J = 25°C			1.0	μΑ
		$V_{DS} = 80 \text{ V}$	T _J = 125°C			100	
Gate-to-Source Leakage Current	I _{GSS}	V _{DS} = 0 V, V _{GS} = 20 V				100	nA
ON CHARACTERISTICS (Note 3)							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D = 78 \mu A$		2		4	V
Negative Threshold Temperature Coefficient	V _{GS(TH)} /T _J	I _D = 78 μA, ref	to 25°C		-8.1		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 15 A		12.2	14.4	mΩ
		V _{GS} = 6 V	I _D = 7.5 A		16.7	21.0	
Forward Transconductance	9FS	V _{DS} = 8 V, I _D	= 15 A		36		S
Gate-Resistance	R_{G}	T _A = 25°C			0.5	1.6	Ω
CHARGES & CAPACITANCES					•		•
Input Capacitance	C _{ISS}	$V_{GS} = 0 \text{ V, f} = 1 \text{ MHz, } V_{DS} = 50 \text{ V}$			965		pF
Output Capacitance	C _{OSS}				270		
Reverse Transfer Capacitance	C _{RSS}				8.4		
Output Charge	Q _{OSS}	V _{GS} = 0 V, V _{DS}	_S = 50 V		22		nC
Total Gate Charge	Q _{G(TOT)}	V _{GS} = 6 V, V _{DS} = 50 V, I _D = 15 A			8		nC
Total Gate Charge	Q _{G(TOT)}	V _{GS} = 10 V, V _{DS} = 50 V,			13		
Gate-to-Source Charge	Q _{GS}	I _D = 15	А		4.6		
Gate-to-Drain Charge	Q_{GD}				1.8		
Plateau Voltage	V _{GP}				4.5		V
SWITCHING CHARACTERISTICS (Note 3)							
Turn-On Delay Time	t _{d(ON)}	V_{GS} = 10 V, V_{DS} = 50 V, I_{D} = 15 A, R_{G} = 6 Ω			12		ns
Rise Time	t _r				2.7]
Turn-Off Delay Time	t _{d(OFF)}				17		
Fall Time	t _f				2.6		
DRAIN-SOURCE DIODE CHARACTERISTIC	s				•		•
Forward Diode Voltage	V _{SD}	V _{GS} = 0 V,	T _J = 25°C 0.85	0.85		V	
		I _S = 15 A	T _J = 125°C		0.72		
Reverse Recovery Time	t _{RR}	V _{GS} = 0 V, dls/dt = 1000 A/μs,			20		ns
Reverse Recovery Charge	Q _{RR}	I _S = 7.5	A		116		nC
Reverse Recovery Time	t _{RR}	V _{GS} = 0 V, dls/dt = 100 A/μs, l _S = 15 A			36		ns
Reverse Recovery Charge	Q _{RR}				34		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.
3. Switching characteristics are independent of operating junction temperatures.
4. R_{θ,JA} is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. R_{θ,JC} is guaranteed by design while R_{θ,CA} is determined by the user's board design.
5. Pulse Test: Pulse Width < 300 μs. Duty cycle < 2%.
6. E_{AS} of 121 mJ is based on started T_J = 25°C, L = 3 mH, I_{AV} = 9 A, V_{DD} = 100 V, V_{GS} = 15 V. 100% test at L = 0.1 mH, I_{AV} = 24 A.
7. As an N-ch device, the negative Vgs rating is for low duty cycle pulse occurrence only. No continuous rating is implied.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 3. On-Resistance vs. Gate-to-Source Voltage






Figure 5. On-Resistance Variation with **Temperature**



V_{GS}, GATE-TO-SOURCE VOLTAGE (V) Figure 2. Transfer Characteristics






Figure 4. On-Resistance vs. Drain Current and **Gate Voltage**




Figure 6. Drain-to-Source Leakage Current vs. Voltage

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source Voltage vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Drain Current vs. Time in Avalanche

TYPICAL CHARACTERISTICS





Figure 13. Transient Thermal Impedance


PACKAGE DIMENSIONS

WDFN8 3.3x3.3, 0.65P



(4X) Θ D1 Λ Λ (8X) Δ 0.10 C SEATING PLANE

END VIEW



NOTES:

- 1. CONTROLLING DIMENSION: MILLIMETERS
- 2. DIMENSIONS D1 & E1 DO NOT INCLUDE MOLD FLASH PROTRUSIONS NOR GATE BURRS.

DIM	MILLIMETERS				
MIN		NOM	MAX		
Α	0.70	0.75	0.80		
A1	0.00	-	0.05		
b	0.23	0.33	0.43		
С	0.15	0.20	0.25		
О	3.20	3.30	3.40		
D1	2.95	3.13	3.30		
D2	1.98	2.20	2.40		
Е	3.20	3.30	3.40		
E1	2.80	3.00	3.15		
E2	1.40	1.60	1.80		
E3	0.15	0.25	0.40		
е	0.65 BSC				
Ŋ	0.30	0.43	0.55		
G1	0.25	0.35	0.45		
K	0.55	0.75	0.95		
Г	0.35	0.52	0.65		
L1	0.06	0.15	0.30		
М	1.35	1.50	1.60		
θ	0	-	12		

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability. arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada

Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative