ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

MOSFET - Power, Single N-Channel, DUAL COOL™, DFN8 5x6.15 60 V, 1.9 mΩ, 199 A

NTMFSC1D9N06HL

Features

- Advanced Dual-Side Cooled Packaging
- Ultra Low R_{DS(on)} to Minimize Conduction Losses
- MSL1 Robust Packaging Design
- Low Qg and Qoss to Minimize Charge Losses
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

Typical Applications

- DC-DC Conversion
- Orring FET/Load Switching
- Synchronous Rectification

MAXIMUM RATINGS (T_J = 25°C, Unless otherwise specified)

Parameter			Symbol	Value	Unit		
Drain-to-Source Breakdown Voltage			V _{(BR)DSS}	60	V		
Gate-to-Source Voltage			V _{GS}	±20	V		
Continuous Drain Current $R_{\theta,JC}$ (Note 2)	Steady State T _C = 25°C		Ι _D	199	Α		
Power Dissipation $R_{\theta JC}$ (Note 2)			P _D	166	V		
Continuous Drain Current $R_{\theta JA}$ (Note 1, 2)	Steady State T _A = 25°C				Ι _D	30	Α
Power Dissipation $R_{\theta JA}$ (Note 1, 2)	State		P _D	3.8	W		
Pulsed Drain Current	$T_A = 25^{\circ}C$	c, t _p = 100 μs	I _{DM}	820	Α		
Operating Junction and Storage Temperature Range			T _J , T _{stg}	-55 to +175	°C		
Source Current (Body Diode)			I _S	138	Α		
Single Pulse Drain-to-Source Avalanche Energy (I _{AV} = 43 A)			E _{AS}	277	mJ		
Lead Temperature Soldering Reflow for Soldering Purposes (1/8" from case for 10 s)			TL	260	°C		

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- 1. Surface–mounted on FR4 board using 1 in² pad size, 1 oz Cu pad.
- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.





ON Semiconductor®

www.onsemi.com

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX		
60 V	1.9 mΩ @ 10 V	199 A		

N-Channel MOSFET





DFN8 5x6.15 CASE 506EG

MARKING DIAGRAM



1D9N06 = Specific Device Code A = Assembly Plant Code YWW = Date Code (Year & Week)

ZZ = Lot Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.

THERMAL CHARACTERISTICS

Symbol	Parameter	Max	Unit
$R_{ heta JC}$	Junction-to-Case - Steady State (Note 2)	0.9	°C/W
$R_{ heta JT}$	Junction-to-Top Source - Steady State (Note 2)	1.4	
$R_{ heta JA}$	Junction-to-Ambient - Steady State (Note 2)	39	

ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise noted)

Parameter	Symbol	Test Conditions		Min	Тур	Max	Unit
OFF CHARACTERISTICS	•						•
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = 250 μA		60			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} / T _J				38		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	Voc. = 0 V T _J = 25°C				10	μΑ
		$V_{GS} = 0 V$, $V_{DS} = 60 V$	T _J = 125°C			250	
Gate-to-Source Leakage Current	I _{GSS}	V _{DS} = 0 V, V _{GS} =	= 20 V			100	nA
ON CHARACTERISTICS (Note 3)							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}$, $I_D = 2$	250 μΑ	1.2		2.0	V
Negative Threshold Temperature Coefficient	V _{GS(TH)} [/] T _J	I _D = 250 μA, ref to 25°C			-5.6		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V, I _D =	: 50 A		1.4	1.9	mΩ
	 	V _{GS} = 4.5 V, I _D =	= 40 A		1.9	2.6	
Forward Trans-conductance	9FS	V _{DS} = 15V, I _D = 50A			357		S
Gate-Resistance	R_{G}	V _{GS} = 0 V, f = 1 MHz			1.4	2.6	Ω
CHARGES & CAPACITANCES	•						•
Input Capacitance	C _{ISS}	$V_{GS} = 0 \text{ V, f} = 1 \text{ MHz,}$ $V_{DS} = 30 \text{ V}$			4910		pF
Output Capacitance	C _{OSS}				862		1
Reverse Transfer Capacitance	C _{RSS}				12		
Total Gate Charge	Q _{G(TOT)}	$V_{GS} = 10 \text{ V}, V_{DS} = 30 \text{ V}, I_D = 50 \text{ A}$			64		nC
Total Gate Charge	Q _{G(TOT)}	$V_{GS} = 4.5 \text{ V}, V_{DS} = 30 \text{ V}, I_{D} = 50 \text{ A}$ $V_{DD} = 30 \text{ V}, V_{GS} = 0 \text{ V}$			29		
Threshold Gate Charge	Q _{G(TH)}				7.2		
Gate-to-Source Charge	Q_{GS}				13.2		nC
Gate-to-Drain Charge	Q_{GD}				5.7		
Output Charge	Q _{OSS}				92		nC
SWITCHING CHARACTERISTICS (Note	e 3)						
Turn-On Delay Time	t _{d(ON)}				25.4		ns
Rise Time	t _r	V_{GS} = 4.5 V, V_{DS} = 30 V, I_D = 50 A, R_G = 2.5 Ω			16.2		
Turn-Off Delay Time	t _{d(OFF)}				30.3		
Fall Time	t _f				10.1		
DRAIN-SOURCE DIODE CHARACTER	ISTICS						
Forward Diode Voltage	V_{SD} $V_{GS} = 0 V$, $T_{J} = 28$		T _J = 25°C		0.80	1.2	V
			T _J = 150°C		0.63		
Reverse Recovery Time	t _{RR}	$V_{GS} = 0 \text{ V, } dI_{S}/dt = 100 \text{ A/}\mu\text{s,}$ $I_{S} = 50 \text{ A}$			56		ns
Reverse Recovery Charge	Q_{RR}				67		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS




Figure 5. On–Resistance Variation with Temperature

Figure 6. Drain-to-Source Leakage Current vs. Voltage

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source and Drain-to-Source Voltage vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Forward Bias Safe Operating Area




Figure 12. Unclamped Inductive Switching Capability

TYPICAL CHARACTERISTICS





Figure 13. Transient Thermal Impedance

ORDERING INFORMATION

Device	Device Marking	Package	Shipping [†]
NTMFSC1D9N06HL	1D9N06	DFN8 (Pb-Free/Halogen Free)	3000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS



DUAL COOL is a registered trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.

ON Semiconductor and ware trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor nessure any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages,

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative