# **ON Semiconductor**

# Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

# **Power MOSFET**

# 40 V, 0.42 m $\Omega$ , 554.5 A, Single N-Channel

#### **Features**

- Small Footprint (8x8 mm) for Compact Design
- Low R<sub>DS(on)</sub> to Minimize Conduction Losses
- Low Q<sub>G</sub> and Capacitance to Minimize Driver Losses
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

## **Typical Applications**

- Power Tools, Battery Operated Vacuums
- UAV/Drones, Material Handling
- BMS/Storage, Home Automation

### **MAXIMUM RATINGS** (T<sub>J</sub> = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			$V_{DSS}$	40	V
Gate-to-Source Voltage			V <sub>GS</sub>	±20	V
Continuous Drain	Steady State	T <sub>C</sub> = 25°C	I <sub>D</sub>	554.5	Α
Current R <sub>0JC</sub> (Note 2)	State	T <sub>C</sub> = 100°C		392.1	
Power Dissipation	Steady State	T <sub>C</sub> = 25°C	P <sub>D</sub>	245.4	W
R <sub>θJC</sub> (Note 2)	State	T <sub>C</sub> = 100°C		122.7	
Continuous Drain	Steady State	T <sub>A</sub> = 25°C	I <sub>D</sub>	78.9	Α
Current R <sub>0JA</sub> (Notes 1, 2)	State	T <sub>A</sub> = 100°C		55.8	
Power Dissipation	Steady	T <sub>A</sub> = 25°C	$P_{D}$	5.0	W
R <sub>θJA</sub> (Notes 1, 2)	State	T <sub>A</sub> = 100°C		2.5	
Pulsed Drain Current	T <sub>A</sub> = 25	°C, t <sub>p</sub> = 10 μs	I <sub>DM</sub>	900	Α
Operating Junction and Storage Temperature Range			T <sub>J</sub> , T <sub>stg</sub>	-55 to +175	°C
Source Current (Body Diode)			I <sub>S</sub>	204.5	Α
Single Pulse Drain-to-Source Avalanche Energy (I <sub>L(pk)</sub> = 52.7 A)			E <sub>AS</sub>	2058	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			TL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

### THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State (Note 2)	$R_{\theta JC}$	0.61	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	30.2	


- 1. Surface-mounted on FR4 board using a 1 in<sup>2</sup> pad size, 1 oz. Cu pad.
- 2. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.




## ON Semiconductor®

### www.onsemi.com

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX
40 V	0.42 m $\Omega$ @ 10 V	5545 A
40 V	0.66 m $\Omega$ @ 4.5 V	554.5 A



**N-CHANNEL MOSFET** 



**POWER 88 CASE 507AP** 

### **MARKING DIAGRAM**



XXX = Device Code

(8 A-N characters max)

= Assembly Location WL = 2-digit Wafer Lot Code

= Year Code

WW = Work Week Code

### **ORDERING INFORMATION**

See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.

## **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub> = 25°C unless otherwise specified)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		40			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> /	I <sub>D</sub> = 250 μA, ref to 25°C			12.6		mV/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{GS} = 0 V$ , $T_{OS} = 0 V$				10	
		$V_{DS} = 40 \text{ V}$	T <sub>J</sub> = 125°C			250	μΑ
Gate-to-Source Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> = 0 V, V <sub>GS</sub> = 20 V				100	nA
ON CHARACTERISTICS (Note 3)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}, I_D = 250 \mu A$		1.2		2.0	V
Negative Threshold Temperature Coefficient	V <sub>GS(TH)</sub> /T <sub>J</sub>	I <sub>D</sub> = 250 μA, ref to 25°C			-6.0		mV/°C
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V	I <sub>D</sub> = 50 A		0.35	0.42	0
		V <sub>GS</sub> = 4.5 V	I <sub>D</sub> = 50 A		0.52	mΩ 52 0.66	mΩ
Forward Transconductance	9 <sub>FS</sub>	V <sub>DS</sub> =5 V, I <sub>D</sub> = 50 A			323		S
Gate Resistance	$R_{G}$	T <sub>A</sub> = 25°C			1.0		Ω
CHARGES, CAPACITANCES & GATE RESIS	STANCE						
Input Capacitance	C <sub>ISS</sub>			16013		pF	
Output Capacitance	C <sub>OSS</sub>	V <sub>GS</sub> = 0 V, f = 1 MHz, V <sub>DS</sub> = 20 V			6801		
Reverse Transfer Capacitance	C <sub>RSS</sub>				299		
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 4.5 V, V <sub>DS</sub> = 20 V; I <sub>D</sub> = 50 A			126		nC
Threshold Gate Charge	Q <sub>G(TH)</sub>				22.5		
Gate-to-Source Charge	$Q_{GS}$				39.9		
Gate-to-Drain Charge	$Q_{GD}$				38.4		
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 2	0 V; I <sub>D</sub> = 50 A		265		nC
SWITCHING CHARACTERISTICS, V <sub>GS</sub> = 4.5	<b>V</b> (Note 4)						
Turn-On Delay Time	t <sub>d(ON)</sub>	$V_{GS}$ = 4.5 V, $V_{DS}$ = 20 V, $I_{D}$ = 50 A, $R_{G}$ = 6 $\Omega$			89.4		- ns
Rise Time	t <sub>r</sub>				111		
Turn-Off Delay Time	t <sub>d(OFF)</sub>				180		
Fall Time	t <sub>f</sub>				84.7		
DRAIN-SOURCE DIODE CHARACTERISTIC	s						
Forward Diode Voltage	V <sub>SD</sub>	V <sub>GS</sub> = 0 V, I <sub>S</sub> = 50 A	T <sub>J</sub> = 25°C		0.75	1.2	
			T <sub>J</sub> = 125°C		0.6		· V
Reverse Recovery Time	t <sub>RR</sub>	$V_{GS} = 0 \text{ V, dIS/dt} = 100 \text{ A/}\mu\text{s,}$ $I_{S} = 50 \text{ A}$			99.3		ns
Charge Time	t <sub>a</sub>				62.4		
Discharge Time	t <sub>b</sub>				36.9		
Reverse Recovery Charge	Q <sub>RR</sub>				228		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. Pulse Test: pulse width  $\leq 300~\mu s$ , duty cycle  $\leq 2\%$ .

4. Switching characteristics are independent of operating junction temperatures.

### **TYPICAL CHARACTERISTICS**



T<sub>J</sub>, JUNCTION TEMPERATURE (°C) Figure 5. On-Resistance Variation with **Temperature** 

65

105

145

25

0

-55

-15

V<sub>DS</sub>, DRAIN-TO-SOURCE VOLTAGE (V) Figure 6. Drain-to-Source Leakage Current vs. Voltage

25

30

35

40

20

 $T_J = 25^{\circ}C$ 

1E+02

က္ဆိ1E+01

1E+00

5

### **TYPICAL CHARACTERISTICS**




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source Voltage vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. I<sub>PEAK</sub> vs. Time in Avalanche

### **TYPICAL CHARACTERISTICS**





Figure 13. Thermal Characteristics


## **DEVICE ORDERING INFORMATION**

Device	Marking	Package	Shipping <sup>†</sup>
NTMTS0D6N04CLTXG	0D6N04CL	POWER 88 (Pb–Free)	3000 / Tape & Reel

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

### **PACKAGE DIMENSIONS**





FRONT VIEW

MILLIMETERS DIM MIN. NOM. MAX. 1.00 1.20 Α 1.10 Α1 0.00 0.05 b 0.90 1.00 1.10 0.43 0.53 0.63 b1 0.23 0.28 0.33 D 8.20 8.30 8.40 D1 7.90 8.00 8.10 D2 6.80 6.90 7.00 D3 6.90 7.00 7.10 8.30 8.40 8.50 E1 7.80 7.90 8.00 E2 5.24 5.34 5.44 0.35 0.45 E3 0.25 е 2.00 BSC e/2 1.00 BSC 2.70 BSC e1 e1/2 1.35 BSC 1.57 1.70 Κ 1.50 0.64 0.74 0.84 0.87 L1 0.67 0.77 0° 12° θ

PROTRUSIONS, OR GATE BURRS. 5. SEATING PLANE IS DEFINED BY THE TERMINALS.

"A1" IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.

ON Semiconductor and ware trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="https://www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify a

## **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative