ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

Power MOSFET

75 Amps, 60 Volts, N-Channel TO-220 and D²PAK

Designed for low voltage, high speed switching applications in power supplies, converters and power motor controls and bridge circuits.

Features

- These Devices are Pb-Free and are RoHS Compliant
- NTBV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable

Typical Applications

- Power Supplies
- Converters
- Power Motor Controls
- Bridge Circuits

MAXIMUM RATINGS (T.I = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
Drain-to-Source Voltage	V_{DSS}	60	Vdc
Drain-to-Gate Voltage (R_{GS} = 10 $M\Omega$)	V_{DGR}	60	Vdc
Gate-to-Source Voltage - Continuous - Non-Repetitive (t _p ≤10 ms)	V _{GS} V _{GS}	±20 ±30	Vdc
Drain Current - Continuous @ T_A = 25°C - Continuous @ T_A = 100°C - Single Pulse ($t_p \le 10 \mu s$)	I _D I _D	75 50 225	Adc Apk
Total Power Dissipation @ T _A = 25°C Derate above 25°C Total Power Dissipation @ T _A = 25°C	P _D	214 1.4 2.4	W W/°C W
Operating and Storage Temperature Range	T _J , T _{stg}	-55 to +175	°C
Single Pulse Drain-to-Source Avalanche Energy – Starting T_J = 25°C (V_{DD} = 50 Vdc, V_{GS} = 10 Vdc, L = 0.3 mH $I_{L(pk)}$ = 75 A, V_{DS} = 60 Vdc)	E _{AS}	844	mJ
Thermal Resistance - Junction-to-Case - Junction-to-Ambient	R _{θJC} R _{θJA}	0.7 62.5	°C/W
Maximum Lead Temperature for Soldering Purposes, 1/8" from case for 10 seconds	TL	260	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.




ON Semiconductor®


http://onsemi.com


75 AMPERES, 60 VOLTS


 $R_{DS(on)} = 9.5 \text{ m}\Omega$




MARKING DIAGRAMS







D²PAK CASE 418B STYLE 2



75N06

= Device Code = Assembly Location

WW

= Year

= Work Week

ORDERING INFORMATION


See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS (T₁ = 25°C unless otherwise noted)

Characteristic			Min	Тур	Max	Unit
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage (Note 1) $(V_{GS}=0\ Vdc,\ I_D=250\ \mu Adc)$ Temperature Coefficient (Positive)		V _{(BR)DSS}	60 -	71 73	- -	Vdc mV/°C
Zero Gate Voltage Drain Current $(V_{DS} = 60 \text{ Vdc}, V_{GS} = 0 \text{ Vdc})$ $(V_{DS} = 60 \text{ Vdc}, V_{GS} = 0 \text{ Vdc}, T_J = 150^{\circ}\text{C})$			- -	- -	10 100	μAdc
Gate-Body Leakage Current (V _{GS} = ±20 Vdc, V _{DS} = 0 Vdc)			-	-	±100	nAdc
ON CHARACTERISTICS (Note 1)						
Gate Threshold Voltage (Note 1) $ (V_{DS} = V_{GS}, I_D = 250 \ \mu Adc) $ Threshold Temperature Coefficient (Negative)			2.0	2.8 8.0	4.0 -	Vdc mV/°C
Static Drain-to-Source On-Resistance (Note 1) $(V_{GS} = 10 \text{ Vdc}, I_D = 37.5 \text{ Adc})$			-	8.2	9.5	mΩ
Static Drain-to-Source On-Voltage (Note 1) $(V_{GS} = 10 \text{ Vdc}, I_D = 75 \text{ Adc})$ $(V_{GS} = 10 \text{ Vdc}, I_D = 37.5 \text{ Adc}, T_J = 150^{\circ}\text{C})$			- -	0.72 0.63	0.86	Vdc
Forward Transconductance (Note 1) (V _{DS} = 15 Vdc, I _D = 37.5 Adc)			-	40.2	-	mhos
OYNAMIC CHARACTERISTICS						
Input Capacitance		C _{iss}	-	3220	4510	pF
Output Capacitance	(V _{DS} = 25 Vdc, V _{GS} = 0 Vdc, f = 1.0 MHz)	C _{oss}	-	1020	1430	
Transfer Capacitance	,	C _{rss}	-	234	330	
SWITCHING CHARACTERISTICS (N	ote 2)					
Turn-On Delay Time		t _{d(on)}	-	16	25	ns
Rise Time	(V _{DD} = 30 Vdc, I _D = 75 Adc,	t _r	-	112	155	
Turn-Off Delay Time	V_{GS} = 10 Vdc, R_G = 9.1 Ω) (Note 1)	t _{d(off)}	-	90	125	
Fall Time		t _f	-	100	140	
Gate Charge		Q _T	-	92	130	nC
	(V _{DS} = 48 Vdc, I _D = 75 Adc, V _{GS} = 10 Vdc) (Note 1)	Q ₁	-	14	-	
	VGS = 10 VGS/ (11010-1)	Q ₂	-	44	-	
OURCE-DRAIN DIODE CHARACT	ERISTICS					
Forward On-Voltage	(I _S = 75 Adc, V _{GS} = 0 Vdc) (Note 1) (I _S = 75 Adc, V _{GS} = 0 Vdc, T _J = 150°C)	V_{SD}	- -	1.0 0.9	1.1 -	Vdc
Reverse Recovery Time		t _{rr}	-	77	-	ns
	$(I_S = 75 \text{ Adc}, V_{GS} = 0 \text{ Vdc},$ $dI_S/dt = 100 \text{ A}/\mu\text{s}) \text{ (Note 1)}$	t _a	-	49	-	1
		t _b	-	28	-	1
Reverse Recovery Stored Charge		Q _{RR}	-	0.16	-	μС

Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2%.
 Switching characteristics are independent of operating junction temperatures.

160



 $V_{DS} \ge 10 \text{ V}$ 140 DRAIN CURRENT (AMPS) 120 100 80 60 40 $T_J = 25^{\circ}C$ ڡٞ 20 $T_J = 100^{\circ}C$ 0 2.5 3 3.5 4 4.5 5 5.5 6 V_{GS}, GATE-TO-SOURCE VOLTAGE (V)

Figure 1. On-Region Characteristics

Figure 2. Transfer Characteristics

Figure 4. On-Resistance vs. Drain Current and




Figure 3. On-Resistance vs. Gate-to-Source Voltage

Gate Voltage 10000 $I_D = 37.5 A$ $V_{GS} = 0 V$ = 150°C V_{GS} = 10 V IDSS, LEAKAGE (nA) 1000 $T_J = 125^{\circ}C$ $T_{.1} = 100^{\circ}C$ 100 10 -25 25 175 10 30 60 T_J, JUNCTION TEMPERATURE (°C) V_{DS}, DRAIN-TO-SOURCE VOLTAGE (V)

Figure 5. On–Resistance Variation with Temperature

R_{DS(on)}, DRAIN-TO-SOURCE RESISTANCE (NORMALIZED)

1.8

1.6

1.4

1.2

0.8

Figure 6. Drain-to-Source Leakage Current vs. Voltage




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source and Drain-to-Source Voltage vs. Total Charge




Figure 9. Resistive Switching Time Variations vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Avalanche Energy vs. Starting Junction Temperature




Figure 13. Thermal Response

ORDERING INFORMATION


Device	Package	Shipping [†]
NTP75N06G	TO-220 (Pb-Free)	50 Units/Rail
NTB75N06G	D ² PAK (Pb-Free)	50 Units/Rail
NTB75N06T4G	D ² PAK (Pb-Free)	800 Tape & Reel
NTBV75N06T4G*	D ² PAK (Pb-Free)	800 Tape & Reel


[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

^{*}NTBV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable.

PACKAGE DIMENSIONS

TO-220 CASE 221A-09 ISSUE AG






- NOTES:
 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.
 3. DIMENSION Z DEFINES A ZONE WHERE ALL BODY AND LEAD IRREGULARITIES ARE ALLOWED.

	INC	INCHES MILLIMETERS		IETERS
DIM	MIN	MAX	MIN	MAX
Α	0.570	0.620	14.48	15.75
В	0.380	0.405	9.66	10.28
С	0.160	0.190	4.07	4.82
D	0.025	0.036	0.64	0.91
F	0.142	0.161	3.61	4.09
G	0.095	0.105	2.42	2.66
Н	0.110	0.161	2.80	4.10
J	0.014	0.025	0.36	0.64
K	0.500	0.562	12.70	14.27
L	0.045	0.060	1.15	1.52
N	0.190	0.210	4.83	5.33
Q	0.100	0.120	2.54	3.04
R	0.080	0.110	2.04	2.79
S	0.045	0.055	1.15	1.39
T	0.235	0.255	5.97	6.47
U	0.000	0.050	0.00	1.27
٧	0.045		1.15	
Z		0.080		2.04

STYLE 5:
PIN 1. GATE
2. DRAIN
3. SOURCE
4. DRAIN

PACKAGE DIMENSIONS


D²PAK CASE 418B-04 **ISSUE K**




- NOTES:
 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.
 3. 418B-01 THRU 418B-03 OBSOLETE, NEW STANDARD 418B-04.

	INCHES		MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	0.340	0.380	8.64	9.65	
В	0.380	0.405	9.65	10.29	
С	0.160	0.190	4.06	4.83	
D	0.020	0.035	0.51	0.89	
E	0.045	0.055	1.14	1.40	
F	0.310	0.350	7.87	8.89	
G	0.100 BSC		2.54 BSC		
Н	0.080	0.110	2.03	2.79	
J	0.018	0.025	0.46	0.64	
K	0.090	0.110	2.29	2.79	
L	0.052	0.072	1.32	1.83	
М	0.280	0.320	7.11	8.13	
N	0.197 REF		5.00 REF		
Р	0.079 REF		2.00 REF		
R	0.039	REF	0.99 REF		
S	0.575	0.625	14.60	15.88	

STYLE 2: PIN 1. GATE 2. DRAIN 3. SOURCE 4. DRAIN



SOLDERING FOOTPRINT*



DIMENSIONS: MILLIMETERS

^{*}For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and un are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada

Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative