onsemi

MOSFET – Power, Single N-Channel 100 V, 26 mΩ, 28 A

NVMFS027N10MCL

Features

- Small Footprint (5x6 mm) for Compact Design
- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- AEC-Q101 Qualified and PPAP Capable
- NVMFWS027N10MCL Wettable Flank Products
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V _{DSS}	100	V
Gate-to-Source Voltage			V _{GS}	±20	V
Continuous Drain	Steady	$T_C = 25^{\circ}C$	۱ _D	28	А
Current $R_{\theta JC}$ (Notes 1, 3)		T _C = 100°C		20	
Power Dissipation	State	$T_C = 25^{\circ}C$	P _D	46	W
$R_{\theta JC}$ (Note 1)		$T_{C} = 100^{\circ}C$		23	
Continuous Drain		$T_A = 25^{\circ}C$	۱ _D	7.9	А
Current R _{θJA} (Notes 1, 2, 3)	Steady	T _A = 100°C		5.6	
Power Dissipation	State	T _A = 25°C	PD	3.5	W
$R_{\theta JA}$ (Notes 1, 2)		T _A = 100°C		1.8	
Pulsed Drain Current	T _A = 25	°C, t _p = 10 μs	I _{DM}	137	А
Operating Junction and Storage Temperature Range			T _J , T _{stg}	–55 to +175	°C
Source Current (Body Diode)			I _S	35	А
Single Pulse Drain–to–Source Avalanche Energy ($I_{L(pk)} = 1.3 A$)			E _{AS}	414	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			ΤL	260	°C

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS


Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State (Note 1)	$R_{\theta JC}$	3.3	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	42.4	


1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

2. Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.

Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
100 V	26 mΩ @ 10 V	28 A
100 V	35 mΩ @ 4.5 V	20 A





ORDERING INFORMATION


See detailed ordering, marking and shipping information on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V_{GS} = 0 V, I _D = 250 μ A		100			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} / T _J				53		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 V,$	T _J = 25 °C			1.0	μΑ
		V _{DS} = 100 V	T _J = 125°C			100	
Gate-to-Source Leakage Current	I _{GSS}	V _{DS} = 0 V, V _{GS} = 20 V				100	nA
ON CHARACTERISTICS							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D =$	= 38 μA	1		3	V
Threshold Temperature Coefficient	V _{GS(TH)} /T _J				-6		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 7 A		21	26	┼──┤
		V _{GS} = 4.5 V	I _D = 5 A		28	35	mΩ
Forward Transconductance	9 _{FS}	V _{DS} = 10 V, I _D = 7 A			25		S
CHARGES, CAPACITANCES & GATE RESISTANCE							
Input Capacitance	C _{ISS}				800		
Output Capacitance	C _{OSS}	V_{GS} = 0 V, f = 1 MHz, V_{DS} = 50 V			300		pF
Reverse Transfer Capacitance	C _{RSS}				4		
Gate Resistance	R _G				0.41		Ω
Total Gate Charge	Q _{G(TOT)}	V_{GS} = 4.5 V, V_{DS} = 50 V; I_D = 7 A			5.5		nC
Total Gate Charge	Q _{G(TOT)}	V_{GS} = 10 V, V_{DS} = 50 V; I_{D} = 7 A			11.5		nC
Threshold Gate Charge	Q _{G(TH)}	V _{GS} = 10 V, V _{DS} = 50 V; I _D = 7 A			1.3		
Gate-to-Source Charge	Q _{GS}				2.1		nC
Gate-to-Drain Charge	Q _{GD}				1.2		
Plateau Voltage	V _{GP}				2.5		V
Output Charge	Q _{OSS}	V _{GS} = 0 V, V _{DS} = 50 V			87		nC
SWITCHING CHARACTERISTICS (Note 4)							
Turn-On Delay Time	t _{d(ON)}	V _{GS} = 10 V, V _{DS} = 50 V, I _D = 7 A, R _G = 6.0 Ω			7.4		
Rise Time	t _r				2		ns
Turn-Off Delay Time	t _{d(OFF)}				19		
Fall Time	t _f				2.9		
DRAIN-SOURCE DIODE CHARACTERISTI	cs						
Forward Diode Voltage	V _{SD}	$V_{SD} = V_{GS} = 0 \text{ V, } \text{ I}_{S} = 7 \text{ A, } \text{ T}_{J} = 25^{\circ}\text{C}$ $V_{GS} = 0 \text{ V, } \text{ I}_{S} = 7 \text{ A, } \text{ T}_{J} = 125^{\circ}\text{C}$			0.84	1.3	V
					0.73		
Reverse Recovery Time	t _{RR}	V _{GS} = 0 V, dI _S /dt = 100 A/µs, I _S = 3 A			28		ns
Reverse Recovery Charge	Q _{RR}				17		nC
Charge Time	ta				13.9		ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 4. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS





Figure 13. Thermal Response

DEVICE ORDERING INFORMATION

Device	Marking	Package	Shipping [†]
NVMFS027N10MCLT1G	027L10	DFN5 (Pb–Free)	1500 / Tape & Reel
NVMFWS027N10MCLT1G	027W10	DFN5 (Wettable Flank, Pb-Free)	1500 / Tape & Reel


+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS



www.onsemi.com 6

PACKAGE DIMENSIONS



onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

onsemi Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 **Europe, Middle East and Africa Technical Support:** Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative