

# MOSFET – Power, N-Channel, Automotive, SUPERFET® III, FRFET®

650 V, 40 mΩ

## NVCR8LS040N65S3FA



### Features

- Typical  $R_{DS(on)} = 33.8 \text{ m}\Omega$  at  $V_{GS} = 10 \text{ V}$
- Typical  $Q_{g(tot)} = 153 \text{ nC}$  at  $V_{GS} = 10 \text{ V}$
- AEC-Q101 Qualified
- RoHS Compliant

### DIMENSION ( $\mu\text{m}$ )

Die Size	9510 x 6170
Die Size (Sawn)	9490 $\pm$ 30 x 6150 $\pm$ 30
Source Attach Area	(8835 x 2626.5) x 2
Gate Attach Area	406 x 618
Die Thickness	203.2 $\pm$ 25.4

Gate and Source : AlSiCu  
 Drain : Ti-NiV-Ag (back side of die)  
 Passivation : SiN  
 Wafer Diameter : 8 inch  
 Wafer sawn on UV Tape  
 Bad dice identified in Inking  
 Gross Die Count : 419

### ORDERING INFORMATION

Device	Package
NVCR8LS040N65S3FA	Wafer Sawn on Foil

### RECOMMENDED STORAGE CONDITIONS

Temperature	22 to 28°C
RH	40% to 66%

### ELECTRICAL CHARACTERISTICS

The Chip is 100% Probed to Meet the Conditions and Limits Specified at  $T_J = 25^\circ\text{C}$

Symbol	Parameter	Condition	Min.	Typ.	Max.	Unit
$BV_{DSS}$	Drain to Source Breakdown Voltage	$I_D = 1 \text{ mA}$ , $V_{GS} = 0 \text{ V}$	650	–	–	V
$I_{DSS}$	Drain to Source Leakage Current	$V_{DS} = 650 \text{ V}$ , $V_{GS} = 0 \text{ V}$	–	–	10	$\mu\text{A}$
$I_{GSS}$	Gate to Source Leakage Current	$V_{GS} = \pm 30 \text{ V}$ , $V_{DS} = 0 \text{ V}$	–	–	$\pm 100$	nA
$V_{GS(th)}$	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}$ , $I_D = 2.1 \text{ mA}$	3.0	–	5.0	V
* $R_{DS(on)}$	Bare Die Drain to Source On Resistance	$I_D = 32.5 \text{ A}$ , $V_{GS} = 10 \text{ V}$	–	33.8	40	mΩ
$V_{SD}$	Drain to Source Diode Forward Voltage	$V_{GS} = 0 \text{ V}$ , $I_{SD} = 32.5 \text{ V}$			1.2	V

\*Accurate RDS(on) test at die level is not feasible for this thin die as limited by the test contact precision attainable in a die form. The max RDS(on) specification is defined from the historical performance of the die in package but is not guaranteed by test in production. The die RDS(on) performance depends on the Source wire/ribbon bonding layout.

# NVCR8LS040N65S3FA

## ABSOLUTE MAXIMUM RATINGS

in Reference to the NVHL040N65S3F electrical data in TO-247 (  $T_J = 25^\circ\text{C}$  unless otherwise noted)

Symbol	Parameter	Ratings	Unit
$V_{DSS}$	Drain to Source Voltage	650	V
$V_{GS}$	Gate to Source Voltage	DC	$\pm 30$
		AC ( $f > 1$ Hz)	$\pm 30$
$I_D$	Continuous Drain Current	$T_C = 25^\circ\text{C}$	65
		$T_C = 100^\circ\text{C}$	45
$I_{DM}$	Pulsed Drain Current	Pulsed (Note 1)	162.5
$E_{AS}$	Single Pulse Avalanche Energy (Note 2)	1009	mJ
$E_{AR}$	Repetitive Avalanche (Note 1)	4.46	mJ
dv/dt	MOSFET dv/dt	100	V/ns
	Peak Diode Recovery dv/dt (Note 3)	50	V/ns
$P_D$	Power Dissipation $R_{\theta JC}$	$T_C = 25^\circ\text{C}$	446
$T_J, T_{STG}$	Operating and Storage Temperature	-55 to +150	$^\circ\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Repetitive rating: pulse-width limited by maximum junction temperature.
2.  $I_{AS} = 9$  A,  $R_G = 25 \Omega$ , Starting  $T_J = 25^\circ\text{C}$ .
3.  $I_{SD} < 32.5$  A,  $di/dt \leq 200$  A/ms,  $V_{DD} \leq BVDSS$ , starting  $T_J = 25^\circ\text{C}$

## THERMAL CHARACTERISTICS

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case, Max	0.28	$^\circ\text{C}/\text{W}$
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient, Max	40	$^\circ\text{C}/\text{W}$

# NVCR8LS040N65S3FA

## ELECTRICAL CHARACTERISTICS

in Reference to the NVHL040N65S3F electrical data in TO-247-3LD ( $T_J = 25^\circ\text{C}$  unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
--------	-----------	------------	------	------	------	------

### OFF CHARACTERISTICS

$BV_{DSS}$	Drain to Source Breakdown Voltage	$I_D = 1 \text{ mA}, V_{GS} = 0 \text{ V}$	650	–	–	V
$I_{DSS}$	Drain to Source Leakage Current	$V_{DS} = 650 \text{ V}, V_{GS} = 0 \text{ V}, T_J = 25^\circ\text{C}$	–	–	10	$\mu\text{A}$
		$V_{DS} = 520 \text{ V}, V_{GS} = 0 \text{ V}, T_J = 125^\circ\text{C}$	–	103	–	$\mu\text{A}$
$I_{GSS}$	Gate to Source Leakage Current	$V_{GS} = \pm 30 \text{ V}$	–	–	$\pm 100$	nA

### ON CHARACTERISTICS

$V_{GS(th)}$	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 2.1 \text{ mA}$	3.0	–	5.0	V
$R_{DS(on)}$	Drain to Source On-Resistance	$V_{GS} = 10 \text{ V}, I_D = 32.5 \text{ A}$	–	33.8	40	m $\Omega$
$g_{FS}$	Forward Transconductance	$V_{DS} = 20 \text{ V}, I_D = 32.5 \text{ A}$	–	40	–	S

### DYNAMIC CHARACTERISTICS

$C_{iss}$	Input Capacitance	$V_{DS} = 400 \text{ V}, V_{GS} = 0 \text{ V},$ $f = 1 \text{ MHz}$	–	5875	–	pF
$C_{oss}$	Output Capacitance		–	140	–	pF
$C_{oss(eff.)}$	Effective Output Capacitance	$V_{DS} = 0 \text{ V to } 400 \text{ V}, V_{GS} = 0 \text{ V}$	–	1333	–	pF
$C_{oss(er.)}$	Energy Related Output Capacitance	$V_{DS} = 0 \text{ V to } 400 \text{ V}, V_{GS} = 0 \text{ V}$	–	241	–	pF
$Q_{g(ToT)}$	Total Gate Charge	$V_{GS} = 10 \text{ V}, V_{DS} = 400 \text{ V}, I_D = 32.5 \text{ A}$ (Note 4)	–	153	–	nC
$Q_{gs}$	Gate to Source Gate Charge		–	51	–	nC
$Q_{gd}$	Gate to Drain "Miller" Charge		–	61	–	nC
ESR	Equivalent Series Resistance	$f = 1 \text{ MHz}$	–	1.9	–	$\Omega$

### SWITCHING CHARACTERISTICS

$t_{d(on)}$	Turn-On Delay Time	$V_{DD} = 400 \text{ V}, I_D = 32.5 \text{ A}, V_{GS} = 10 \text{ V},$ $R_G = 2.2 \Omega$ (Note 4)	–	41	–	ns
$t_r$	Rise Time		–	53	–	ns
$t_{d(off)}$	Turn-Off Delay Time		–	96	–	ns
$t_f$	Fall Time		–	28	–	ns

### DRAIN – SOURCE DIODE CHARACTERISTICS

$I_S$	Maximum Continuous Drain to Source Diode Forward Current				65	A
$I_{SM}$	Maximum Pulsed Drain to Source Diode Forward Current				162.5	A
$V_{SD}$	Source to Drain Diode Voltage	$V_{GS} = 0 \text{ V}, I_{SD} = 32.5 \text{ A}, V_{GS} = 0 \text{ V}$	–	–	1.3	V
$t_{rr}$	Reverse Recovery Time	$V_{GS} = 0 \text{ V}, I_{SD} = 32.5 \text{ A},$ $di_{SD}/dt = 100 \text{ A}/\mu\text{s}$	–	159	–	ns
$Q_{rr}$	Reverse Recovery Charge		–	840	–	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Essentially independent of operating temperature typical characteristics.

# NVCR8LS040N65S3FA

## TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. On-Region Characteristics




Figure 3. Transfer Characteristics




Figure 4. On-Resistance Variation vs. Drain Current and Gate Voltage




Figure 5. Body Diode Forward Voltage Variation vs. Source Current and Temperature




Figure 6. Capacitance Characteristics

# NVCR8LS040N65S3FA

## TYPICAL CHARACTERISTICS




Figure 7. Gate Charge Characteristics




Figure 8. Breakdown Voltage Variation vs. Temperature




Figure 9. On-Resistance Variation vs. Temperature




Figure 10. Maximum Safe Operating Area




Figure 11. Maximum Drain Current vs. Case Temperature






Figure 12. E\_OSS vs. Drain-to-Source Voltage

# NVCR8LS040N65S3FA

## TYPICAL CHARACTERISTICS



**Figure 13. Normalized Power Dissipation vs. Case Temperature**



**Figure 14. Peak Current Capability**

# NVCR8LS040N65S3FA

## TYPICAL CHARACTERISTICS




Figure 15.  $R_{DS(ON)}$  vs. Gate Voltage




Figure 16. Normalized Gate Threshold Voltage vs. Temperature




Figure 17. Transient Thermal Response Curve

FRFET and SUPERFET are registered trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Email Requests to: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**onsemi Website:** [www.onsemi.com](http://www.onsemi.com)

### TECHNICAL SUPPORT

**North American Technical Support:**  
Voice Mail: 1 800-282-9855 Toll Free USA/Canada  
Phone: 011 421 33 790 2910

**Europe, Middle East and Africa Technical Support:**

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative