MOSFET – Power, Single, P-Channel -60 V, 16 mΩ, -61 A

Features

- Low R_{DS(on)} to Minimize Conduction Losses
- High Current Capability
- Avalanche Energy Specified
- AEC-Q101 Qualified
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Param	eter		Symbol	Value	Unit
Drain-to-Source Voltage	ce Voltage			-60	V
Gate-to-Source Voltage	∋-to-Source Voltage			±20	٧
Continuous Drain Cur-		T _C = 25°C	I _D	-61	Α
rent R _{θJC} (Note 1)	Steady	T _C = 100°C		-43	
Power Dissipation R _{θJC}	State	T _C = 25°C	P_{D}	118	W
(Note 1)		T _C = 100°C		59	
Continuous Drain Cur-		T _A = 25°C	I _D	-11	Α
rent R _{θJA} (Notes 1 & 2)	Steady State	T _A = 100°C		-8	
Power Dissipation R _{θJA}		T _A = 25°C	P_{D}	4.1	W
(Notes 1 & 2)		T _A = 100°C		2.1	
Pulsed Drain Current	$T_A = 25^{\circ}C, t_p = 10 \mu s$		I _{DM}	-419	Α
Current Limited by Package (Note 3)	T _A	= 25°C	I _{Dmaxpkg}	60	Α
Operating Junction and Storage Temperature $Source\ Current\ (Body\ Diode)$ $Single\ Pulse\ Drain-to-Source\ Avalanche$ $Energy\ (T_J=25^\circ\text{C},\ V_{DD}=50\ \text{V},\ V_{GS}=10\ \text{V},$ $I_{L(pk)}=40\ \text{A},\ L=0.3\ \text{mH},\ R_G=25\ \Omega)$			T _J , T _{stg}	-55 to 175	°C
			IS	-118	Α
			E _{AS}	240	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			TL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State (Drain)	$R_{\theta JC}$	1.3	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	37	


- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- 2. Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.
- Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.



ON Semiconductor®


www.onsemi.com

V _{(BR)DSS}	R _{DS(on)}	I _D	
-60 V	16 mΩ @ –10 V	-61 A	
	22 mΩ @ -4.5 V	-017	





MARKING DIAGRAMS & PIN ASSIGNMENT



Gate Source

A = Assembly Location*

Y = Year

WW = Work Week 5117L = Device Code

G = Pb-Free Package

* The Assembly Location Code (A) is front side optional. In cases where the Assembly Location is stamped in the package bottom (molding ejecter pin), the front side assembly code may be blank.

ORDERING INFORMATION

Device	Package	Shipping [†]				
NVD5117PLT4G	DPAK (Pb-Free)	2500 / Tape & Reel				
NVD5117PLT4G- VF01	DPAK (Pb-Free)	2500 / Tape & Reel				

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise noted)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS	•		•			•	•
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	$V_{GS} = 0 \text{ V}, I_D = -250 \mu\text{A}$		-60			V
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 \text{ V}.$ $T_{J} = 25^{\circ}\text{C}$				-1.0	μΑ
		$V_{GS} = 0 \text{ V}, V_{DS} = -60 \text{ V}$	T _J = 125°C			-100	1
Gate-to-Source Leakage Current	I _{GSS}	V _{DS} = 0 V, V _{GS}	S = ±20 V			±100	nA
ON CHARACTERISTICS (Note 4)							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_{D}$	= -250 μΑ	-1.5		-2.5	V
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = −10 V, I	_D = -29 A		12	16	mΩ
		$V_{GS} = -4.5 \text{ V},$	I _D = -29 A		16	22	1
Froward Transconductance	9 _{FS}	V _{DS} = −15 V, I	_D = -15 A		30		S
CHARGES AND CAPACITANCES							
Input Capacitance	C _{iss}	V _{GS} = 0 V, f =	1.0 MHz,		4800		pF
Output Capacitance	C _{oss}	$V_{DS} = -2$	25 V		480		1
Reverse Transfer Capacitance	C _{rss}				320		1
Total Gate Charge	Q _{G(TOT)}	$V_{DS} = -48 \text{ V}, \qquad V_{GS} = -4$			49		nC
		$I_{\rm D} = -29 {\rm A}^{2}$	V _{GS} = -10 V		85		1
Threshold Gate Charge	Q _{G(TH)}	$V_{GS} = -4.5 \text{ V}, V_{DS} = -48 \text{ V},$ $I_{D} = -29 \text{ A}$			3		1
Gate-to-Source Charge	Q_{GS}				13		1
Gate-to-Drain Charge	Q_{GD}				28		1
Plateau Voltage	V_{GP}				3.2		V
SWITCHING CHARACTERISTICS (No	otes 4)				•	•	
Turn-On Delay Time	t _{d(on)}				22		ns
Rise Time	t _r	V _{GS} = -4.5 V, V	ns = -48 V.		195		1
Turn-Off Delay Time	t _{d(off)}	$I_{D} = -29 \text{ A}, R_{G} = 2.5 \Omega$			50		1
Fall Time	t _f				132		1
DRAIN-SOURCE DIODE CHARACTERISTICS							
Forward Diode Voltage	V_{SD}	$V_{GS} = 0 V$,	T _J = 25°C		-0.86	-1.0	V
		I _S = -29 A	T _J = 125°C		-0.74		
Reverse Recovery Time	t _{RR}	$V_{GS} = 0 \text{ V, } dl_{S}/dt = 100 \text{ A/}\mu\text{s,}$ $l_{s} = -29 \text{ A}$			36		ns
Charge Time	t _a				19		1
Discharge Time	t _b				17		1
Reverse Recovery Charge	Q _{RR}				44		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Pulse Test: Pulse Width \leq 300 µs, Duty Cycle \leq 2%.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation

Figure 8. Gate-to-Source vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance

Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased **Safe Operating Area**

Figure 12. Maximum Avalanche Energy vs. **Starting Junction Temperature**

TYPICAL CHARACTERISTICS





Figure 13. Thermal Response





DOCUMENT NUMBER:	98AON10527D	Electronic versions are uncontrolled except when accessed directly from the Document Rep Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	DPAK (SINGLE GAUGE)		PAGE 1 OF 1

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales