# **ON Semiconductor**

# Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

# MOSFET – Power, Single N-Channel 40 V, 3.4 m $\Omega$ , 107 A

# **NVTYS003N04CL**

#### **Features**

- Small Footprint (3.3 x 3.3 mm) for Compact Design
- Low R<sub>DS(on)</sub> to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

#### **MAXIMUM RATINGS** (T<sub>J</sub> = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			$V_{DSS}$	40	٧
Gate-to-Source Voltage			V <sub>GS</sub>	±20	V
Continuous Drain		T <sub>C</sub> = 25°C	I <sub>D</sub>	106	Α
Current R <sub>θJC</sub> (Notes 1, 3)	Steady	T <sub>C</sub> = 100°C		75	
Power Dissipation	State	T <sub>C</sub> = 25°C	$P_{D}$	69	W
R <sub>θJC</sub> (Note 1)		T <sub>C</sub> = 100°C		34	
Continuous Drain		T <sub>A</sub> = 25°C	I <sub>D</sub>	23	Α
Current R <sub>0JA</sub> (Notes 1, 2, 3)	Steady	T <sub>A</sub> = 100°C	1	16	
Power Dissipation	State	T <sub>A</sub> = 25°C	P <sub>D</sub>	3.2	W
R <sub>θJA</sub> (Notes 1, 2)		T <sub>A</sub> = 100°C	1	1.6	
Pulsed Drain Current	$T_A = 25^{\circ}C, t_p = 10 \ \mu s$		I <sub>DM</sub>	498	Α
Operating Junction and Storage Temperature Range			T <sub>J</sub> , T <sub>stg</sub>	-55 to +175	°C
Source Current (Body Diode)			Is	57.1	Α
Single Pulse Drain-to-Source Avalanche Energy (I <sub>L(pk)</sub> = 7.4 A)			E <sub>AS</sub>	179	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)		TL	260	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

#### THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State	$R_{\theta JC}$	2.2	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	46.7	


- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- 2. Surface-mounted on FR4 board using a 650 mm<sup>2</sup>, 2 oz. Cu pad.
- 3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.



### ON Semiconductor®

#### www.onsemi.com

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX
40 V	3.4 m $\Omega$ @ 10 V	107.4
40 V	5.3 mΩ @ 4.5 V	107 A



**N-CHANNEL MOSFET** 



LFPAK8 3.3x3.3 CASE 760AD

#### **MARKING DIAGRAM**

003N 04CL AWLYW

003N04CL = Specific Device Code

A = Assembly Location

WL = Wafer Lot Y = Year W = Work Week

(Note: Microdot may be in either location)

## **ORDERING INFORMATION**

See detailed ordering, marking and shipping information on page 5 of this data sheet.

# **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub> = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS	•				•	•	
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		40			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> /				23		mV/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{GS} = 0 V$	T <sub>J</sub> = 25 °C			10	
		V <sub>DS</sub> = 40 V	T <sub>J</sub> = 125°C			μA 250	
Gate-to-Source Leakage Current	I <sub>GSS</sub>	$V_{DS} = 0 \text{ V}, V_{GS}$	<sub>S</sub> = 20 V			100	nA
ON CHARACTERISTICS (Note 4)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}, I_D$	= 60 μΑ	1.2		2.0	V
Threshold Temperature Coefficient	V <sub>GS(TH)</sub> /T <sub>J</sub>				-5.7		mV/°C
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V	I <sub>D</sub> = 40 A		2.9	3.4	
		V <sub>GS</sub> = 4.5 V	I <sub>D</sub> = 40 A		4.3	5.3	mΩ
Forward Transconductance	9FS	$V_{DS} = 5 \text{ V}, I_{D}$	= 40 A		120		S
CHARGES AND CAPACITANCES							
Input Capacitance	C <sub>ISS</sub>	V <sub>GS</sub> = 0 V, f = 1 MHz, V <sub>DS</sub> = 25 V			2240		
Output Capacitance	C <sub>OSS</sub>				800		pF
Reverse Transfer Capacitance	C <sub>RSS</sub>				21		
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 32 V; I <sub>D</sub> = 40 A			36		
Total Gate Charge	$Q_{G(TOT)}$				17		
Threshold Gate Charge	Q <sub>G(TH)</sub>	$V_{GS} = 4.5 \text{ V}, V_{DS} = 32 \text{ V}; I_D = 40 \text{ A}$			3.5		nC
Gate-to-Source Charge	$Q_{GS}$				6.5		
Gate-to-Drain Charge	$Q_{GD}$				5.5		
Plateau Voltage	$V_{GP}$				3.1		V
SWITCHING CHARACTERISTICS (Note 5)	)						
Turn-On Delay Time	t <sub>d(ON)</sub>				17		
Rise Time	t <sub>r</sub>	V <sub>GS</sub> = 4.5 V, V <sub>D</sub>	<sub>S</sub> = 32 V,		13		- ns
Turn-Off Delay Time	t <sub>d(OFF)</sub>	$V_{GS} = 4.5 \text{ V}, V_{D}$ $I_{D} = 40 \text{ A}, R_{G}$	= 2.5 Ω		24		
Fall Time	t <sub>f</sub>				9		1
DRAIN-SOURCE DIODE CHARACTERIST	rics						
Forward Diode Voltage	V <sub>SD</sub>	V <sub>GS</sub> = 0 V,	T <sub>J</sub> = 25°C		0.84	1.2	.,
		I <sub>S</sub> = 40 A T <sub>J</sub> = 125°C			0.72		V
Reverse Recovery Time	t <sub>RR</sub>	$V_{GS} = 0 \text{ V, } dI_{S}/dt = 100 \text{ A/}\mu\text{s,}$ $I_{S} = 40 \text{ A}$			34		
Charge Time	t <sub>a</sub>				15		ns
Discharge Time	t <sub>b</sub>				19		
Reverse Recovery Charge	Q <sub>RR</sub>				14		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Pulse Test: pulse width  $\leq 300~\mu s$ , duty cycle  $\leq 2\%$ .

5. Switching characteristics are independent of operating junction temperatures.

### **TYPICAL CHARACTERISTICS**




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate-to-Source Voltage




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On–Resistance Variation with Temperature





Figure 6. Drain-to-Source Leakage Current vs. Voltage

#### **TYPICAL CHARACTERISTICS**






Figure 9. Resistive Switching Time Variation vs. Gate Resistance





Figure 11. Safe Operating Area



 $V_{DS} = 32 V$ 

35

40

 $T_J = 25^{\circ}C$ 

I<sub>D</sub> = 40 A

30




Figure 10. Diode Forward Voltage vs. Current




Figure 12. I<sub>PEAK</sub> vs. Time in Avalanche

### **TYPICAL CHARACTERISTICS**




Figure 13. Thermal Characteristics

#### **DEVICE ORDERING INFORMATION**


Device	Marking	Package	Shipping <sup>†</sup>
NVTYS003N04CLTWG	003N 04CL	LFPAK33 (Pb-Free)	3000 / Tape & Reel


<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


#### PACKAGE DIMENSIONS

# LFPAK8 3.3x3.3, 0.65P


CASE 760AD **ISSUE A** 








**BOTTOM VIEW** 



DETAIL 'A'



#### LAND PATTERN RECOMMENDATION

\*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

#### NOTES:

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- CONTROLLING DIMENSION: MILLIMETERS
- 3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH. PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS OR BURRS SHALL NOT EXCEED 0.150mm PER SIDE.
- 4. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
- 5. DATUMS A AND B ARE DETERMINED AT DATUM PLANE H.
- 6. OPTIONAL MOLD FEATURE.

MILLIMETERS			
MIN.	NOM.	MAX.	
0.95	1.05	1.15	
0.00	0.05	0.10	
0.95	1.00	1.05	
	0.15 REI	F	
0.27	0.32	0.37	
0.12	0.17	0.22	
0.12	0.17	0.22	
2.50	2.60	2.70	
1.82	1.92	2.02	
1.46	1.56	1.66	
0.20	0.25	0.30	
3.20	3.30	3.40	
3.00	3.10	3.20	
2.15	2.25	2.35	
0.65 BSC			
3.20	3.30	3.40	
0.25	0.37	0.50	
0.48	0.58	0.68	
0.35	0.45	0.55	
0.45	0.50	0.55	
0°	4°	8°	
	MIN. 0.95 0.00 0.95 0.27 0.12 0.12 2.50 1.82 1.46 0.20 3.20 3.00 2.15 0.25 0.48 0.35 0.45	MIN. NOM. 0.95 1.05 0.00 0.05 0.95 1.00 0.15 RE 0.27 0.32 0.12 0.17 0.12 0.17 2.50 2.60 1.82 1.92 1.46 1.56 0.20 0.25 3.20 3.30 3.00 3.10 2.15 2.25 0.65 BSC 3.20 3.30 0.25 0.37 0.48 0.58 0.45 0.45 0.50	

ON Semiconductor and 🕠 are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability. arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative