ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

MOSFET - Power, Single

N-Channel

60 V, 9.8 mΩ, 51 A

NVTYS010N06CL

Features

- Small Footprint (3.3 x 3.3 mm) for Compact Design
- Low R_{DS(on)} to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V_{DSS}	60	V
Gate-to-Source Voltage	9		V _{GS}	±20	V
Continuous Drain	Steady	T _C = 25°C	I _D	51	Α
Current R _{θJC} (Notes 1, 2, 3, 4)		T _C = 100°C		36	
Power Dissipation	State	T _C = 25°C	P_{D}	47	W
R _{θJC} (Notes 1, 2, 3)		T _C = 100°C		23	
Continuous Drain		T _A = 25°C	I _D	13	Α
Current R _{0JA} (Notes 1, 3, 4)	Steady State	T _A = 100°C		9	
Power Dissipation		T _A = 25°C	P_{D}	3.1	W
R _{θJA} (Notes 1, 3)		T _A = 100°C		1.6	
Pulsed Drain Current	$T_A = 25^{\circ}C, t_p = 10 \mu s$		I _{DM}	217	Α
Operating Junction and Storage Temperature Range			T _J , T _{stg}	-55 to +175	°C
Source Current (Body Diode)			I _S	38.7	Α
Single Pulse Drain-to-Source Avalanche Energy (I _{L(pk)} = 2.3 A)			E _{AS}	80	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			TL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS (Note 1)

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State (Note 3)	$R_{ heta JC}$	3.2	°C/W
Junction-to-Ambient - Steady State (Note 3)	$R_{\theta JA}$	48	

- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- 2. Psi (Ψ) is used as required per JESD51–12 for packages in which substantially less than 100% of the heat flows to single case surface.
- 3. Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.
- Continuous DC current rating. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.




ON Semiconductor®

www.onsemi.com

V _{(BR)DSS}	R _{DS(on)} MAX	I _D MAX	
60 V	9.8 mΩ @ 10 V	51 A	
	15 mΩ @ 4.5 V	317	

N-Channel





3.3x3.3

CASE 760AD

MARKING DIAGRAM

010N 06CL AWLYW

010N06CL = Specific Device Code

A = Assembly Location

WL = Wafer Lot Y = Year W = Work Week

(Note: Microdot may be in either location)

ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS	<u> </u>						•
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = 250 μA		60			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /				26		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 V$	T _J = 25°C			10	μΑ
		V _{DS} = 60 V	T _J = 125°C			250	1
Gate-to-Source Leakage Current	I _{GSS}	V _{DS} = 0 V, V _{GS} = 20 V				100	nA
ON CHARACTERISTICS (Note 5)					-		
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D = 35 \mu A$		1.2		2.0	V
Threshold Temperature Coefficient	V _{GS(TH)} /T _J				-5.48		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 25 A		8.1	9.8	mΩ
		V _{GS} = 4.5 V	I _D = 25 A		12	15	1
Forward Transconductance	9FS	$V_{DS} = 5 \text{ V}, I_{D}$	= 25 A		55		S
CHARGES AND CAPACITANCES					-		
Input Capacitance	C _{ISS}	$V_{GS} = 0 \text{ V, f} = 1 \text{ MHz, } V_{DS} = 25 \text{ V}$ $V_{GS} = 4.5 \text{ V, } V_{DS} = 48 \text{ V; } I_{D} = 25 \text{ A}$			910		pF
Output Capacitance	C _{OSS}				500		1
Reverse Transfer Capacitance	C _{RSS}				9		1
Total Gate Charge	Q _{G(TOT)}				6		nC
Total Gate Charge	Q _{G(TOT)}	V _{GS} = 10 V, V _{DS} = 48 V; I _D = 25 A			13		nC
Threshold Gate Charge	Q _{G(TH)}	V _{GS} = 10 V, V _{DS} = 48 V; I _D = 25 A			1.4		nC
Gate-to-Source Charge	Q _{GS}				2.5		1
Gate-to-Drain Charge	Q_GD				1.5		1
Plateau Voltage	V _{GP}				2.8		V
SWITCHING CHARACTERISTICS (Note 6)					-		
Turn-On Delay Time	t _{d(ON)}				7.3		ns
Rise Time	t _r	V _{GS} = 10 V, V _{DS}	s = 48 V,		2.3		1
Turn-Off Delay Time	t _{d(OFF)}	$I_D = 25 \text{ A}, R_G = 2.5 \Omega$			17		1
Fall Time	t _f				2.5		1
DRAIN-SOURCE DIODE CHARACTERIST	TICS						
Forward Diode Voltage	V_{SD}	V _{GS} = 0 V,	T _J = 25°C		0.9	1.2	V
		I _S = 25 A	T _J = 125°C		0.8		1
Reverse Recovery Time	t _{RR}	V_{GS} = 0 V, dls/dt = 100 A/ μ s, I_{S} = 25 A			29		ns
Charge Time	t _a				13		
Discharge Time	t _b				16		
Reverse Recovery Charge	Q _{RR}				12		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.


5. Pulse Test: pulse width $\leq 300~\mu s$, duty cycle $\leq 2\%$.

6. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS




TYPICAL CHARACTERISTICS



10 V_{GS}, GATE-TO-SOURCE VOLTAGE (V) Q_T 9 8 6 5 Q_{gd} $\mathbf{Q}_{\underline{gs}}$ 3 $T_J = 25^{\circ}C$ V_{DS} = 48 V I_D = 25 A 8 10 12 Qq, TOTAL GATE CHARGE (nC)

Figure 7. Capacitance Variation

Figure 8. Gate-to-Source vs. Total Charge







Figure 9. Resistive Switching Time Variation vs. Gate Resistance

Figure 10. Diode Forward Voltage vs. Current






Figure 11. Maximum Rated Forward Biased Safe Operating Area

Figure 12. Maximum Drain Current vs. Time in Avalanche

TYPICAL CHARACTERISTICS




Figure 13. Thermal Characteristics

DEVICE ORDERING INFORMATION


Device	Marking	Package	Shipping [†]
NVTYS010N06CLTWG	010N 06CL	LFPAK33 (Pb-Free)	3000 / Tape & Reel


[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


PACKAGE DIMENSIONS

LFPAK8 3.3x3.3, 0.65P


CASE 760AD ISSUE E








BOTTOM VIEW



DETAIL 'A' SCALE: 2:1



LAND PATTERN RECOMMENDATION

*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

NOTES:

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- 2. CONTROLLING DIMENSION: MILLIMETERS
- 3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS OR BURRS SHALL NOT EXCEED 0,150mm PER SIDE,
- 4. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
- 5. DATUMS A AND B ARE DETERMINED AT DATUM PLANE H.
- 6. OPTIONAL MOLD FEATURE.

DIM	MILLIMETERS				
5,	MIN.	NOM.	MAX.		
Α	0.95	1.05	1.15		
A1	0.00	0.05	0.10		
A2	0.95	1.00	1.05		
A3		0.15 REI	F		
b	0.27	0.32	0.37		
С	0.12	0.17	0.22		
c2	0.12	0.17	0.22		
D1	2.50	2.60	2.70		
D2	1.82	1.92	2.02		
D3	1.46	1.56	1.66		
D4	0.20	0.25	0.30		
Е	3.20	3.30	3.40		
E1	3.00	3.10	3.20		
E2	2.15	2.25	2.35		
е	0.65 BSC				
I	3.20	3.30	3.40		
L	0.25	0.37	0.50		
L1	0.48	0.58	0.68		
L2	0.35	0.45	0.55		
Q	0.45	0.50	0.55		
θ	0°	4°	8°		
0	U	-			

ON Semiconductor and ware trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, Buyer shall indemnify

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative