

750 V, 200 A Extremefast Diode Die



ON Semiconductor®

www.onsemi.com

PCRKA20075F8

Features

- AEC-Q101 Rev. D Qualified for Enhanced Reliability
- Maximum Junction Temperature 175°C
- Extremefast Technology Generation 2 with Improved Soft Recovery
- Low Forward Voltage: $V_F = 1.7\text{ V (Typ.) @ } I_F = 200\text{ A}$

Applications

- Automotive Traction Modules
- General Power Modules

$V_{RRM} = 750\text{V}$
 $I_F = \text{Limited by } T_{j(\text{max})}$

MECHANICAL PARAMETERS

Parameter	Mils	μm
Die Size	394 x 197	10,000 x 5,000
Anode Pad Size	346 x 149	8,776 x 3,776
Scribe Lane Width	3.14	80
Die Thickness	3.62	92
Top Metal	6 μm AlSiCu	
Back Metal	1.4 μm Ti/NiV/Ag	
Topside Passivation	Silicon Nitride plus Polyimide	
Wafer Diameter	200 mm	
Max Possible Die Per Wafer	467	
Recommended Storage Environment	In original container, in dry nitrogen, < 3 months at an ambient temperature of 23°C	

DIODE DIE



DIE OUTLINE



ORDERING INFORMATION

Device	Inking?	Shipping
PCRKA20075F8	Yes	Sawn Wafer on Tape

PCRKA20075F8

ABSOLUTE MAXIMUM RATINGS ($T_{VJ} = 25^{\circ}\text{C}$ Unless Otherwise Noted)

Parameter	Symbol	Ratings	Unit
Repetitive Peak Reverse Voltage	V_{RRM}	750	V
DC Forward Current, limited by T_{VJ} max	I_F	(Note 1)	A
Pulsed Forward Current, t_p limited by T_{VJ} max (Note 2)	I_{FM}	600	A
Operating Junction Temperature	T_{VJ}	-40 to +175	$^{\circ}\text{C}$
Storage Temperature Range	T_{stg}	+18 to +28	$^{\circ}\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Depends on the thermal properties of assembly.
2. Not subject to production test – verified by design/characterization.

ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}\text{C}$ Unless Otherwise Noted)

Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Unit
-----------	--------	-----------------	------	------	------	------

STATIC CHARACTERISTICS (Tested on Wafers)

Breakdown Voltage	V_{BR}	$I_R = 1\text{ mA}$	750	–	–	V
Reverse Leakage Current	I_R	$V_R = 750\text{ V}$	–	–	30	μA
Forward Voltage	V_F	$I_F = 200\text{ A}$	1.4	1.7	1.95	V

ELECTRICAL CHARACTERISTICS (Not Subjected to Production Test – Verified by Design/Characterization)

Breakdown Voltage	V_{BR}	$I_R = 1\text{ mA}$	$T_{VJ} = -40^{\circ}\text{C}$	700	800	–	V
Forward Voltage	V_F	$I_F = 200\text{ A}$	$T_{VJ} = 25^{\circ}\text{C}$	–	1.7	–	V
			$T_{VJ} = 150^{\circ}\text{C}$	–	1.72	–	V
			$T_{VJ} = 175^{\circ}\text{C}$	–	1.7	–	V
Reverse Recovery Charge	Q_{rr}	$I_F = 200\text{ A}$ $V_R = 400\text{ V}$, $dI_F/dt = 500\text{ A}/\mu\text{s}$, $T_{VJ} = 25^{\circ}\text{C}$		–	2.49	–	μC
Reverse Recovery Current	I_{rr}			–	23	–	A
Reverse Recover Time	T_{rr}			–	220	–	nS
Reverse Recovery Charge	Q_{rr}	$I_F = 200\text{ A}$ $V_R = 400\text{ V}$, $dI_F/dt = 500\text{ A}/\mu\text{s}$, $T_{VJ} = 150^{\circ}\text{C}$		–	9.6	–	μC
Reverse Recovery Current	I_{rr}			–	46	–	A
Reverse Recover Time	T_{rr}			–	420	–	nS
Reverse Recovery Charge	Q_{rr}	$I_F = 200\text{ A}$ $V_R = 400\text{ V}$, $dI_F/dt = 500\text{ A}/\mu\text{s}$, $T_{VJ} = 175^{\circ}\text{C}$		–	11.9	–	μC
Reverse Recovery Current	I_{rr}			–	49.5	–	A
Reverse Recover Time	T_{rr}			–	483	–	nS

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Switching characteristics and thermal properties are depending strongly on module design and mounting technology.

For ordering, technique and other information on ON Semiconductor automotive bare die products, please contact automotivebaredie@onsemi.com.

Die Layout





Figure 1. Die Layout

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
 Email Requests to: orderlit@onsemi.com

TECHNICAL SUPPORT
North American Technical Support:
 Voice Mail: 1 800-282-9855 Toll Free USA/Canada
 Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:
 Phone: 00421 33 790 2910
 For additional information, please contact your local Sales Representative