ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari



ON Semiconductor®


RURP15100-F085 15A 1000V Ultrafast Rectifier

Features

- High Speed Switching (t_{rr}=200ns(Typ.) @ I_F=15A)
- Low Forward Voltage(V_F=1.8V(Max.) @ I_F=15A)
- Avalanche Energy Rated
- AEC-Q101 Compliant

Applications


- Automotive DCDC converter
- Automotive On Board Charger
- Switching Power Supply
- Power Switching Circuits



15A, 1000V Ultrafast Rectifier

The RURP15100-F085 is an ultrafast diode with soft recovery characteristics (trr< 200ns). It has a low forward voltage drop and is of silicon nitride passivated, ion-implanted, epitaxial construction.

This device is intended for use as a freewheeling/ clamping diode and rectifier in a variety of automotive power supplies and other power switching automotive applications. Its low stored charge and ultrafast recovery with soft recovery characteristics minimizes ringing and electrical noise in many power switching circuits, thus reducing power loss in the switching transistor.



Absolute Maximum Ratings T_C = 25°C unless otherwise noted

| Symbol | Parameter | Ratings | Units | |
|----------------------------------|---|-----------|--------|--|
| V _{RRM} | Peak Repetitive Reverse Voltage | 1000 | V | |
| V _{RWM} | Working Peak Reverse Voltage | 1000 | V V | |
| V _R | DC Blocking Voltage | 1000 | | |
| I _{F(AV)} | Average Rectified Forward Current $@ T_C = 25^{\circ}C$ | 15 | А | |
| I _{FSM} | Non-repetitive Peak Surge Current | 45 | А | |
| E _{AVL} | Avalanche Energy(1A,40mH) | 20 | mJ | |
| T _{J,} T _{STG} | Operating Junction and Storage Temperature | - 55 ~175 | °C | |

Thermal Characteristics T_c = 25°C unless otherwise noted

| Symbol | Parameter | Мах | Units |
|---------------------|---|------|-------|
| $R_{	ext{	heta}JC}$ | Maximum Thermal Resistance, Junction to Case | 0.94 | °C/W |
| $R_{	hetaJA}$ | Maximum Thermal Resistance, Junction to Ambient | 85 | °C/W |

Package Marking and Ordering Information

| Device Marking | Device | Package | Tube | Quantity |
|----------------|----------------|----------|------|----------|
| RURP15100 | RURP15100-F085 | TO-220AC | - | 50 |

| Symbol | Parameter Instantaneous Reverse Current | Conditions | | Min. | Тур. | Max | Units |
|---|--|---|---|-------------|------------------|-------------|----------------|
| | | V _R = 1000V | T _C = 25 °C | | - | 100 | uA |
| | | | T _C = 175 °C | - | - | 1000 | uA |
| V _F ¹ | Instantaneous Forward Voltage | I _F = 15A | T _C = 25 °C T _C = 175 °C | - | 1.35 1.14 | 1.8 1.6 | V V |
| t _{rr} ² | Reverse Recovery Time | I _F =1A, di/dt = 100A/μs, V _R =650V | T _C = 25 °C | - | 126 | 260 | ns |
| | | I _F =15A, di/dt = 100A/μs, V _R =650V | T _C = 25 °C T _C = 175 °C | - | 200 720 | 450 - | ns ns |
| t _a t _b Q _{rr} | Reverse Recovery Time Reverse Recovery Charge | I _F =15A, di/dt = 100A/μs, V _R =650V | T _C = 25 °C | - - - | 63 137 683 | - - - | ns ns nC |
| W _{AVL} | Avalanche Energy | I _{AV} =1.0A, L=40mH | I | 20 | - | - | mJ |


Electrical Characteristics T_c = 25°C unless otherwise noted


Notes:


1. Pulse : Test Pulse width = 300 μ s, Duty Cycle = 2%


2. Guaranteed by design.

Test Circuit and Waveforms









ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such uninten

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative